

9002AW14

Foot Switch, Harmony 9002AW, industrial, pedal and side shields, DPDT contact, NEMA 2, 4, 13 enclosure, 0.6A at 600V AC



Main

Range	9002AW
Product	Foot switch
Contact Operation	1 step
Certifications	UL Listed CSA
Cable Entry	0.75 inch NPT conduit entrance
Contact Arrangement	DPDT
Enclosure Rating	NEMA 2/4/13
Voltage Rating	600 V AC/DC
Protection	Side shield Pedal shield
Operator Action	Spring return
Rated Breaking Capacity	3 A 120 V AC inductive control circuit UL 508 1.5 A 240 V AC inductive control circuit UL 508 0.75 A 480 V AC inductive control circuit UL 508 0.6 A 600 V AC inductive control circuit UL 508 3 A 120 V AC resistive control circuit UL 508 0.2 A 125 V DC resistive control circuit UL 508
Height	4.84 in (123 mm)
Width	5.39 in (137 mm)
Depth	9.02 in (229 mm)

Ordering and shipping details

Category	21441-9002 AW FOOT SWITCHES
Discount Schedule	CS1
GTIN	785901817413
Returnability	Yes
Country of origin	MX

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.71 in (14.5 cm)
Package 1 Width	5.79 in (14.7 cm)
Package 1 Length	12.20 in (31.0 cm)
Package 1 Weight	4.45 lb(US) (2.02 kg)

Offer Sustainability

Sustainable offer status	Green Premium product
California proposition 65	WARNING: This product can expose you to chemicals including: Nickel compounds, which is known to the State of California to cause cancer, and Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov
REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Mercury free	Yes
China RoHS Regulation	China RoHS Declaration
RoHS exemption information	Yes
Environmental Disclosure	Product Environmental Profile

Contractual warranty

Warranty	18 months
----------	-----------