

PhotoMOS HE SOP 1 Form A High Capacity


Product Catalog



PhotoMOS

HE SOP 1 Form A High Capacity

Miniature SOP6-pin type with high capacity up to Max. 3.3A in the series



TYPES

Category	Output rating*1		Part No.		Packing quantity	
			Surface mount terminal			
	Load voltage	Load current	Tube packing style	Tape and reel packing style X*2	Tube	Tape and reel
AC/DC	60 V	3.3 A	AQV252G3S	AQV252G3SX	1-tube: 75 pcs.	1-reel: 1,000 pc
dual use	100 V	2.2 A	AQV255G3S	AQV255G3SX	Outer carton: 1,500 pcs.	

Note: For space reasons, the two initial letters of the part number "AQ" and the packing style indicator "X" are not marked on the device.

(Ex. the label for product number AQV252G3SX is V252G3S.)

*1.Indicate the peak AC and DC values.

*2. Tape and reel packing style X: picked from the 1/2/3-pin side. For part numbers with picked from the 4/5/6-pin side, change the "X" at the end to "Z" when ordering.

RATING


Absolute maximum ratings (Ambient temperature: 25°C)

	Item	Symbol	Type of connection	AQV252G3S	AQV255G3S	Remarks
	LED forward current	١۶	-	50 mA		
÷	LED reverse voltage	VR	-	5	V	
Input	Peak forward current	IFP	-	1	A	f = 100 Hz, Duty Ratio = 0.1%
	Power dissipation	Pin	-	75	mW	
	Load voltage (peak AC)	V.	-	60 V	100 V	
			A	3.3 A	2.2 A	A connection: Peak AC, DC
t	Continuous load current	IL	В	3.5 A	2.4 A	P. C. connection: DC
Output			С	6.6 A	4.4 A	B, C connection: DC
0	Peak load current	Ipeak	-	10 A	6.6 A	100 ms (1 shot), V∟ = DC at A connection
	Power dissipation	Pout	-	450 mW		
Total	power dissipation	Ρτ	-	500	mW	
I/O is	I/O isolation voltage		-	1,500	Vrms	
Ambi	ent temperature (Operating)	T _{opr}	-	-40 to +85°C		(Avoid icing and condensation)
Ambi	ent temperature (Storage)	Tstg	-	-40 to	+100°C	
Junct	ion temperature	Tj	-	12	5°C	

Electrical characteristics (Ambient temperature: 25°C)

	Item		Symbol	Type of connection	AQV252G3S	AQV255G3S	Condition
LED operate current		Typical Maximum	Fon	-		mA nA	I∟ = 100 mA
Input	LED turn off current	Minimum Typical	Foff	-		mA mA	I∟ = 100 mA
	LED dropout voltage	Typical Maximum	VF	-		/ at I⊧ = 5 mA) 5 V	I⊧ = 50 mA
		Typical	_		0.033 Ω	0.07 Ω	I⊧ = 5 mA
		Maximum	Ron	A	0.06 Ω	0.12 Ω	l∟ = Max. Within 1 s
	On maintaine	Typical	_	_	0.017 Ω	0.035 Ω	I⊧ = 5 mA
Output	On resistance	Maximum	Ron	В	0.04 Ω	0.07 Ω	l∟ = Max. Within 1 s
õ	õ	Typical	_	0	0.0095 Ω	0.02 Ω	I⊧ = 5 mA
		Maximum	Ron	С	0.02 Ω	0.04 Ω	I∟ = Max. Within 1 s
	Off state leakage current	Maximum	Leak	-	1 µA		I _F = 0 mA V∟ = Max.
	Turn on time*	Typical	Ton -		1.8 ms		I _F = 5 mA I∟ = 100 mA
	rum on une	Maximum	Ion	-	5 ms		$V_{L} = 10 \text{ V}$
tics	Turn off time*	Typical	Toff		0.15 ms		I⊧ = 5 mA I⊾ = 100 mA
teris		Maximum	loff	-	0.5 ms		$V_{L} = 10 \text{ V}$
larac	I/O capacitance	Typical	Ciso	_		pF	f = 1 MHz
		Maximum	- 135		1.5	pF	V _B = 0 V
Site Turn off time* I/O capacitance Initial I/O isolation resistance	Minimum	Riso	-	1,000) ΜΩ	500 V DC	
Max operating		Maximum	-	-	2.5	cps	I _F = 5 mA duty = 50% I _L = Max. V _L = Max.

*Turn on/Turn off time




Recommended operating conditions (Ambient temperature: 25°C) Please use under recommended operating conditions to obtain expected characteristics.

	Item	Symbol	Min.	Max.	Unit
L	ED current	F	5	30	mA
	Load voltage (Peak AC)	VL	-	48	V
AQV252G3S	Continuous load current (A connection)	l.	-	3.3	A
	Load voltage (Peak AC)	VL	-	80	V
AQV255G3S	Continuous load current (A connection)	١L	-	2.2	A


REFERENCE DATA

1-1.Load current vs. ambient temperature characteristics

Sample: AQV252G3S Allowable ambient temperature: -40 to +85°C




3.Turn on time vs. ambient temperature characteristics




1-2.Load current vs. ambient temperature characteristics

Sample: AQV255G3S Allowable ambient temperature: -40 to +85°C




4.Turn off time vs. ambient temperature

characteristics LED current: 5 mA; Load voltage: 10 V (DC); Cartingue background 400 mA; (DC)




2.On resistance vs. ambient temperature characteristics



5.LED operate current vs. ambient temperature characteristics

Tested sample: All; Load voltage: 10 V (DC); Continuous load current: 100mA (DC) 5 4 4 3 3 2




- 3 -

PhotoMOS HE SOP 1 Form A High Capacity


6.LED turn off current vs. ambient

temperature characteristics




7.LED dropout voltage vs. ambient temperature characteristics

LED current: 5 to 50 mA




8.Current vs. voltage characteristics of output at MOS portion


Measured portion: between terminals 4 and 6; Ambient temperature: 25°C




9.Off state leakage current vs. load voltage characteristics













11.Turn off time vs. LED forward current characteristics

Measured portion: between terminals 4 and 6; Load voltage: 10 V (DC); Continuous load current: 100 mA (DC); Ambient temperature: 25°C




12.Output capacitance vs. applied voltage characteristics



13.Max. operating frequency vs. load

voltage and load current characteristics






DIMENSIONS CAD The CAD data of the products with a "CAD" mark can be downloaded from our Website. Unit: mm


CAD

External dimensions

Recommended mounting pad (TOP VIEW)







SCHEMATIC AND WIRING DIAGRAMS

Schematic	Output configuration	Load type	Connection	Wiring diagram
	1 Form A	AC/DC	A	$E_{1} \xrightarrow{f} 2$
			DC B	$E_1 \underbrace{\downarrow F}_{3} \underbrace{\downarrow F}_{3} \underbrace{\downarrow F}_{3} \underbrace{\downarrow F}_{4} \downarrow F$
20		DC		$E_{1} \xrightarrow{I_{F}} 2$
				Can be also connected as 2 Form A type. (However, the sum of the continuous load current should not exceed the absolute maximum rating.)
		DC	С	$E_{1} \xrightarrow{f} 2$

*Terminal 3 cannot be used, since it is in the internal circuit of the device.

SAFETY STANDARDS

			UL (Recognized)		
Part No.		File No. (Standard No.)	Contact rating	Remarks	
AC/DC dual use	AQV252G3S	E191218	3.3A 60V AC (peak) A connection 3.3A 60V DC A connection 3.5A 60V DC B connection 6.6A 60V DC C connection		
	AQV255G3S	(UL1577)	2.2A 100V AC (peak) A connection 2.2A 100V DC A connection 2.4A 100V DC B connection 4.4A 100V DC C connection		

Note: For the latest information on compliance with safety standards, please refer to our website.

Please refer to **"the latest product specifications"** when designing your product. •Requests to customers: https://industrial.panasonic.com/ac/e/salespolicies/

- 5 -

A SAFETY WARNINGS

- Do not use the product under conditions that exceed the range of its specifications. It may cause overheating, smoke, or fire.
- Do not touch the recharging unit while the power is on. There is a danger of electrical shock. Be sure to turn off the power when performing mounting, maintenance, or repair operations on the device (including connecting parts such as the terminal board and socket).

PhotoMOS[®] Cautions for Use

Derating design

Derating is a significant factor for reliable design and product life. Even if the conditions of use (temperature, current, voltage, etc.) of the product are within the absolute maximum ratings, reliability may be lowered remarkably when continuously used in high load conditions (high temperature, high humidity, high current, high voltage, etc.) Therefore, please derate sufficiently below the absolute maximum ratings and evaluate the device in the actual condition.

Moreover, regardless of the application, if malfunctioning can be expected to pose high risk to human life or to property, or if products are used in equipment otherwise requiring high operational safety, in addition to designing double circuits, that is, incorporating features such as a protection circuit or a redundant circuit, safety testing should also be carried out.

Applying stress that exceeds the absolute maximum rating

If the voltage or current value for any of the terminals exceeds the absolute maximum rating, internal elements will deteriorate because of the overvoltage or overcurrent. In extreme cases, wiring may melt, or silicon P/N junctions may be destroyed.

Therefore, the circuit should be designed in such a way that the load never exceed the absolute maximum ratings, even momentarily.

Input voltage (for Voltage-sensitive type)

For rising and dropping ratio of input voltage(dv/dt), maintain Min. 100mV/ms.

Oscillation circuit and control circuit (for CC Type)

The oscillation circuit and control circuit of product may be destroyed by external noise, surge, static electricity and so on.

For noise effect to peripheral circuits when oscillation circuit operates, please implement safety measures on the system before use by verifying operation under the actual design.

Deterioration and destruction caused by discharge of static electricity

This phenomenon is generally called static electricity destruction, and occurs when static electricity generated by various factors is discharged while the PhotoMOS[®] terminals are in contact, producing internal destruction of the element.

To prevent problems from static electricity, the following precautions and measures should be taken when using your device.

- 1) Employees handling PhotoMOS[®] should wear anti-static clothing and should be grounded through protective resistance of $500k\Omega$ to $1M\Omega$.
- A conductive metal sheet should be placed over the worktable. Measuring instruments and jigs should be grounded.
- When using soldering irons, either use irons with low leakage current, or ground the tip of the soldering iron. (Use of low-voltage soldering irons is also recommended.)
- 4) Devices and equipment used in assembly should also be grounded.

- Check the wiring diagrams in the catalog and be sure to connect the terminals correctly. If the device is energized with short circuit or any wrong connection, it may cause unexpected malfunction, abnormal heat or fire.
 - 5) When packing printed circuit boards and equipment, avoid using high-polymer materials such as foam styrene, plastic, and other materials which carry an electrostatic charge.
 - 6) When storing or transporting PhotoMOS[®], the environment should not be conducive to generating static electricity (for instance, the humidity should be between 45% and 60%), and PhotoMOS[®] should be protected using conductive packing materials.

Unused terminals

The No. 3 terminal is used with the circuit inside the device. Therefore, do not connect it to the external circuitry with either connection method A, B or C. (1 Form A 6-pin type)


Short across terminals

Do not short circuit between terminals when device is energized, since there is possibility of breaking of the internal IC.


Surge voltages at the input

If reverse surge voltages are present at the input terminals, connect a diode in reverse parallel across the input terminals and keep the reverse voltages below the reverse breakdown voltage. Typical circuits are below shown.

1) 6-pin








Reverse voltages at the input (for CC Type)

If reverse voltages are present at the input terminals, for example, connect a schottky barrier diode in reverse parallel across the input terminals and keep the reverse voltages below the reverse breakdown voltage. Typical circuit is shown below.




Recommended LED forward current or recommended input voltage

Design in accordance with the recommended operating conditions for each product.


Since these conditions are affected by the operating environment, ensure conformance with all relevant specifications.

LED forward current vs. Ambient temperature characteristics

Please keep the LED forward current to within the range given below.




For AQV209G, APV1111GV, APV3111GV



Ripple in the input power supply


If ripple is present in the input power supply, observe the following:
 1) For LED forward current at E^{min}, please maintain the value mentioned at "■Recommended LED forward current."

- 2) Please make sure the LED forward current for $E_{\mbox{\tiny max}}$ is no higher than 50 mA.
- Please maintain the input voltage at least 4V for Emin. (GU, RF and Power voltage-sensitive type).
- Please make sure the input voltage for E_{max}. is no higher than 6V (GU and RF voltage-sensitive type).
- Please make sure the input voltage for E_{max}. is no higher than 30V (Power voltage-sensitive type).




- 6) Please maintain the input voltage at least 3V for E_{min}. (for CC Type)
- 7) Please make sure the input voltage for $E_{\mbox{\tiny max}}$ is no higher than 5.5V. (for CC Type)


 Please keep amplitude voltage of ripple within ±0.5V. (for CC Type)



Output spike voltages

 If an inductive load generates spike voltages which exceed the absolute maximum rating, the spike voltage shall be limited. Representative circuit examples of AC/DC dual use type are shown below. There are the same with DC only type.
 (1) 6-pin






2) When Clamp diode or CR Snubber is used in the circuit, the spike voltages from the load are limited. But the longer wire may become the inductance and cause the spike voltage. Keep the wire as short as possible.

Output Waveform (CC Type)

This product has the capacitor coupled isolation. Therefore, if output waveform fluctuates along the time axis (e.g. AC waveform or pulsating waveform), it may affect the operation of this product and peripheral circuit. Please evaluate the device in the actual condition.


Continual DC bias (AQV259 and AQV258)

If a continual DC bias will be applied between the input and output, the breakdown voltage of the switching element MOSFET on the output side may degrade. Therefore, be sure to test the product under actual conditions. Example of circuits that will cause degradation of breakdown voltage of MOSFET is given below.



Connections Between Input and Output (CC Type)

If you wish to use the product with a connection between input and output, you may not obtain expected performance. Therefore, please be sure to evaluate the device in the actual usage. A circuit example is shown below that may negatively affect PhotoMOS characteristics.




Cleaning solvents compatibility

Cleaning the solder flux should use the immersion washing with an organic solvent. If you have to use ultrasonic cleaning, please adopt the following conditions and check that there are no problems in the actual usage.

- Frequency: 27 to 29kHz
- Ultrasonic output: No greater than 0.25W/cm^{2*}
- · Cleaning time: 30s or less
- Others: Float PCB and the device in the cleaning solvent to prevent from contacting the ultrasonic vibrator
 * Applies to unit area ultrasonic output for ultrasonic baths
- Notes for mounting
 - When different kinds of packages are mounted on PC boad, temperature rise at soldering lead is highly dependent on package size. Therefore, please set the lower temperature soldering condition than the conditions of item "■Soldering", and confirm the temperature condition of actual usage before soldering.
 - 2) When soldering condition exceeds our recommendation, the PhotoMOS[®] characteristics may be adversely affected. It may occur package crack or bonding wire breaking because of thermal expansion unconformity and resin strength reduction. Please contact our sales office about the propriety of the condition.
 - Please confirm the heat stress by using actual board because it may be changed by board condition or manufacturing process condition.
 - 4) Solder creepage, wettability, or soldering strength will be affected by the soldering condition or used soldering type. Please check them under the actual production condition in detail.
 - 5) Please apply coating when the device returns to a room temperature.

Input wiring pattern

 With AQY* or AQW* series avoid installing the input (LED side) wiring pattern to the bottom side of the package if you require the specified I/O isolation voltage (V_{iso}) after mounting the PC board. Since part of the frame on the output side is exposed, it may cause fluctuations in the I/O isolation voltage.




May not allow the prescribed I/O withstan voltage (Viso) to be achieved

- * Excluding high I/O isolation voltage products and SSOP, SON, and TSON packages
- 2) Exposed terminals are electrically connected to internal elements. Be aware that contact with external circuits may cause deterioration of insulation between input and output, leading to destruction of internal elements.
- If installed in proximity to other device, take care to avoid short circuits between device, which may occur if exposed frames of adjacent device come too close.

Soldering

- Example of surface-mount terminal recommended conditions
 IR (Infrared reflow) soldering method
 - In case of automatic soldering, following conditions should be observed. (recommended condition reflow: Max. 2 times, measurement point: soldering lead)




T1 = 150 to 180°C T2 = 230°C T3 = 240 to 250°C* t1 = 60 to 120 s t2 = Within 30 s t3 = Within 10 s *240 to 245°C for SON, VSSOP and TSON package

- (2) Other soldering methods Other soldering methods (VPS, hot-air, hot plate, laser heating, pulse heater, etc.) affect the PhotoMOS[®] characteristics differently, please evaluate the device under the actual usage.
- (3) Manual soldering method Temperature: 350 to 400°C, within 3s, electrical power 30 to 60W
- 2) Example of through hole terminal recommended conditions

(1) DWS soldering method

In case of automatic soldering, following conditions should be observed. (recommended condition number of times: Max. 1 time, measurement point: soldering lead *1)



T₁ = 120°C T₂ = Max. 260°C t₁ = within 60 s t₂+t₃ = within 5 s

*1 Solder temperature: Max. 260°C

(2) Other soldering method (recommended condition: 1 time) Preheating: Max. 120°C, within 120s, measurement point: soldering lead

Soldering: Max. 260°C, within 10s, measurement area: soldering temperature


(3) Manual soldering method

Temperature: 350 to 400°C, within 3s, electrical power 30 to 60W

About the exposed terminals on the sides of the package (for VSSOP)

For VSSOP type, as shown in the following figure, part of the input and output frames are exposed on the sides of the package. Due to this, please be keep in mind the cautions listed below.

- Take care to avoid short circuits between exposed terminals, which may cause insulation deterioration between input and output, leading to destruction of internal elements.
- 2) Since the exposed terminals are connected electrically to the internal element, please refer to the item "Deterioration and destruction caused by discharge of static electricity", and implement sufficient measures to control static electricity.
- 3) When installing the devices in the vicinity, please keep in mind that if the exposed frames of adjacent devices get too close, a short between devices may occur.



Adjacent mounting

When several PhotoMOS[®] are mounted closely each other or heat-generating components are mounted close to the PhotoMOS[®], the abnormal heating may occur. This abnormal heat may be caused by the internal element when energized or thermal interference between the devices. The degree of temperature rise depends on the mounting layout of the devices and usage condition, therefore please be sure to use PhotoMOS[®] with reduced load current after testing under the worst condition of the actual usage.

Transportation and storage

- Extreme vibration during transport may deform the lead or damage the PhotoMOS[®] characteristics. Please handle the outer and inner boxes with care.
- Inadequate storage condition may degrade soldering, appearance, and characteristics. The following storage conditions are recommended:
 - Temperature: 0 to 45°C
 - Humidity: Max. 70%RH
 - Atmosphere: No harmful gasses such as sulfurous acid gas, minimal dust.
- 3) Storage before TSON, VSSOP, SON, SSOP, or SOP processing In case the heat stress of soldering is applied to the PhotoMOS[®] which absorbs moisture inside of its package, the evaporation of the moisture increases the pressure inside the package and it may cause the package blister or crack. This device is sensitive to moisture and it is packed in the sealed moisture-proof package. Please make sure the following condition after unsealing.
 - * Please use the device immediately after unsealing.

(Within 30 days at 0 to 30°C and Max. 70%RH)

* If the device will be kept for a long time after unsealing, please store in the another moisture-proof package containing silica gel. (Please use within 90 days.)


Water condensation

Water condensation occurs when the ambient temperature changes suddenly from a high temperature to low temperature at high humidity, or the device is suddenly transferred from a low ambient temperature to a high temperature and humidity. Condensation causes the failures such as insulation deterioration. Panasonic Industry Co., Ltd. does not guarantee the failures caused by water condensation. The heat conduction by the equipment the PhotoMOS[®] is mounted may accelerate the water condensation. Please confirm that there is no condensation in the worst condition of the actual usage. (Special attention should be paid when high temperature heating parts are close to the PhotoMOS[®].)

-9-


Packing format

1) Tape and reel




Note: " * " indicates characters of number or alphabet.

Panasonic Industry Co., Ltd. Electromechanical Control Business Division industrial.panasonic.com/ac/e/





Note: " * " indicates characters of number or alphabet.



2) Tube


Devices are packaged in a tube so that 1-pin is on the stopper B side. Observe correct orientation when mounting them on PC boards.





Current limit function (output current control)

 Current limit function aims to increase resistance to surges when the switch is turned on. Before using this function, connect the varistor to the output as shown in the figure below.



2) The current limit function capability can be lost if used longer than the specified time. Be sure to set the output loss to the Max. rate.


Short circuit protection circuit

The short circuit protection circuit is designed to protect circuits from excess current. Therefore, surge current may be detected as current overload in which case the output current will be cut and the off state maintained. For this reason, please include the inrush current in the load current and keep it below the maximum load current. Also, in order to maintain stability of internal IC operation, maintain an input current of at least 5 mA (Latch type), 10 mA (Non Latch type).

Photovoltaic MOSFET driver cautions for use

When two external MOSFETs are connected with a common source terminal, oscillation may occur when operation is restored. Therefore, please insert a 100 to 1,000 Ω resistor between the gate terminal of the first MOSFET and the gate terminal of the second MOSFET.

A typical example of this is given in the circuit below.



Input LED current

(For High Capacity type: with part number G) When making PhotoMOS turn on and turn off, please make sure that the LED forward current increases and decreases instantly.

■ Input voltage (for Power voltage-sensitive type)

For rising and dropping ratio of input voltage (dv/dt), maintain Min. 100 mV/s.

Adjacent mounting (for Power type)

- When devices are mounted close together with the heatgenerated devices, ambient temperature may rise abnormally. Mounting layout and ventilation should be considered.
- 2) When many devices are mounted close together, load current should be reduced. (Refer to the data of "Load current in adjacent mounting vs. Ambient temperature characteristics.")

Recommended load voltage

As a guide in selecting PhotoMOS[®], please refer to the following table.

1) Power photoMOS[®] (1 Form A)

		Absolute ma:	Recommended	
		Load voltage Load current		load voltage
	AQZ102	60 V DC	4.0 A DC	5, 12, 24 V DC
DC	AQZ105	100 V DC	2.6 A DC	48 V DC
type	AQZ107	200 V DC	1.3 A DC	100 V DC
	AQZ104	400 V DC	0.7 A DC	200 V DC
	AQZ202	Peak AC, DC 60 V	Peak AC, DC 3.0 A	12 V AC 5, 12, 24 V DC
AC/ DC	AQZ205	Peak AC, DC 100 V	Peak AC, DC 2.0 A	24 V AC 48 V DC
type	AQZ207	Peak AC, DC 200 V	Peak AC, DC 1.0 A	48 V AC 100 V DC
	AQZ204	Peak AC, DC 400 V	Peak AC, DC 0.5 A	120 V AC 200 V DC

2) Power photoMOS® (1 Form B)

		Absolute ma	Recommended	
		Load voltage	Load current	load voltage
AC/ DC type	AQZ404	Peak AC, DC 400 V	Peak AC, DC 0.5 A	100 V AC 200 V DC

3) Power photoMOS® Voltage-sensitive type (1 Form A)

		Absolute ma	ximum rating	Recommended
		Load voltage Load current		load voltage
	AQZ102D	60 V DC	3.6 A DC	5, 12, 24 V DC
DC	AQZ105D	100 V DC	2.3 A DC	48 V DC
type	AQZ107D	200 V DC	1.1 A DC	100 V DC
	AQZ104D	400 V DC	0.6 A DC	200 V DC
	AQZ202D	Peak AC, DC 60 V	Peak AC, DC 2.7 A	12 V AC 5, 12, 24 V DC
AC/ DC	AQZ205D	Peak AC, DC 100 V	Peak AC, DC 1.8 A	24 V AC 48 V DC
type	AQZ207D	Peak AC, DC 200 V	Peak AC, DC 0.9 A	48 V AC 100 V DC
	AQZ204D	Peak AC, DC 400 V	Peak AC, DC 0.45 A	120 V AC 200 V DC

4) Power photoMOS® High Capacity type (1 Form A)

		Absolute ma	Recommended	
		Load voltage	Load current	load voltage
DC	AQZ192	60 V DC	10 A DC	5, 12, 24 V DC
type	AQZ197	200 V DC	5 A DC	100 V DC
	AQZ202G	Peak AC, DC 60 V	Peak AC, DC 6 A	12 V AC 5, 12, 24 V DC
AC/ DC	AQZ205G	Peak AC, DC 100 V	Peak AC, DC 4 A	24 V AC 48 V DC
type	AQZ207G	Peak AC, DC 200 V	Peak AC, DC 2 A	48 V AC 100 V DC
	AQZ206G2	Peak AC, DC 600 V	Peak AC, DC 1 A	120, 240 V AC 200, 400 V DC



Panasonic Industry Co., Ltd.

Electromechanical Control Business Division 1006, Oaza Kadoma, Kadoma-shi, Osaka 571-8506, Japan industral.panasonic.com/ac/e/

