





NOTES:
1.) MATERIAL WILL BE TYPE I PVC
2.) ALL TOLERANCES TO BE $\pm$.015 UNLESS OTHERWISE NOTED
3.) MAXIMUM OPERATING TEMPERATURE TO BE 140° F.

PLPVC108

PART No. 14PVC0907



for more information visit
www.hammfg.com
Data subject to change without notice
Drawing Not to Scale