





THIS PRINT VALID FOR
THIS ORDER ONLY.

P.O. # _____
DATE: _____

NOTES:
1.) MATERIAL WILL BE TYPE I PVC
2.) ALL TOLERANCES TO BE $\pm .015$ UNLESS OTHERWISE NOTED
3.) MAXIMUM OPERATING TEMPERATURE TO BE 140° F.

PLPVC66



PART No. 14PVC0505

for more information visit
www.hammfg.com
Data subject to change without notice
Drawing Not to Scale