

### Product Search Data Sheet

Note: This datasheet may be out of date. Please download the latest datasheet of DFE18SANR47ME0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR47ME0%23

"#" indicates a package specification code.

# DFE18SANR47ME0#

In Production











Size Code 1608 (0603) in mm (in inch), 0.8mm max. Thickness. Small and high performance type.





< List of part numbers with package codes > DFE18SANR47ME0L



## **Applications**

Consumer equipment Please refer to Our Website and specifications, etc. for information about the performance, functions, quality, Specific management, and safety required for **Applications** the above applications, and use Products after confirming the performance and reliability of the actual Product.




### **Notices**

The saturation allowable DC current value is specified when the decrease of the initial inductance value at 30%. When rated current is applied to the products, the temperature rise caused by self-generated heat shall be limited to 40°C max. Keep the temperature (ambient temperature plus self-generation of heat) under 125°C.



## Appearance & Shape







## References

Packaging		Standard Packing Quantity
L	180Embossed Tape	3000

Mass (typ.)	
1 piece	0.007g

1 of 4

- 1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.
- 2. This datasheet has only typical specifications because there is no space for detailed specifications
- Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering





# DFE18SANR47ME0#

Note: This datasheet may be out of date.

Please download the latest datasheet of DFE18SANR47ME0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR47ME0%23

"#" indicates a package specification code.



# **Specifications**

L size	1.6±0.2mm
W size	0.8±0.2mm
T size	0.8mm
Size code inch (mm)	0603 (1608)
Inductance	0.47µH±20%
Inductance Test Frequency	1MHz
Rated current (Isat) (Based on Inductance change)	3100mA
Rated current (Itemp) (Based on Temperature rise)	2400mA
Max. of DC resistance	0.064Ω
Operating Temperature Range (Self-temperature rise is included)	-40°C to 125°C
Class of magnetic shield	Metal Alloy
Operating Temperature Range(Self-temperature rise is not included)	-40°C to 85°C
Absolute maximum voltage	20Vdc
Brand	Murata
Series	DFE18SAN_E0

2 of 4

#### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.



### Product Search Data Sheet

Please download the latest datasheet of DFE18SANR47ME0# from the official website of Murata

Manufacturing Co., Ltd.

Note: This datasheet may be out of date.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR47ME0%23


"#" indicates a package specification code.





## Characteristic Data


DFE18SANR47ME0#

The charts below may show another part number which shares its characteristics.









3 of 4

1. This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering






# DFE18SANR47ME0#

Note: This datasheet may be out of date.

Please download the latest datasheet of DFE18SANR47ME0# from the official website of Murata Manufacturing Co., Ltd.

http://www.murata.com/en/products/productdetail?partno=DFE18SANR47ME0%23

"#" indicates a package specification code.



4 of 4

#### Attention

1.This datasheet is downloaded from the website of Murata Manufacturing Co., Ltd. Therefore, it's specifications are subject to change or our products in it may be discontinued without advance notice. Please check with our sales representatives or product engineers before ordering.

2. This datasheet has only typical specifications because there is no space for detailed specifications.

Therefore, please review our product specifications or consult the approval sheet for product specifications before ordering.

