ASPIAIG-F6060

Request Samples 🕥

Check Inventory

6.6 x 6.4 x 5.8 mm RoHS/RoHS II Compliant MSL Level = 1

Features

- PPAP ready and supported
- TS16949 certified production lines
- AEC-Q200 qualified $(-55^{\circ}C \sim +155^{\circ}C)$
- Shielded construction
- Soft saturation
- Low DCR, High Efficiency

Applications

- Body electronics and comfort system
- Infotainment and entertainment
- Electric vehicles
- Lighting
- Solar inverters and power
- Industrial and robotics
- Medium and high-power switch mode power supplies.

Electrical Specifications

Part Number	Inductance	Tolerance	DC Resistance		Saturation Current	Temperature Rise Current
	0.1MHz/1.0V		Max	Тур.	Max	Тур.
Units	μH	%	n	ıΩ	Α	Α
Symbol	L	Μ	D	CR	Isat	Irms
ASPIAIG-F6060-4R7M-T	4.70	20	14.4	13.10	9.5	11.0
ASPIAIG-F6060-5R6M-T	5.60	20	15.8	14.30	9.0	10.0
ASPIAIG-F6060-6R8M-T	6.80	20	20.8	18.90	8.7	9.0
ASPIAIG-F6060-8R2M-T	8.20	20	24.8	22.50	8.0	8.0
ASPIAIG-F6060-100M-T	10.0	20	29.3	26.60	6.8	7.0

Test Conditions


Isat: DC current at which the inductance drops 30% from its value without current. Irms: DC current that causes the temperature rise (ΔT , approximate 40 °C) from 25°C ambient.

Operating Temperature: -55°C ~ +155°C (including self-temperature rise)

Storage Condition: $-55^{\circ}C \sim +155^{\circ}C$ (on board), $-10^{\circ}C \sim +40^{\circ}C$ (with packaging) and R.H. 60 max **ASPIAIG-F6060 Series is RoHS Compliant and Pb free**

ASPIAIG-F6060 is AEC-Q200 Grade 0 qualified (-55°C ~ +155°C)


Part Identification





5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION: IR 05-01-23






5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION: IR 05-01-23






Zone	Description	Temperature	Times
1	Preheat	$\begin{array}{l} T_{SMIN} \sim T_{SMAX} \\ 150^{\circ}C \sim 200^{\circ}C \end{array}$	$60 \sim 180$ sec.
2	Reflow	T _L 217°C	$60 \sim 150$ sec.
3	Peak heat	Тр 260°С	10 sec. MAX



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION: IR 05-01-23



ATTENTION: Abracon LLC's products are COTS – Commercial-Off-The-Shelf products; suitable for Commercial, Industrial and, where designated, Automotive Applications. Abracon's products are not specifically designed for Military, Aviation, Aerospace, Life-dependent Medical applications or any application requiring high reliability where component failure could result in loss of life and/or property. For applications requiring high reliability and/or presenting an extreme operating environment, written consent and authorization from Abracon LLC is required. Please contact Abracon LLC for more information.



5101 Hidden Creek Ln Spicewood TX 78669 Phone: 512-371-6159 | Fax: 512-351-8858 For terms and conditions of sales, please visit: www.abracon.com

REVISION: IR 05-01-23