VC 10/1/9



Advantages

Minimum size at high output

Dual output voltage for series or parallel connection

Permanent corrosion protection, high insulation value and maximum electrical reliability due to XtraDenseFill resin encapsulation


Self-extinguishing potting material

Applications

As a mains transformer for adjustment of the voltage and simple electrical isolation.

As a safety transformer for the safe electrical isolation of the input and output of the limit on the output voltage.

Sample application



Standards

Safety isolating transformer to: VDE 0570 Part 2-6, DIN EN 61558-2-6, EN 61558-2-6, IEC 61558-2-6, UL 5085-1/-2, CSA 22.2 No.66

Approvals







VDE, UL 5085-1/-2, CSA 22.2 No.66





Safety isolating transformer **VC 10/1/9**

Туре	VC 10/1/9	Туре	VC 10/1/9	
5 Input		Terminal and mounting		
Rated input voltage	230 Vac	Terminals	Terminals Pins for printed circuit boards	
Rated frequency	50 - 60 Hz	Measures and weights		
Output Rated output voltage		Pin (a) Core type	0.031 inch	
Rated output voltage	9 Vac		EI 48/16,8	
o Power	10 VA	₩eight	0.62 lbs	
Power No-load voltage (app. x factor) No-load loss (typ.) Efficiency	1.25	.은		
No-load loss (typ.)	1.6 W	© Dimensions in inch	Weight 0.62 lbs Dimensions in inch	
Efficiency	74 %	0		
Standards		Ž		
Classification	Safety isolating transformer		1.36	
Approvals		A •	0.2	
Approvals	cURus, VDE	0.98 PRI SEC	0.59 2.01	
Environment		↓ •	0.2	
Ambient temperature max.	104.0 °F		↑	
Safety and protection			<u> </u>	
Туре	Encapsulated	1.69	+	
Insulation class	VDE=B, UL=class 105			
Protection index	IP 00			
Safety class (prepared)	II			
Short circuit strength	non-short-circuit proof			
Order numbers				
Order Number	VC 10/1/9			

