

UIC558 13PIN-FI-CRT



Image is for illustration purposes only. Please refer to product description.

Part number	09 58 013 3101
Specification	UIC558 13PIN-FI-CRT
HARTING eCatalogue	https://b2b.harting.com/09580133101

Identification

Category	Inserts
Series	HARTING UIC 558

Version

Termination method	Crimp termination
Gender	Female
Number of contacts	13
Details	Please order crimp contacts separately.

Technical characteristics

Conductor cross-section	0.75 ... 1 mm ²
Conductor cross-section	AWG 18 ... AWG 17
Rated current	10 A
Rated voltage	60 V
Insulation resistance	>10 ⁷ Ω
Limiting temperature	-50 ... +125 °C
Mating cycles	≥10,000

Material properties

Material (insert)	Polyamide (PA)
Colour (insert)	Black
Material flammability class acc. to UL 94	V-0



Pushing Performance
Since 1945

Specifications and approvals

Specifications	UIC 550
	IRS 50558
	IEC 61373 Category 2
	IEC 60529

Commercial data

Packaging size	1
Net weight	87 g
Country of origin	India
European customs tariff number	85366990
GTIN	5713140186972
eCl@ss	27440205 Contact insert for industrial connectors