

www.vishay.com

Vishay

# **Pulse Proof Thick Film Chip Resistors**




### **LINKS TO ADDITIONAL RESOURCES**



The pulse proof thick film chip resistor series is the perfect choice for high pulse load performance resistors. Typical applications include automotive DC-DC converters and on-board chargers, lighting ballasts, and storage drivers.

### **FEATURES**

- High pulse performance, up to 10 kW
- High pulse voltage up to 4 kV, 1.2 μs / 50 μs





- AEC-Q200 qualified
- Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912">www.vishay.com/doc?99912</a>

### **APPLICATIONS**

- DC-DC converters
- On-board chargers
- · Lighting ballasts
- Storage drivers

DESCRIPTION	10/CRCW0402-IF	D11/CRCW0603-IF	D12/CRCW0805-IF	D25/CRCW1206-I	FCRCW1210-IF	CRCW2010-IF	CRCW2512-I		
DESCRIPTION	e3	e3	e3	e3	e3	e3	e3		
Imperial size	0402	0603	0805	1206	1210	2010	2512		
Metric size code	RR1005M	RR1608M	RR2012M	RR3216M	RR3225M	RR5025M	RR6332M		
Resistance range			1 Ω t	o 100 kΩ					
Resistance tolerance	± 10 %; ± 5 %								
Temperature coefficient	± 200 ppm/K								
Rated dissipation, $P_{70}$ (1)	0.063 W	0.10 W	0.125 W	0.25 W	0.50 W	0.75 W	1.0 W		
Operating voltage, <i>U</i> <sub>max.</sub> AC <sub>RMS</sub> /DC	50 V	75 V	150 V	200 V	200 V	400 V	500 V		
Permissible film temperature, $\vartheta_{\rm F \ max.}$ (1)	155 °C								
Operating temperature range		-55 °C to +155 °C							
Max. resistance change at P <sub>70</sub> for resistance range, I∆R/RI after:									
1000 h 8000 h				1.0 % 2.0 %					
Permissible voltage against ambient (insulation):									
1 min, U <sub>ins</sub>	75 V	100 V	200 V	300 V	300 V	300 V	300 V		
Failure rate: FIT <sub>observed</sub>	≤ 0.1 x 10 <sup>-9</sup> /h								

#### Note

(1) Please refer to "Application Information" below



## **APPLICATION INFORMATION**

When the resistor dissipates power, a temperature rise above the ambient temperature occurs, dependent on the thermal resistance of the assembled resistor together with the printed circuit board. The rated dissipation applies only if the permitted film temperature is not exceeded.


These resistors do not feature a limited lifetime when operated within the permissible limits. However, resistance value drift increasing over operating time may result in exceeding a limit acceptable to the specific application, thereby establishing a functional lifetime.

TEMPERATURE COEFFICIENT AND RESISTANCE RANGE								
TYPE / SIZE	TCR	TOLERANCE	RESISTANCE	E-SERIES				
D10/CRCW0402-IF e3	± 200 ppm/K	± 10 %	- 1.0 Ω to 100 kΩ	E24				
D 10/ChCW0402-IF e3	± 200 ppiii/K	± 5 %	1.0 \$2 to 100 K\$2	L24				
D11/CRCW0603-IF e3	± 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
DTI/Chcwooos-IF es	± 200 ppiii/K	± 5 %	1.0 \$2 to 100 K\$2					
D12/CRCW0805-IF e3	± 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
D12/ChCW0003-IF e3	± 200 ppm/K	± 5 %	1.0 \$2 to 100 K\$2					
D25/CRCW1206-IF e3	± 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
DZJ/ONOW1200-II eJ	± 200 ppm/K	± 5 %	1.0 22 to 100 K22	L24				
CRCW1210-IF e3	± 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
ChCW1210-IF e3	± 200 ppm/K	± 5 %	1.0 \$2 to 100 K\$2					
CRCW2010-IF e3	+ 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
Chowzulu-ir es	± 200 ppm/K	± 5 %	1.0 22 tO 100 K22					
CRCW2512-IF e3	+ 200 ppm/K	± 10 %	1.0 Ω to 100 kΩ	E24				
CRCW2512-IF es	± 200 ppm/K	± 5 %	1.0 22 tO 100 K22	L24				

PACKAGING									
TYPE / SIZE	CODE	QUANTITY	PACKAGING STYLE	WIDTH	PITCH	PACKAGING DIMENSIONS			
D10/CRCW0402-IF e3	ED = ET7	10 000		8 mm	2 mm	Ø 180 mm / 7"			
D10/ChCW0402-IF e3	EE = EF4	50 000		0 111111		Ø 330 mm / 13"			
	EI = ET2	5000				Ø 180 mm / 7"			
	ED = ET3	10 000			2 mm	Ø 180 mm / 7"			
	EL = ET4	20 000			2 111111	Ø 285 mm / 11.25"			
D11/CRCW0603-IF e3	EE = ET8	50 000		8 mm		Ø 330 mm / 13"			
	EA = ET1	5000			4 mm	Ø 180 mm / 7"			
	EB = ET5	10 000				Ø 285 mm / 11.25"			
	EC = ET6	20 000	Paper tape according to IEC 60286-3, type 1a			Ø 330 mm / 13"			
	EA = ET1	5000		8 mm	4 mm	Ø 180 mm / 7"			
D12/CRCW0805-IF e3	EB = ET5	10 000				Ø 285 mm / 11.25"			
	EC = ET6	20 000				Ø 330 mm / 13"			
	EA = ET1	5000			4 mm	Ø 180 mm / 7"			
D25/CRCW1206-IF e3	EB = ET5	10 000		8 mm		Ø 285 mm / 11.25"			
	EC = ET6	20 000				Ø 330 mm / 13"			
	EA = ET1	5000				Ø 180 mm / 7"			
CRCW1210-IF e3	EB = ET5	10 000		8 mm	4 mm	Ø 285 mm / 11.25"			
	EC = ET6	20 000				Ø 330 mm / 13"			
CRCW2010-IF e3	EF = E02	4000	Dial and a second second	12 mm	4 mm	Ø 180 mm / 7"			
CRCW2512-IF e3	EG = E67	2000	Blister tape according to IEC 60286-3 type 2a	12 mm	8 mm	Ø 180 mm / 7"			
0110112012-II 60	EH = E82	4000		12 111111	4 mm	2 100 111117 7			

www.vishay.com

Vishay





Vishay

### **DESCRIPTION**

Production is strictly controlled and follows an extensive set of instructions established for reproducibility. A cermet film layer and a glass-over are deposited on a high grade (Al<sub>2</sub>O<sub>3</sub>) ceramic substrate with its prepared inner contacts. The resistor elements are covered by a protective coating designed for electrical, mechanical and climatic protection. The terminations receive a final pure tin on nickel plating.

The result of the determined production is verified by an extensive testing procedure on 100 % of the individual chip resistors. Only accepted products are laid directly into the tape in accordance with **IEC 60286-3 Type 1a and Type 2a** (1).

#### **ASSEMBLY**

The resistors are suitable for processing on automatic SMD assembly systems. They are suitable for automatic soldering using wave, reflow or vapor phase as shown in **IEC 61760-1** <sup>(1)</sup>. The encapsulation is resistant to all cleaning solvents commonly used in the electronics industry, including alcohols, esters and aqueous solutions. The suitability of conformal coatings, potting compounds and their processes, if applied, shall be qualified by appropriate means to ensure the long-term stability of the whole system.

The resistors are RoHS-compliant, the pure tin plating provides compatibility with lead (Pb)-free and lead-containing soldering processes. Solderability is specified for 2 years after production or requalification. The permitted storage time is 20 years. The immunity of the plating against tin whisker growth has been proven under extensive testing.

### **MATERIALS**

Vishay acknowledges the following systems for the regulation of hazardous substances:

 IEC 62474, Material Declaration for Products of and for the Electrotechnical Industry, with the list of declarable substances given therein (2)

- The Global Automotive Declarable Substance List (GADSL) (3)
- The REACH regulation (1907/2006/EC) and the related list of substances with very high concern (SVHC) (4) for its supply chain

The products do not contain any of the banned substances as per IEC 62474, GADSL, or the SVHC list, see <a href="https://www.vishav.com/how/leadfree">www.vishav.com/how/leadfree</a>.

Hence the products fully comply with the following directives:

- 2000/53/EC End-of-Life Vehicle Directive (ELV) and Annex II (ELV II)
- 2011/65/EU Restriction of the Use of Hazardous Substances Directive (RoHS) with amendment 2015/863/EU
- 2012/19/EU Waste Electrical and Electronic Equipment Directive (WEEE)

Vishay pursues the elimination of conflict minerals from its supply chain, see the Conflict Minerals Policy at <a href="https://www.vishay.com/doc?49037">www.vishay.com/doc?49037</a>.

#### **APPROVALS**

The resistors are qualified according to AEC-Q200.

Where applicable, the resistors are tested in accordance with **EN 140401-802** which refers to **EN 60115-1**, **EN 60115-8** and the variety of environmental test procedures of the **IEC 60068** <sup>(1)</sup> series.

#### **RELATED PRODUCTS**

For more information about pulse proof and high power products please refer to CRCW-HP e3, "Pulse Proof, High Power Thick Film Chip Resistors" datasheet (www.vishav.com/doc?20043)

For anti-surge and high power products, please refer to RCS e3, "Anti-Surge, High Power Thick Film Chip Resistors" datasheet (www.vishav.com/doc?20065)

#### Notes


- (1) The quoted IEC standards are also released as EN standards with the same number and identical contents
- (2) The IEC 62474 list of declarable substances is maintained in a dedicated database, which is available at http://std.iec.ch/iec62474
- (9) The Global Automotive Declarable Substance List (GADSL) is maintained by the American Chemistry Council and available at www.gadsl.org

(4) The SVHC list is maintained by the European Chemical Agency (ECHA) and available at http://echa.europa.eu/candidate-list-table




## **FUNCTIONAL PERFORMANCE**

## Single Pulse




Maximum pulse load, single pulse; applicable if  $\overline{P} \to 0$  and n < 1000 and  $\hat{U} = \hat{U}_{\text{max}}$ ; for permissible resistance change equivalent to 8000 h operation

### **Continuous Pulse**



Maximum pulse load, continuous pulses; applicable if  $\overline{P} \leq P$  ( $\vartheta_{amb}$ ) and  $\hat{U} = \hat{U}_{max}$ ; for permissible resistance change equivalent to 8000 h operation


## **Pulse Voltage**




Maximum pulse voltage, single and continuous pulses; applicable if  $\hat{P} = \hat{P}_{\text{max}}$ ; for permissible resistance change equivalent to 8000 h operation



## **Derating**




## 1.2 µs / 50 µs Pulse



Pulse load rating in accordance to EN 60115-1, 4.27; 1.2  $\mu$ s / 50  $\mu$ s; 5 pulses at 12 s intervals; for permissible resistance change 1 %

## 10 μs / 700 μs Pulse



Pulse load rating in accordance to EN 60115-1, 4.27; 10  $\mu$ s / 700  $\mu$ s; 10 pulses at 1 min intervals; for permissible resistance change 1 %



## **TESTS AND REQUIREMENTS**

All executed tests are carried out in accordance with the following specifications:

EN 60115-1, generic specification

EN 60115-8 (successor of EN 140400), sectional specification

EN 140401-802, detail specification

IEC 60068-2-xx, test methods

The parameters stated in the Test Procedures and Requirements table are based on the required tests and permitted limits of EN 140401-802. The table presents only the most important tests, for the full test schedule refer to the documents listed above. However, some additional tests and a number of improvements against those minimum requirements have been included.

The testing also covers most of the requirements specified by EIA/IS-703 and JIS-C-5201-1.

The tests are carried out under standard atmospheric conditions in accordance with IEC 60068-1, 4.3, whereupon the following values are applied:

Temperature: 15 °C to 35 °C Relative humidity: 25 % to 75 %

Air pressure: 86 kPa to 106 kPa (860 mbar to 1060 mbar).

A climatic category LCT / UCT / 56 is applied, defined by the lower category temperature (LCT), the upper category temperature (UCT), and the duration of exposure in the damp heat, steady state test (56 days). The components are mounted for testing on boards in accordance with EN 60115-8, 2.4.2 unless otherwise specified.

TEST PR	OCEDURES A	AND REQUIREMENTS	5		
	IEC 60068-2 <sup>(1)</sup>		PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE ( $\Delta R$ ) STABILITY CLASS 2 OR BETTER	
EN 60115-1		TEST			
CLAUSE	TEST METHOD		Stability for product types:	101.10010	
			D/CRCW-IF e3	1 Ω to 100 kΩ	
4.5	-	Resistance	-	± 5 %; ± 10 %	
4.8	-	Temperature coefficient	At (20 / -55 / 20) °C and (20 / 125 / 20) °C	± 200 ppm/K	
			$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}$ 1.5 h on; 0.5 h off		
4.25.1	-	Endurance at 70 °C	70 °C; 1000 h	± (1 % R + 0.05 Ω)	
			70 °C; 8000 h	± (2 % R + 0.1 Ω)	
4.25.3	-	Endurance at upper category temperature	155 °C; 1000 h	± (1 % R + 0.05 Ω)	
4.24	78 (Cab)	Damp heat, steady state	(40 ± 2) °C; (93 ± 3) % RH; 56 days	± (1 % R + 0.05 Ω)	
4.37	67 (Cy)	Damp heat, steady state, accelerated	$U = \sqrt{0.1 \times P_{85} \times R}; U \le 100 \text{ V};$ $U = \sqrt{0.1 \times P_{85} \times R}; U \le 100 \text{ V};$ $1000 \text{ h}$	± (1 % R + 0.05 Ω)	
4.23	-	Climatic sequence:			
4.23.2	2 (Ba)	Dry heat	125 °C; 16 h		
4.23.3	30 (Db)	Damp heat, cyclic	55 °C; 24 h; ≥ 90 % RH; 1 cycle		
4.23.4	1 (Ab)	Cold	-55 °C; 2 h	± (1 % R + 0.05 Ω)	
4.23.5	13 (M)	Low air pressure	8.5 kPa; 2 h; (25 ± 10) °C		
4.23.6	30 (Db)	Damp heat, cyclic	55 °C; 5 days; > 90 % RH; 5 cycles		
4.23.7	-	DC load	$U = \sqrt{P_{70} \times R} \le U_{\text{max.}}; 1 \text{ min}$		
-	1 (Aa)	Cold	-55 °C; 2 h	$\pm (0.25 \% R + 0.05 \Omega)$	
4.19	14 (Na)	Rapid change of temperature	30 min. at -55 °C and 30 min. at 125 °C 1000 cycles	± (1 % R + 0.05 Ω)	
4.13	-	Short time overload	$U = 2.5 \text{ x } \sqrt{(P_{70} \text{ x } R)} \le 2 \text{ x } U_{\text{max.}};$ whichever is the less severe; 5 s	± (2 % R + 0.05 Ω)	
4.27	-	Single pulse high voltage overload	Severity no. 4: $U = 10 \times \sqrt{P_{70} \times R}$ or $U \le 2 \times U_{\text{max.};}$ whichever is the less severe; 10 pulses 10 µs / 700 µs	± (1 % <i>R</i> + 0.05 Ω)	

www.vishay.com

Vishay

EN 60115-1	IEC 60068-2 <sup>(1)</sup>	TEST	PROCEDURE	REQUIREMENTS PERMISSIBLE CHANGE (\(\triangle R\))  STABILITY CLASS 2 OR BETTER	
CLAUSE	TEST METHOD		Stability for product types:	1 Ω to 100 kΩ	
			D/CRCW-IF e3	1 22 to 100 K22	
4.39	-	Periodic electric overload	$U = \sqrt{15 \times P_{70} \times R}$ $U \le 2 \times U_{\text{max.}}$ ; whichever is the less severe; 0.1 s on; 2.5 s off; 1000 cycles	$\pm$ (1 % $R$ + 0.05 $\Omega$ ) no visible damage	
4.38	-	Electrostatic discharge (human body model)	IEC 61340-3-1 <sup>(1)</sup> ; 3 positive + 3 negative discharges; ESD voltage according to the size	± (1 % R + 0.05 Ω)	
4.22	6 (Fc)	Vibration	Endurance by sweeping; 10 Hz to 2000 Hz; no resonance; amplitude ≤ 1.5 mm or ≤ 200 m/s²; 7.5 h	± (0.25 % R + 0.05 Ω) no visible damage	
4.17	58 (Td)	Solderability	Solder bath method, Sn60Pb40; non-activated flux $(235 \pm 5)$ °C; $(2 \pm 0.2)$ s Solder bath method, Sn96.5Ag3Cu0.5 or $Sn99.3Cu0.7$ ; non-activated flux $(245 \pm 5)$ °C or $(250 \pm 5)$ °C; $(3 \pm 0.3)$ s	Good tinning (≥ 95 % covered); no visible damage	
4.18	58 (Td)	Resistance to soldering heat	Soldering bath method; $(260 \pm 5)$ °C; $(10 \pm 1)$ s	± (0.25 % R + 0.05 Ω)	
4.29	45 (XA)	Component solvent resistance	Isopropyl alcohol; +50 °C; method 2	No visible damage	
4.32	21 (Ue <sub>3</sub> )	Shear (adhesion)	CRCW0402-IF: 9 N CRCW0603-IF to CRCW2512-IF: 17.7 N	No visible damage	
4.33	21 (Ue <sub>1</sub> )	Substrate bending	Depth 2 mm; 3 times	$ \begin{array}{c} \pm \ (0.25 \ \% \ R + 0.05 \ \Omega) \\ \text{no visible damage,} \\ \text{no open circuit in bent position} \end{array} $	
4.7	-	Voltage proof	$U = 1.4 \times U_{\text{ins}}$ ; 60 s	No flashover or breakdown	
4.35	-	Flammability, needle flame test	IEC 60695-11-5 <sup>(1)</sup> ; 10 s	No burning after 30 s	


## Note

<sup>(1)</sup> The quoted IEC standards are also released as EN standards with the same number and identical contents




**DIMENSIONS** 





DIMENSIONS AND MASS									
TYPE / SIZE	L (mm)	W (mm)	H (mm)	T1 (mm)	T2 (mm)	MASS (mg)			
D10/CRCW0402-IF e3	1.0 ± 0.05	$0.5 \pm 0.05$	$0.35 \pm 0.05$	0.25 ± 0.10	0.2 ± 0.10	0.65			
D11/CRCW0603-IF e3	1.55 + 0.10 / - 0.05	0.85 ± 0.1	0.45 ± 0.05	0.3 ± 0.20	$0.3 \pm 0.20$	2			
D12/CRCW0805-IF e3	2.0 + 0.20 / - 0.10	1.25 ± 0.15	0.45 ± 0.05	0.3 + 0.20 / - 0.10	0.3 ± 0.20	5.5			
D25/CRCW1206-IF e3	3.2 + 0.10 / - 0.20	1.6 ± 0.15	0.55 ± 0.05	0.45 ± 0.20	$0.4 \pm 0.20$	10			
CRCW1210-IF e3	3.2 ± 0.20	2.5 ± 0.2	0.55 ± 0.05	0.45 ± 0.20	0.4 ± 0.20	16			
CRCW2010-IF e3	5.0 ± 0.15	2.5 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	0.6 ± 0.20	25.5			
CRCW2512-IF e3	6.3 ± 0.20	3.15 ± 0.15	0.6 ± 0.10	0.6 ± 0.20	$0.6 \pm 0.20$	40.5			

## **SOLDER PAD DIMENSIONS**



RECOMMENDED SOLDER PAD DIMENSIONS								
TYPE / SIZE	WAVE SOLDERING				REFLOW SOLDERING			
	G (mm)	Y (mm)	X (mm)	Z (mm)	G (mm)	Y (mm)	X (mm)	Z (mm)
D10/CRCW0402-IF e3	-	-	=	-	0.45	0.60	0.60	1.65
D11/CRCW0603-IF e3	0.65	1.10	1.25	2.85	0.75	0.75	1.00	2.25
D12/CRCW0805-IF e3	0.90	1.30	1.60	3.50	1.00	0.95	1.45	2.90
D25/CRCW1206-IF e3	1.40	1.40	1.95	4.20	1.50	1.05	1.80	3.60
CRCW1210-IF e3	1.80	1.45	2.95	4.70	1.70	1.10	2.80	3.90
CRCW2010-IF e3	3.40	1.65	2.85	6.70	3.50	1.45	2.80	6.40
CRCW2512-IF e3	4.60	1.60	3.65	7.80	4.75	1.45	3.50	7.65

#### Note

The given solder pad dimensions reflect the considerations for board design and assembly as outlined e.g. in standards IEC 61188-5-x or in publication IPC-7351. They do not guarantee any supposed thermal properties, particularly as these are also strongly influenced by many other parameters. Still, the given solder pad dimensions will be found adequate for most general applications

The rated dissipation applies only if the permitted film temperature is not exceeded. Furthermore, a high level of ambient temperature or of
power dissipation may raise the temperature of the solder joint, hence special solder alloys or board materials may be required to maintain
the reliability of the assembly.



## **Legal Disclaimer Notice**

Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.