

Mod. 2717HL.B


2717HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Small size watertight case injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal storage for documents, tablets, small electronic devices, tools and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



INTERNAL DIMENSIONS

L LENGTH	276 mm
W WIDTH	200 mm
D DEPTH	170 mm
LID	35 mm
BASE	135 mm


EXTERNAL DIMENSIONS

L LENGTH	316 mm
W WIDTH	270 mm
D DEPTH	192 mm

OTHER DATA

WEIGHT EMPTY	1.62 Kg
WEIGHT WITH FOAM	1.89 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	9.40 lt
BUOYANCY	6.70 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	10 7/8 in
W WIDTH	7 7/8 in
D DEPTH	6 11/16 in
LID	1 3/8 in
BASE	5 5/16 in

EXTERNAL DIMENSIONS

L LENGTH	12 7/16 in
W WIDTH	10 5/8 in
D DEPTH	7 9/16 in

OTHER DATA

WEIGHT EMPTY	3.57 lbs
WEIGHT WITH FOAM	4.16 lbs
WEIGHT WITH CUSTOM FOAM	lbs
VOLUME	2.48 gal
BUOYANCY	14.77 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194