# Pan-Way® T-70 Surface Raceway System



### specifications

T-70 non-metallic multi-channel capable surface raceway shall be used to route, protect, and conceal data, voice, video, fiber optic and power cabling. The raceway shall be listed as suitable for use in applications up to 600 volts between conductors by Underwriters Laboratories, Inc. per standard 5A, and by Canadian Standards Association, Inc. per 22.2 no. 62.1-03, when screw secured and installed per instructions. A full complement of fittings with a 1" minimum bend radius compliant with TIA/EIA-568-B, must be available as well as device brackets and internal junction boxes to install a variety of communication and electrical devices. Divider walls must be available to form separate channels in the multi-channel raceway. "Snap-on" faceplates for data and power terminations shall be available. An offset box shall be available, with versions for Panduit "Snap-on" as well as "screw mount" faceplates, for mounting the power receptacle outside of the raceway channel. T-70 raceway will be manufactured from impactresistant material with flammability rating of V-0. T-70 raceway must be tamper resistant yet, also allow access for moves, adds and changes. T-70 raceway finish shall be pure color and will resist scratches and dents and will not peel or corrode. T-70 raceway shall be available in four standard colors and shall be optimized for use with the Panduit® Pan-Net® Communication System.



#### technical information

Material:	Rigid PVC
Flammability:	UL94V-0; FT4
Voltage rating:	UL-5A 600VAC; CSA C22.2 No. 62.1-03 600 V
Safety compliance:	UL Listed 95425 (raceway); UL Listed E116129 (fittings)
NEC:	Article 388
Color:	Off White (IW), Electrical Ivory (EI), White (WH)
CSI spec form:	LP-CSISPEC-T70-1

### key features and benefits

1" bend radius control fittings	Cables in the raceway will satisfy the minimum 1" bend radius requirement, preventing the potential degradation of cable performance; meets TIA/EIA standard and many warranty requirements
Snap-on faceplates	Faceplates snap directly onto the raceway base; cabling can be quickly accessed by removing only the faceplate, requiring less labor and cost of maintenance
Channel has a 70mm opening	Accepts any manufacturer's NEMA standard snap-on or screw-on power or communication faceplates
Highly tamper resistant	Very difficult for untrained personnel to enter the raceway or remove faceplates; provides maximum security for communication cabling and maximum safety for power cabling
Non-metallic construction	Lightweight reduces installer fatigue; solid color throughout profile will not chip peel, rust, corrode, or scratch; easy to cut reducing the need for special cutting devices; high impact resistance; durable
Designer profile	Aesthetically pleasing and matches a wide variety of decors
Available in three standard colors	Matches a variety of colors for various applications

### applications

Pan-Way® T-70 Non-Metallic Surface Raceway is a multi-channel channel raceway which provides solutions for routing low voltage, fiber optic and/or power cabling along perimeter walls. T-70 raceway can mount NEMA standard screw-on faceplates or superior Pan-Way® Snap-on Faceplates directly to the channel. T-70 features the Workstation Outlet Center™ Offset Box, which provides an offset solution to maximize channel capacity and outlet density.

### www.panduit.com

#### Pan-Way® T-70 Raceway

Raceway Base 6 feet:

8 feet: **T70BIW8** 10 feet: T70BIW10

**T70BIW6** 

Raceway Cover

6 feet: **T70CIW6** 8 feet: **T70CIW8** 10 feet: T70CIW10

Divider Wall

6 feet: T70DW6 8 feet: T70DW8 10 feet: T70DW10

#### T-70 Raceway Fittings and Accessories

Base coupling: T70BCIW-X Cover coupling: T70CCIW-X **Outside corner fitting:** T700CIW Inside corner fitting: T70ICIW Right angle fitting: T70RAIW End cap fitting: T70ECIW Entrance end fitting: T70EEIW Tee fitting: T70TIW Insert for tee fitting: T70TIW

Transition fitting

base/cover: T70TRIW Transition fitting cover only: T70TRCIW Wire retainer: T70WR-X

Device bracket: T70DB-X Standard faceplate bracket: T70SDB-X

Three-sided hanging box: T70HB3-X Hanging box: T70HB-X

Workstation Outlet Center™ Offset Box: T70WCIW

Workstation Outlet Center™

Offset Box:

with EI (Electrical Ivory), or WH (White).

T70WC2IW For standard colors other than IW (Off White), replace IW in part number


# **Pan-Way® T-70 Surface Raceway System**

### Wire Fill

Raceway Type and Configuration	Fill Area (in²)	Electrical Cables			Data Grade Cables									Coax Cables				Fiber Optic Cable	
		14 AWG	12 AWG	10 AWG	24 A	wg	23 A	wg	26 A	wg	23 A	wg							
		THHN/THWN/T90		Cat. 5e		Cat. 6		Cat. 6A (SD)		Cat. 6A		RG6		RG59/u		2 Strand			
		0.111	0.130	0.164	DIA =	0.193	DIA =	0.240	DIA =	0.240	DIA =	0.300	DIA =	0.275	DIA =	0.242	DIA =	0.175	
		FILL		FILL		FILL		FILL		FILL		FILL		FILL		FILL			
		MAX	MAX	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	SPEC	MAX	
		(UL Temp Rise Test)		(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)	(40%)	(60%)		
T-70: No Devices	5.15	24	20	15	70	105	45	68	45	68	29	43	34	52	44	67	85	128	
T-70: Power and data using the three-sided hanging box and device bracket	0.86	14	11	7	_	_	_	_	_	_	_	_	_	_	-	-	_	_	
	1.72	-	_	_	23	35	15	22	15	22	9	14	11	17	14	22	28	42	
T-70: Data only (Screw-on Faceplates)	3.67	-	_	_	50	75	32	48	32	48	20	31	24	37	31	47	61	91	
T-70: Data only (Snap-on Faceplates)	4.71	-	_	_	64	96	41	62	41	62	26	39	31	47	40	61	78	117	
T-70: Power and data using the Workstation Outlet Center™ Offset Box	0.91	14	11	7	-	_	_	-	-	-	_	_	_	-	-	-	_	-	
	3.12	_	_	_	42	63	27	41	27	41	17	26	21	31	27	40	51	77	


Note: For all cable options please see the Raceway Cable Fill Calculator on www.panduit.com/calculators.

### T-70 Raceway



## Pan-Way® T-70 Surface Raceway System

### Fittings and Accessories



**WORLDWIDE SUBSIDIARIES AND SALES OFFICES** 

PANDUIT US/CANADA Phone: 800.777.3300 PANDUIT EUROPE LTD. London, UK Phone: 44.20.8601.7200 PANDUIT SINGAPORE PTE. LTD. Republic of Singapore Phone: 65.6305.7575 PANDUIT JAPAN Tokyo, Japan Phone: 81.3.6863.6000 PANDUIT LATIN AMERICA Guadalajara, Mexico Phone: 52.33.3777.6000 PANDUIT AUSTRALIA PTY. LTD. Victoria, Australia Phone: 61.3.9794.9020

