

## Mod. 3317HL.B


3317HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Small size watertight case injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal storage for documents, tablets, electronic devices, tools and more.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



### INTERNAL DIMENSIONS

<b>L LENGTH</b>	330 mm
<b>W WIDTH</b>	234 mm
<b>D DEPTH</b>	170 mm
<b>LID</b>	68 mm
<b>BASE</b>	102 mm


### EXTERNAL DIMENSIONS

<b>L LENGTH</b>	360 mm
<b>W WIDTH</b>	304 mm
<b>D DEPTH</b>	192 mm

### OTHER DATA

<b>WEIGHT EMPTY</b>	1.86 Kg
<b>WEIGHT WITH FOAM</b>	2.08 Kg
<b>WEIGHT WITH CUSTOM FOAM</b>	Kg
<b>VOLUME</b>	13.10 lt
<b>BUOYANCY</b>	7.10 Kg/max
<b>OPERATING TEMPERATURE</b>	°C min -33 / max +90

IMPERIAL IN-LBS-F°



**INTERNAL DIMENSIONS**

<b>L LENGTH</b>	13 in
<b>W WIDTH</b>	9 3/16 in
<b>D DEPTH</b>	6 11/16 in
<b>LID</b>	2 11/16 in
<b>BASE</b>	4 in

**EXTERNAL DIMENSIONS**

<b>L LENGTH</b>	14 3/16 in
<b>W WIDTH</b>	11 15/16 in
<b>D DEPTH</b>	7 9/16 in

**OTHER DATA**

<b>WEIGHT EMPTY</b>	4.10 lbs
<b>WEIGHT WITH FOAM</b>	4.58 lbs
<b>WEIGHT WITH CUSTOM FOAM</b>	lbs
<b>VOLUME</b>	3.46 gal
<b>BUOYANCY</b>	15.65 lbs/max
<b>OPERATING TEMPERATURE</b>	°F min -27.4 / max +194