

Mod. 4412HL.B


4412HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE

Medium size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks. Ideal container for mechanical equipment, optical equipment and electronic devices, valuables, emergency kits and more. Can be used as a portable work station.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



INTERNAL DIMENSIONS

L LENGTH	445 mm
W WIDTH	345 mm
D DEPTH	125 mm
LID	47 mm
BASE	78 mm


EXTERNAL DIMENSIONS

L LENGTH	485 mm
W WIDTH	414 mm
D DEPTH	149 mm

OTHER DATA

WEIGHT EMPTY	2.67 Kg
WEIGHT WITH FOAM	3.17 Kg
WEIGHT WITH CUSTOM FOAM	3.47 Kg
VOLUME	19.20 lt
BUOYANCY	10.80 Kg/max
OPERATING TEMPERATURE	°C min -33 / max +90

IMPERIAL IN-LBS-F°



INTERNAL DIMENSIONS

L LENGTH	17 1/2 in
W WIDTH	13 9/16 in
D DEPTH	4 15/16 in
LID	1 7/8 in
BASE	3 1/16 in

EXTERNAL DIMENSIONS

L LENGTH	19 1/8 in
W WIDTH	16 5/16 in
D DEPTH	5 7/8 in

OTHER DATA

WEIGHT EMPTY	5.88 lbs
WEIGHT WITH FOAM	6.98 lbs
WEIGHT WITH CUSTOM FOAM	7.65 lbs
VOLUME	5.07 gal
BUOYANCY	23.80 lbs/max
OPERATING TEMPERATURE	°F min -27.4 / max +194