

## Mod. 4419HL.B

4419HL – EXPLORER CASES, ULTRALIGHT WATERPROOF CASE


Medium size watertight case, injected with proprietary copolymer PP that makes it more resistant and lightweight than other similar products. IP67 and MIL Stan certified to be resistant to impact, liquids, shocks.

Ideal container for mechanical equipment, optical equipment and electronic devices, valuables, outdoor equipment and more. Can be used as a portable work station.

- Metal reinforced padlock holes
- Single block high performance injected O-ring
- Automatic pressure valve
- Soft rubber handle grip
- Removable lid
- Anti-tilt support
- Certified to grant constant performances between -33°C and +90 °C.
- Six standard colors available



METRIC MM-KG-C°



### INTERNAL DIMENSIONS

L LENGTH	445 mm
W WIDTH	345 mm
D DEPTH	190 mm
LID	47 mm
BASE	143 mm

### EXTERNAL DIMENSIONS

L LENGTH	485 mm
W WIDTH	414 mm
D DEPTH	212 mm

### OTHER DATA


WEIGHT EMPTY	2.8 Kg
WEIGHT WITH FOAM	3.5 Kg
WEIGHT WITH CUSTOM FOAM	Kg
VOLUME	29.2 lt
BUOYANCY	19.8 Kg/max

### OPERATING

°C min -33 / max +90

TEMPERATURE

IMPERIAL IN-LBS-F°



**INTERNAL DIMENSIONS**

**EXTERNAL DIMENSIONS**

**OTHER DATA**

<b>L LENGTH</b>	17 1/2 in
<b>W WIDTH</b>	13 9/16 in
<b>D DEPTH</b>	7 1/2 in
<b>LID</b>	1 7/8 in
<b>BASE</b>	5 5/8 in

<b>L LENGTH</b>	19 1/8 in
<b>W WIDTH</b>	16 5/16 in
<b>D DEPTH</b>	8 3/8 in

<b>WEIGHT EMPTY</b>	6.17 lbs
<b>WEIGHT WITH FOAM</b>	7.71 lbs
<b>WEIGHT WITH CUSTOM FOAM</b>	lbs
<b>VOLUME</b>	7.71 gal
<b>BUOYANCY</b>	43.65 lbs/max
<b>OPERATING TEMPERATURE</b>	°F min -27.4 / max +194