



AMP | Heavy Duty Sealed Connector Series, MATEnet

TE Internal #: 9-2334935-1

Data Connectivity Housings, Housing for Male Terminals, A, Wire-to-Wire, 8 Position, .157 in [4 mm] Centerline, Heavy Duty Sealed Connector Series

[View on TE.com >](#)

Connectors > Automotive Connectors > Data Connectivity Systems > Data Connectivity Housings



Connector & Housing Type: **Housing for Male Terminals**

Mating Tab Width: .5 mm, 1.6 mm [ .019 in, .062 in ]

Mating Tab Thickness: .4 mm, .6 mm [ .015 in, .023 in ]

Connector & Keying Code: **A**

Connector System: **Wire-to-Wire**

**Features**

**Product Type Features**

Hybrid Connector	Yes
Connector & Housing Type	Housing for Male Terminals
Connector System	Wire-to-Wire
Sealable	Yes
Connector & Contact Terminates To	Wire & Cable

**Configuration Features**

Number of Positions	8
---------------------	---

**Electrical Characteristics**

Operating Voltage	60 VDC
-------------------	--------

**Body Features**

Cable Exit Type	Straight to Angled, Straight to Straight
Ferrule	With
Body Material	PBT GF
Connector & Keying Code	A



Cable Exit Angle	180°
------------------	------

### Contact Features

Center Contact	With
----------------	------

Contact Type	Tab
--------------	-----

Contact Mating Area Plating Material	Silver
--------------------------------------	--------

RF Connector Center Contact Plating Material	Silver (Ag)
--	-------------

Mating Tab Width	.5 mm, 1.6 mm [.019 in] [.062 in]
------------------	-----------------------------------

Mating Tab Thickness	.4 mm, .6 mm [.015 in] [.023 in]
----------------------	----------------------------------

Contact Current Rating (Max)	3 A, 20 A
------------------------------	-----------

### Termination Features

Termination Method to Wire & Cable	Crimp
------------------------------------	-------

### Mechanical Attachment

Mating Retention	With
------------------	------

Connector Mounting Type	Cable Mount (Free-Hanging)
-------------------------	----------------------------

### Housing Features

Housing Color	Black
---------------	-------

Centerline (Pitch)	4 mm [.157 in]
--------------------	----------------

### Dimensions

Connector Height	27 mm [1.06 in]
------------------	-----------------

Product Width	40.6 mm [1.59 in]
---------------	-------------------

Product Length	52.8 mm [2.07 in]
----------------	-------------------

### Usage Conditions

Operating Temperature (Max)	125 °C [257 °F]
-----------------------------	-----------------

Cable Type	STP, UTP
------------	----------

Operating Temperature Range	-40 – 125 °C [-40 – 257 °F]
-----------------------------	-----------------------------

### Operation/Application

Shielded	Yes
----------	-----

Circuit Application	Power & Signal
---------------------	----------------

### Industry Standards

Agency/Standard	ISO 8092
-----------------	----------

IP Rating	IP67, IP6K9K
-----------	--------------



### Packaging Features

Packaging Method	Box
------------------	-----

### Other

Outer Contact Plating Material	Nickel (Ni)
Dielectric Material	PA

### Product Compliance

[For compliance documentation, visit the product page on TE.com>](#)

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Not reviewed for solder process capability





#### Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>








### Compatible Parts









Also in the Series | **Heavy Duty Sealed Connector Series**



Also in the Series | **MATEnet**

			
<p>Automotive Connector Caps &amp; Covers (5)</p>	<p>Automotive Housings(1)</p>	<p>Automotive Seals &amp; Cavity Plugs(5)</p>	<p>Data Connectivity Headers(7)</p>
			
<p>Data Connectivity Housings(31)</p>	<p>Other Automotive Connector Accessories(1)</p>	<p>PCB Headers &amp; Receptacles(2)</p>	

### Customers Also Bought

 <p>TE Part #1563111-1 COVER,180</p>	 <p>TE Part #2112295-1 Heavy Duty Sealed Connector Series Cap</p>	 <p>TE Part #726346 SO RINGTONG 6-35</p>	 <p>TE Part #9-2331355-1 HD MATEnet 1+6 REC. HSG ASSY, GRP D</p>
 <p>TE Part #9-2334941-1 HD MATEnet 1+6 SWS, GRP D</p>	 <p>TE Part #9-2334942-1 HD MATEnet COVER FOR SWS, GRP D</p>	<p>TE Part #K1070513 Schlagschalter (Hauptantr) 06-63-410</p>	<p>TE Part #825-252-102 Antenna rod L405</p>

### Documents

#### Product Drawings

[HD MATEnet 1+6 TAB HSG. ASSY, GRP D](#)

English

#### CAD Files

[3D PDF](#)

[3D](#)

[Customer View Model](#)

[ENG\\_CVM\\_CVM\\_9-2334935-1\\_C.2d\\_dxf.zip](#)



English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2334935-1\\_C.3d\\_igs.zip](#)

English

Customer View Model

[ENG\\_CVM\\_CVM\\_9-2334935-1\\_C.3d\\_stp.zip](#)

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

**Product Specifications**

[Application Specification](#)

English