



# Part No. 1004138 GPS Ceramic Patch Antenna with LNA

1.575 GHz

Supports: Tracking, Smart Home, Agriculture, Automotive, Healthcare, Digital Signage, Wearables, Industrial Devices



# GPS Ceramic Patch Antenna with LNA

1.575 GHz

#### **KEY BENEFITS**

# Reduced Costs & Time-to-Market

Standard antennas eliminate design fees, redesign cycle time and minimize risk associated with customer solution. Quicker time to market.

## **Quicker Time-to-Market**

By optimizing antenna size, performance and emissions, customer and regulatory specifications are more easily met. Reliability

M2M, Industrial

recommended

environments

devices Smart Grid

in harsh

OBD-II

Not

Products are the latest RoHS version compliant.

#### **APPLICATIONS**

- Embedded design
- POS, Headsets, Tablets
- Gateway,
   Access Point
- Telematics
- Tracking
- Healthcare

KYOCERA AVX antennas deliver on the key needs of device designers for higher functionality and performance in smaller/thinner designs. These innovative antennas provide compelling advantages for GPS enabled handheld devices, media players and other mobile communications devices.

GPS active patch antenna solution utilizes a Low Noise Amplifier (LNA) mounted on a PCB for superior performance.

## **Electrical Specifications**

Typical characteristics in free-space

| Frequency           | 1.575 GHz              |  |
|---------------------|------------------------|--|
| Center Frequency fo | 1575.42 ± 2.0 MHz      |  |
| Bandwidth           | 10 MHz min             |  |
| Gain at Zenith      | 1.0 dBic (typ)         |  |
| Polarization        | R.H.C.P                |  |
| Impedance           | 50 ohm                 |  |
| Output VSWR         | 2.0 (typ)              |  |
| Operation Voltage   | 3.0 ± 0.1 V            |  |
| LNA/Filter Gain     | 21 ± 3 dB (DC = 3.0 V) |  |

# **Mechanical Specifications & Ordering Part Number**


| Ordering Part Number | 1004138                     |  |
|----------------------|-----------------------------|--|
| Size (mm)            | 13.0 x 13.0 x 6.8           |  |
| Mounting             | Drop-in + Cable + Connector |  |
| Weight (grams)       | 4.9                         |  |
| Packaging            | Plastic Tray                |  |
| Connector            | IPEX MHF                    |  |
| Cable (mm)           | Ø 1.13 coax , 126.0 cable   |  |



GPS Ceramic Patch Antenna with LNA KYOCERA AVX Embedded Antenna Specifications KYOCERA AVX produces a wide variety of standard and custom antennas to meet user needs.

# Filter/LNA Specifications

| Gain                     | 21 ± 3 dB (DC = 3.0 V)     |  |
|--------------------------|----------------------------|--|
| Noise Figure             | 1.5  dB typ (DC =  3.0  V) |  |
| Output VSWR              | 2.0 max (DC = 3.0 V)       |  |
| Current (DC =3.0 ± 0.1V) | 4.5 ± 1.5 mA               |  |



### **Mechanical Dimensions**

Typical antenna dimensions (mm)

| Part Number | A (mm)     | B (mm)     | C (mm)    | D (mm)      |
|-------------|------------|------------|-----------|-------------|
| 1004138     | 13.0 ± 0.2 | 13.0 ± 0.2 | 6.8 ± 0.7 | 126.0 ± 3.0 |

