

SM9336-BCE-T-250-000

✓ ACTIVE

MEAS | SMI 9000

TE Internal #: 9336-BCE-T-250-000

Digital Pressure and Altimeter Sensor Modules, Differential, 2.5 mbar, Output/Span 16 bit I2C, ±1.5% F.S, Supply Voltage 3 V, SMI 9000

[View on TE.com >](#)



Sensors > Pressure Sensors > Board Mount Pressure Sensors > Ultra-low Pressure Digital Sensor



Board Level Pressure Sensor Type: **Digital Pressure and Altimeter Sensor Modules**

Board Level Pressure Sensor Style: **Differential**

Pressure: **2.5 mbar**

Proof Pressure Range: **.07 bar**

Output/Span: **16 bit I2C**

[All Ultra-low Pressure Digital Sensor \(25\)](#)

Features

Product Type Features

Board Level Pressure Sensor Type	Digital Pressure and Altimeter Sensor Modules
Board Level Pressure Sensor Style	Differential

Configuration Features

Tubes	Barb Tube
-------	-----------

Electrical Characteristics

Board Level Pressure Sensor Supply Voltage	3 V
--	-----

Dimensions

Dimensions	10.26 x 10.31 mm[.40 x .41 in]
------------	--------------------------------

Usage Conditions

Operating Temperature Range	-20 – 85 °C[-4 – 185 °F]
-----------------------------	--------------------------

Operation/Application

Output Interface	I2C
Pressure	2.5 mbar
Proof Pressure Range	.07 bar
Output/Span	16 bit I2C



Board Level Pressure Sensor Accuracy	±1.5% F.S
--------------------------------------	-----------

Packaging Features

Package Style	Dual Vertical
Board Level Pressure Sensor Package	SOIC-16

Other

Sensor Options	No Option
----------------	-----------

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Not Yet Reviewed
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUN 2020 (209) Does not contain REACH SVHC
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not reviewed for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) ‘Guidance on requirements for substances in articles’ posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts



TE Part # 9336-BCE-S-250-000
250PA DIFF. DIGITAL PRESSURE
SENSOR

TE Part # CAT-BLPS0063
Low Pressure Digital / Analog Sensor

Also in the Series | SMI 9000

Board Mount Pressure Sensors(25)

Customers Also Bought

TE Part #9236-BCE-T-600-002
Ultra-low Pressure Digital Sensor

TE Part #5420E-100-A-P-T
100 PSIA SO-8 PRESSURE SENSOR

TE Part #1321-BCE-S-015-000
15PSI DIFFERENTIAL SENSOR

TE Part #1321-BCE-T-015-000
15psi Differential Sensor

TE Part #SM3041-005-S-C-3-T
5 PSIG I2C SO16

TE Part #4321-BCE-T-350-000
Differential, -350 to 350mmHg

TE Part #5421-BCE-T-110-000
-10 to 110cmH2O Asymmetric

TE Part #7321-BCE-T-010-000
10CMH2O DIFFERENTIAL SENSOR

TE Part #9541-010C-D-C-3-T
PRESSURE 0.15 PSID I2C SO16



Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_9336-BCE-T-250-000_1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_9336-BCE-T-250-000_1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_9336-BCE-T-250-000_1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

SM9000

English