


DRAWING NUMBER **IISM3-T2**  
 PAGE 1 OF 1  
 REPLACES  
 CHECK  
 REVISIONS  
**A** CO22077  
 GCH 6 DEC 66  
**B** CO29449  
 SRH 23 FEB 72  
**C** CO-82803-B  
 CSL 6 SEP 96  
**D** CO-95172  
 JJA 23 JUNE 99  
**E** CO-95691  
 GJW 3 DEC 99  
 CHECK  
 LSD 21 DEC '66  
 CHECK  
 GCH 6 DEC 66  
 DRAWN  
**FORMTEK**



**NOTE -**  
 ▲ - MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA ON .375 ±.002 CENTERS  
 2 - TERMINALS ARE PLATED FOR SOLDERING  
 3 - SWITCH WILL WITHSTAND TEMPERATURE OF 250° F

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

CHARACTERISTICS	ELECTRICAL DATA	SCALE 2 TO 1
OPERATING FORCE ----- 3 - 5 OZ	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
RELEASE FORCE ----- 1 OZ MIN	30 VOLTS DC RATING	UNLESS OTHERWISE NOTED
DIFFERENTIAL TRAVEL ----- .004 MAX	INDUCTIVE ----- SEA LEVEL ----- 3 AMP	DIMENSIONS ARE IN INCHES
OVERTRAVEL ----- .005 MIN	50,000 FT ----- 2.5 AMP	<b>TOLERANCES ARE:</b>
	RESISTIVE ----- SEA LEVEL ----- 5 AMP	ONE PLACE (.0) ±.030
	50,000 FT ----- 5 AMP	TWO PLACE (.00) ±.015
	MAXIMUM INRUSH ----- 24 AMP	THREE PLACE (.000) ±.005
		ANGLES ±
	UNDERWRITERS' LAB. INC. LISTED RATING	WEIGHT .006 LB MAX
	5 A - 250 VAC	

