

OSRAM SPL PL90AT03

Datasheet

Preliminary datasheet version

Published by **ams-OSRAM AG**

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved



Radial T1 3/4

SPL PL90AT03

Pulsed Laser Diode in Plastic Package 75 W Peak Power



Applications

- 3D Sensing
- Robotics

Features

- Laser wavelength 905 nm
- Suited for short laser pulses from 1 to 100 ns
- Contact width 70 μm
- Cost effective plastic package for high volume applications

Ordering Information

Type	Peak output power typ. $I_F = 25 \text{ A}; t_p = 30 \text{ ns}; f = 1 \text{ kHz}; T_A = 25 \text{ }^\circ\text{C}$ P_{opt}	Ordering Code
SPLPL90AT03	75 W	Q65113A5477

Maximum Ratings

$T_A = 25\text{ °C}$

Parameter	Symbol	Values
Operating temperature	T_{op}	min. -40 °C max. 85 °C
Storage temperature	T_{stg}	min. -40 °C max. 100 °C
Peak output power ¹⁾	P_{opt}	max. 75 W
Forward current	I_F	max. 25 A
Pulse width (FWHM)	t_p	max. 30 ns
Duty cycle	D	max. 0.1 %
Soldering temperature	T_s	max. 260 °C
$t_{max} = 10\text{ }\mu\text{s}$		


Characteristics

 $I_F = 8 \text{ A}$; $t_p = 100 \text{ ns}$; $T_A = 25 \text{ °C}$

Parameter	Symbol		Values
Operating voltage	V_{op}	typ.	6 V
Peak wavelength ²⁾	λ_{peak}	min. typ. max.	898 nm 905 nm 912 nm
Spectral bandwidth (FWHM)	$\Delta\lambda$	typ.	5 nm
Peak output power ¹⁾	P_{opt}	min. typ. max.	20 W 25 W 30 W
Beam divergence (FWHM) parallel to pn-junction	$\Theta_{ }$	typ.	12 °
Beam divergence (FWHM) perpendicular to pn-junction	Θ_{\perp}	typ.	25 °
Threshold current	I_{th}	typ.	0.3 A
Temperature coefficient of wavelength	TC_{λ}	typ.	0.28 nm / K
Temperature coefficient of optical power	TC_P	typ.	-0.4 % / K
Thermal resistance junction ambient real	R_{thJA}	typ.	200 K / W


Relative Spectral Emission ³⁾, ⁴⁾

$$I_{e,rel} = f(\lambda); I_F = 25 \text{ A}; P_{opt} = 75 \text{ W}; t_p = 30 \text{ ns}$$




Far-Field Distribution Parallel to pn-Junction ³⁾, ⁴⁾

$$I_{rel} = f(\Theta_{II}); P_{opt} = 75 \text{ W}; t_p = 30 \text{ ns}; f = 1 \text{ kHz}$$




Far-Field Distribution Perpendicular to pn-Junction 3), 4)

$I_{rel} = f(\Theta_{\perp}); P_{opt} = 75W; t_p = 30ns; f = 1kHz$




Optical Output Power 3), 4)

$P_{opt} = f(I_F); t_p = 30 ns; f = 1 kHz$




Forward Voltage 3), 4)

$V_F = f(I_F); t_p = 30 ns; f = 1 kHz$



Preliminary datasheet version

Dimensional Drawing ⁵⁾



C67062-A0447-A1-01

Further Information:

Approximate Weight: 241.0 mg

Package marking: Anode

Notes

Depending on the mode of operation, these devices emit highly concentrated visible and non visible light which can be hazardous to the human eye. Products which incorporate these devices have to follow the safety precautions given in IEC 60825-1.

Subcomponents of this device contain, in addition to other substances, metal filled materials including silver. Metal filled materials can be affected by environments that contain traces of aggressive substances. Therefore, we recommend that customers minimize device exposure to aggressive substances during storage, production, and use. Devices that showed visible discoloration when tested using the described tests above did show no performance deviations within failure limits during the stated test duration. Respective failure limits are described in the IEC60810.

For further application related information please visit www.osram-os.com/appnotes

Disclaimer

AMS OSRAM assumes no liability whatsoever for any use of this document or its content by recipient including, but not limited to, for any design in activities based on this preliminary draft version. AMS OSRAM may e.g. decide at its sole discretion to stop developing and/or finalizing the underlying design at any time.

Attention please!

The information describes the type of component and shall not be considered as assured characteristics. Terms of delivery and rights to change design reserved. Due to technical requirements components may contain dangerous substances.

For information on the types in question please contact our Sales Organization.

If printed or downloaded, please find the latest version on our website.

Packing

Please use the recycling operators known to you. We can also help you – get in touch with your nearest sales office. By agreement we will take packing material back, if it is sorted. You must bear the costs of transport. For packing material that is returned to us unsorted or which we are not obliged to accept, we shall have to invoice you for any costs incurred.

Product and functional safety devices/applications or medical devices/applications

Our components are not developed, constructed or tested for the application as safety relevant component or for the application in medical devices.

Our products are not qualified at module and system level for such application.

In case buyer – or customer supplied by buyer – considers using our components in product safety devices/ applications or medical devices/applications, buyer and/or customer has to inform our local sales partner immediately and we and buyer and /or customer will analyze and coordinate the customer-specific request between us and buyer and/or customer.

Glossary

- 1) **Brightness:** The brightness values are measured with a tolerance of $\pm 11\%$.
- 2) **Wavelength:** The wavelengths are measured with a tolerance of ± 1 nm.
- 3) **Typical Values:** Due to the special conditions of the manufacturing processes of semiconductor devices, the typical data or calculated correlations of technical parameters can only reflect statistical figures. These do not necessarily correspond to the actual parameters of each single product, which could differ from the typical data and calculated correlations or the typical characteristic line. If requested, e.g. because of technical improvements, these typ. data will be changed without any further notice.
- 4) **Testing temperature:** TA = 25°C (unless otherwise specified)
- 5) **Tolerance of Measure:** Unless otherwise noted in drawing, tolerances are specified with ± 0.1 and dimensions are specified in mm.

Revision History

Version	Date	Change
0.0	2023-01-18	Initial Version

Preliminary datasheet version



EU RoHS and China RoHS compliant product

此产品符合欧盟 RoHS 指令的要求；
按照中国的相关法规和标准，
不含有毒有害物质或元素。

Published by ams-OSRAM AG

Tobelbader Strasse 30, 8141 Premstaetten, Austria

Phone +43 3136 500-0

ams-osram.com

© All rights reserved

am 

OSRAM