

## Specification Sheet

Part Number: 151-04038



No drilling or extra hardware required – just secure to steel surface.

Magnetic mounts are reliable even in debris, dirt, and oil.

Use for permanent mounting or as a temporary installation tool.

Reuse and reposition capabilities allow for a flexible mounting solution.

Easily remove without residue.

Magnetic Bridle Ring, Large, 2" Dia Ring, Neodymium Magnet/Steel, 90lb Pull Force, 100/Box

Article Number	151-04038
----------------	-----------

Type	MAGBR90L
------	----------

Color	Metal (ML)
-------	------------

Quantity Per	box
--------------	-----

Product Description	<p>Magnetic bridle rings route cables by securing to steel surfaces without the need for a mounting hole. Simply attach cables within the bridle ring and position the magnet onto the beam, metal joist, ceiling channel, conveyor frame, or other steel surface. Magnetic bridle rings are ideal for supporting communication and data cables. The mounts are simple to secure and can attach to surfaces contaminated with oil or debris. Ultra-strong neodymium magnets are ideal as a permanent mount or for temporary applications. Reuse and reposition them for ultimate flexibility without needing to replace or repurchase parts.</p>
---------------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Short Description	Magnetic Bridle Ring, Large, 2" Dia Ring, Neodymium Magnet/Steel, 90lb Pull Force, 100/Box
Global Part Name	MAGBR90L-NDFEB45/ST-ML
Fixation Method	Magnet
Height H (Imperial)	3.84
Height H (Metric)	97.63
Diameter D (Imperial)	1.57
Diameter D (Metric)	40
Material	Steel (ST) Neodymium alloy 45M (NDFEB45)
Material Shortcut	ST NDFEB45
Halogen Free	Yes
UV Resistant (Yes/No)	No
Operating Temperature	-40°F to +176°F (-40°C to +80°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes

Package Quantity (Imperial)	100
Package Quantity (Metric)	100
Customs Number	8505110070

## About HellermannTyton

HellermannTyton is a global manufacturer of cable management and identification solutions for automotive, solar, electrical, construction, industrial automation, broadband and other OEM markets. The company's integrated approach to product design, sustainability, production, quality assurance and delivery is optimized to benefit local and global customers. HellermannTyton operates in 39 countries, with North American headquarters in Milwaukee, Wisconsin. ([www.hellermann.tyton.com](http://www.hellermann.tyton.com)).

© 2023 HellermannTyton. All Rights Reserved.

[Contact Us](#)

[RoHS/WEEE Compliance](#)

[Disclaimer](#)

[Terms and Conditions](#)