BENEFITS OF USING CAPACITOR ARRAYS

KYOCERA AVX capacitor arrays offer designers the opportunity to lower placement costs, increase assembly line output through lower component count per board and to reduce real estate requirements.

Reduced Costs

Placement costs are greatly reduced by effectively placing one device instead of four or two. This results in increased throughput and translates into savings on machine time. Inventory levels are lowered and further savings are made on solder materials, etc.

Space Saving

Space savings can be quite dramatic when compared to the use of discrete chip capacitors. As an example, the 0508 4-element array offers a space reduction of >40% vs. 4 x 0402 discrete capacitors and of >70% vs. 4 x 0603 discrete capacitors. (This calculation is dependent on the spacing of the discrete components.)

Increased Throughput

Assuming that there are 220 passive components placed in a mobile phone:

A reduction in the passive count to 200 (by replacing discrete components with arrays) results in an increase in throughput of approximately 9%.

A reduction of 40 placements increases throughput by 18%.


For high volume users of cap arrays using the very latest placement equipment capable of placing 10 components per second, the increase in throughput can be very significant and can have the overall effect of reducing the number of placement machines required to mount components:

KYOCERa

If 120 million 2-element arrays or 40 million 4-element arrays were placed in a year, the requirement for placement equipment would be reduced by one machine.

During a 20Hr operational day a machine places 720K components. Over a working year of 167 days the machine can place approximately 120 million. If 2-element arrays are mounted instead of discrete components, then the number of placements is reduced by a factor of two and in the scenario where 120 million 2-element arrays are placed there is a saving of one pick and place machine.


Smaller volume users can also benefit from replacing discrete components with arrays. The total number of placements is reduced thus creating spare capacity on placement machines. This in turn generates the opportunity to increase overall production output without further investment in new equipment.



W2A (0508) Capacitor Arrays

The 0508 4-element capacitor array gives a PCB space saving of over 40% vs four 0402 discretes and over 70% vs four 0603 discrete capacitors.


W3A (0612) Capacitor Arrays



The 0612 4-element capacitor array gives a PCB space saving of over 50% vs four 0603 discretes and over 70% vs four 0805 discrete capacitors.

KINCERENTIAL The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.






GENERAL DESCRIPTION


KYOCERA AVX is the market leader in the development and manufacture of capacitor arrays. The array family of products also includes the 0612 4-element device as well as 0508 2-element and 4-element series, all of which have received widespread acceptance in the marketplace.

KYOCERA AVX capacitor arrays are available in X5R, X7R and NP0 (C0G) ceramic dielectrics to cover a broad range of capacitance values. Voltage ratings from 6.3 Volts up to 100 Volts are offered. KYOCERA AVX also now offers a range of automotive capacitor arrays qualified to AEC-Q200 (see separate table).

Key markets for capacitor arrays are Mobile and Cordless Phones, Digital Set Top Boxes, Computer Motherboards and Peripherals as well as Automotive applications, RF Modems, Networking Products, etc.



HOW TO ORDER



KUDEERA The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-SMDMLCC-0011 | Rev 1



	SIZE		W	2 = 05	08	W3 = 0612		2
# F	# Elements			4			4	
	oldering		Re	flow/Wa		Reflow/Wave		
	ackaqinq			er/Embo				
	uokuqiiiq	mm		1.30 ± 0.1		Paper/Embossed 1.60 ± 0.150		
Length		(in.)	(0.	051 ± 0.0	06)	(0.0	063 ± 0.00)6)
Width		mm (in)		2.10 ± 0.1			126 ± 0.20	
Max.		(in.) mm	(0.	083 ± 0.0 0.94	00)	(0.	126 ± 0.00 1.35	(00
Thicknes	ss	(in.)		(0.037)			(0.053)	
	WVDC		16	25	50	16	25	50
1R0	Сар	1.0						
1R2	(pF)	1.2						
1R5		1.5						
1R8		1.8						
2R2		2.2						
2R7		2.7						
3R3		3.3						
3R9		3.9						
4R7		4.7						
5R6 6R8		5.6 6.8						
8R2 100		8.2 10						
120		10						
150		12						
180		18						
220		22						
270		27						
330		33						
390		39						
470		47						
560		56						
680		68						
820		82						
101		100						
121		120						
151		150						
181		180						
221		220						
271 331		270 330						
331		330 390						
471		390 470						
561		470 560						
681		680						
821		820						
102		1000						
122		1200						
152		1500						
182		1800						
222		2200						
272		2700						
332		3300						7
392		3900						
472		4700						
562		5600						
682		6800						
822		8200						



= Supported Values

KUCERE KWXC The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-SMDMLCC-0011 | Rev 1

Capacitor Array Capacitance Range – X7R



SIZE				N2 =	050	8			V	V2 =	050	8			V	V3 =	061	2	
# Elements					2						4						1		
	Soldering			Reflow	_	/e			F		//Wav	e		Reflow/Wave					
	Packaging				Paper						mboss			Paper/Embossed					
Longet	mm				± 0.15	5					± 0.15						0.150		-
Lengt	n (in.)		(0.051	± 0.00)6)			(0	0.051	± 0.00	6)			(0.063 ± 0.006)				
Width	mm			2.10	± 0.15	5				2.10	± 0.15					3.20 :	± 0.20		
	(in.)		(0.083)6)			(0		± 0.00	6)			(0		± 0.00	8)	
Max.	mm				.94						94						35		
Thick					037)	1 = -	1		1)37)						53)		1
4.04	WVDC	6	10	16	25	50	100	6	10	16	25	50	100	6	10	16	25	50	100
101	Cap (pF) 100																		<u> </u>
121	120																		
151 181	150 180																		
221	220																		
271	220																		-
331	330																		
391	330		-																-
471	470		1		<u> </u>	1													
561	560	-			1	1	1												
681	680																		+
751	750																		
821	820																		
102	1000																		
122	1200								1										
152	1500																		
182	1800																		
222	2000																		
272	2700																		
332	3300																		
392	3900																		
472	4700																		
562	5600																		
682	6800																		
822	8200																		
103	Сар (µF) 0.010																		<u> </u>
153	0.015																		<u> </u>
183	0.018											<u> </u>							<u> </u>
223 273	0.022				<u> </u>								<u> </u>						-
	0.027																		
333 393	0.033				<u> </u>				<u> </u>										<u> </u>
473	0.039																		<u> </u>
563	0.047																		
683	0.050																		
823	0.082						<u> </u>												
104	0.100											<u> </u>							+
154	0.150																		<u> </u>
224	0.220					1	1		1			1	1						<u> </u>
274	0.270																		
334	0.330		1			1	1		1			1							
394	0.390		1	İ		1	1		1	İ	İ				İ		İ		
474	0.470		1		1	1	1			ĺ	ĺ		1		ĺ				
564	0.560																		
684	0.680																		
824	0.820																		
105	1.000																		Γ

KUCERE KWXC The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

TDS-SMDMLCC-0011 | Rev 1

Capacitor Array Automotive Capacitor Array (IPC)







As the market leader in the development and manufacture of capacitor arrays KYOCERA AVX is pleased to offer a range of AEC-Q200 qualified arrays to compliment our product offering to the Automotive industry. Both the KYOCERA AVX 0612 and 0508 4-element capacitor array styles are qualified to the AEC-Q200 automotive specifications.


AEC-Q200 is the Automotive Industry qualification standard and a detailed qualification package is available on request. All KYOCERA AVX automotive capacitor array production facilities are certified to ISO/TS 16949:2002.

HOW TO ORDER



*Contact factory for availability by part number for K = ±10% and J = ±5% tolerance.






*Not RoHS Compliant



KUDEERA The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.



PART & PAD LAYOUT DIMENSIONS



PART DIMENSIONS

0508 - 2 Element

L	W	Т	BW	BL	Р	S
1.30 ± 0.15	2.10 ± 0.15	0.94 MAX	0.43 ± 0.10	0.33 ± 0.08	1.00 REF	0.50 ± 0.10
(0.051 ± 0.006)	(0.083 ± 0.006)	(0.037 MAX)	(0.017±0.004)	(0.013 ± 0.003)	(0.039 REF)	(0.020 ± 0.004)

0508 - 4 Element

L	W	Т	BW	BL	Р	Х	S
1.30 ± 0.15	2.10 ± 0.15	0.94 MAX	0.25 ± 0.06	0.20 ± 0.08	0.50 REF	0.75 ± 0.10	0.25 ± 0.10
(0.051 ± 0.006) (0.083 ± 0.006)	(0.037 MAX)	(0.010 ± 0.003)	(0.008 ± 0.003)	(0.020 REF)	(0.030 ± 0.004)	(0.010 ± 0.004)

0612 - 4 Element

L	w	Т	BW	BL	Р	Х	S
1.60 ± 0.20	3.20 ± 0.20	1.35 MAX	0.41 ± 0.10		0.76 REF	1.14 ± 0.10	0.38 ± 0.10
(0.063 ± 0.008)	(0.126 ± 0.008)	(0.053 MAX)	(0.016 ± 0.004)	(0.007+0.010) -0.003	(0.030 REF)	(0.045 ± 0.004)	(0.015±0.004)

PAD LAYOUT DIMENSIONS

0508 - 2 Element

Α	В	C	D	E
0.68	1.32	2.00	0.46	1.00
(0.027)	(0.052)	(0.079)	(0.018)	(0.039)

0508 - 4 Element	0508 -	4 Element
------------------	--------	-----------

Α	В	С	D	E
0.56	1.32	1.88	0.30	0.50
(0.022)	(0.052)	(0.074)	(0.012)	(0.020)

0612 - 4 Element

Α	В	С	D	E
0.89	1.65	2.54	0.46	0.76
(0.035)	(0.065)	(0.100)	(0.018)	(0.030)

KUCERE The Important Information/Disclaimer is incorporated in the catalog where these specifications came from or available online at www.kyocera-avx.com/disclaimer/ by reference and should be reviewed in full before placing any order.

millimeters (inches)