3-1703843-2 - ACTIVE

AMP | Heavy Duty Sealed Connector Series

TE Internal #: 3-1703843-2 Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Green, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]

View on TE.com >



Connectors > Automotive Connectors > Automotive Housings > Heavy Duty Sealed Connector Series Housings



Connector & Housing Type: Housing for Male Terminals

Mating Tab Width: 1.6 mm [.063 in]

Connector System: Wire-to-Wire

Number of Positions: 2

Centerline (Pitch): 4 mm [.157 in]

All Heavy Duty Sealed Connector Series Housings (204)

Features

Product Type Features

| Connector Shape | Rectangular | |
|------------------------------|----------------------------|--|
| Connector & Housing Type | Housing for Male Terminals | |
| Connector System | Wire-to-Wire | |
| Sealable | Yes | |
| Hybrid Connector | No | |
| Primary Locking Feature | On the Terminal | |
| Configuration Features | | |
| Number of Positions | 2 | |
| Number of Rows | 1 | |
| Electrical Characteristics | | |
| Operating Voltage | 60 VDC | |
| Nominal Voltage Architecture | 12 V, 24 V, 42 V, 60 V | |

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Green, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



Body Features

| Cable Exit Angle | 180°, 90° |
|------------------------------|------------------|
| Primary Product Color | Green |
| Connector & Keying Code | С |
| Contact Features | |
| Contact Size | 1.6mm |
| Contact Type | Tab |
| Mating Tab Width | 1.6 mm[.063 in] |
| Contact Current Rating (Max) | 20 A |
| Mechanical Attachment | |
| Terminal Position Assurance | Yes |
| Strain Relief | Add By Accessory |
| Mating Alignment Type | Keyed |
| Mating Alignment | With |
| Connector Mounting Type | Panel Mount |
| Housing Features | |

Housing Material

4 mm[.157 in]

PBT GF

Dimensions

| Connector Height | 29.8 mm[1.173 in] | |
|-----------------------------|--|--|
| Product Width | 47.05 mm[1.852 in] | |
| Product Length | 37.5 mm[1.476 in] | |
| Usage Conditions | | |
| Operating Temperature (Max) | 70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 ° F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F] | |
| Operating Temperature Range | -40 – 140 °C[-40 – 284 °F] | |
| Operation/Application | | |
| Circuit Application | Signal | |
| Industry Standards | | |
| Degree of Protection | IP67 | |
| UL Flammability Rating | UL 94V-0 | |

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Green, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



Packaging Features

| Packaging Quantity | 450 |
|--------------------------------------|--------|
| Packaging Method | Carton |
| Other | |
| Serviceable | Yes |
| Connector Position Assurance Capable | No |

Product Compliance

For compliance documentation, visit the product page on TE.com>

| EU RoHS Directive 2011/65/EU | Compliant |
|---|--|
| EU ELV Directive 2000/53/EC | Compliant |
| China RoHS 2 Directive MIIT Order No 32, 2016 | No Restricted Materials Above Threshold |
| EU REACH Regulation (EC) No. 1907/2006 | Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC |
| Halogen Content | Not Low Halogen - contains Br or Cl > 900 ppm. |
| | |


Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked.Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE's information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) 'Guidance on requirements for substances in articles' (Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of 'complex object', the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA "Guidance on requirements for substances in articles" (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Green, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]








TE Part # 2-964269-2 TAB A 1.6x0.6 CONTACT CF SWS Ag

Also in the Series | Heavy Duty Sealed Connector Series

| Automotive Connector Caps & Covers (25) | Automotive Housings(207) | Automotive Seals & Cavity Plugs(5) | Data Connectivity Headers(2) |
|--|--------------------------|------------------------------------|------------------------------|



Documents

& For support call+1 800 522 6752

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Green, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



CAD Files Customer View Model ENG_CVM_3-1703843-2_C.3d_igs.zip English Customer View Model ENG_CVM_3-1703843-2_C.3d_stp.zip English Customer View Model ENG_CVM_3-1703843-2_C.2d_dxf.zip English 3D PDF English

Product Specifications Application Specification

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

English