

AMP | Heavy Duty Sealed Connector Series

TE Internal #: 1-1670730-2 Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Black, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]

View on TE.com >



Connectors > Automotive Connectors > Automotive Housings > Heavy Duty Sealed Connector Series Housings



Connector & Housing Type: Housing for Male Terminals

Mating Tab Width: 1.5 mm [.059 in]

Connector System: Wire-to-Wire

Number of Positions: 2

Centerline (Pitch): 4 mm [.157 in]

All Heavy Duty Sealed Connector Series Housings (204)

Features

Product Type Features

Connector Shape	Rectangular	
Connector & Housing Type	Housing for Male Terminals	
Connector System	Wire-to-Wire	
Sealable	Yes	
Hybrid Connector	No	
Primary Locking Feature	On the Terminal	
Configuration Features		
Number of Positions	2	
Number of Rows	1	
Electrical Characteristics		
Electrical Characteristics Operating Voltage	60 VDC	

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Black, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



Body Features

Cable Exit Angle	180°, 90°	
Primary Product Color	Black	
Connector & Keying Code	A	
Contact Features		
Contact Size	1.6mm	
Contact Type	Tab	
Mating Tab Width	1.5 mm[.059 in]	
Mechanical Attachment		
Terminal Position Assurance	Yes	
Strain Relief	Add By Accessory	
Mating Alignment Type	Keyed	
Mating Alignment	With	
Connector Mounting Type	Panel Mount	
Housing Features		
Housing Material	PBT GF	

Dimensions

Connector Height	19 mm[.748 in]	
Product Width	47.05 mm[1.852 in]	
Product Length	27.6 mm[1.087 in]	
Usage Conditions		
Operating Temperature (Max)	70 °C, 80 °C, 85 °C, 90 °C, 100 °C, 105 °C, 110 °C, 120 °C, 125 °C, 130 °C, 140 °C[158 ° F][167 °F][176 °F][185 °F][194 °F][212 °F][221 °F][230 °F][248 °F][257 °F][266 °F][284 °F]	
Operating Temperature Range	-40 – 140 °C[-40 – 284 °F]	
Operation/Application		
Circuit Application	Signal	
Industry Standards		
Degree of Protection	IP67	
UL Flammability Rating	UL 94V-0	
Packaging Features		

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Black, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



Packaging Quantity	1
Packaging Method	Carton
Other	
Serviceable	Yes
Connector Position Assurance Capable	No

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant	
EU ELV Directive 2000/53/EC	Compliant	
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold	
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JAN 2023 (233) Does not contain REACH SVHC	
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.	
Solder Process Capability	Not reviewed for solder process capability	

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Black, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]








TE Part # 2-964269-2 TAB A 1.6x0.6 CONTACT CF SWS Ag

Also in the Series | Heavy Duty Sealed Connector Series

Automotive Connector Caps & Covers (25)	Automotive Housings(207)	Automotive Seals & Cavity Plugs(5)	Data Connectivity Headers(2)



Documents

& For support call+1 800 522 6752

Housing for Male Terminals, Wire-to-Wire, 2 Position, .157 in [4 mm] Centerline, Sealable, Black, Signal, Panel Mount, -40 – 284 °F [-40 – 140 °C]



CAD Files

3D PDF

3D

Customer View Model ENG_CVM_CVM_1-1670730-2_H.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_1-1670730-2_H.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_1-1670730-2_H.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Specifications Product Specification

English