

Page 1 of 3

# RH100-12.288-18-2030-EXT-TR


# • SPECIFICATIONS

PARAMETER	VALUE
NOMINAL FREQUENCY	12.288 MHz
MODE OF OSCILLATION	Fundamental
FREQUENCY TOLERANCE AT 25°C	±20 ppm max
FREQUENCY STABILITY OVER TEMPERATURE	±30 ppm max
OPERATING TEMPERATURE RANGE	-40°C to +85°C
STORAGE TEMPERATURE RANGE	-40°C to +85°C
AGING	±5 ppm per year max
LOAD CAPACITANCE	18 pF
EQUIVALENT SERIES RESISTANCE	100 Ω max
SHUNT CAPACITANCE	5 pF max
DRIVE LEVEL	100 µW max




Photo is not actual part

# MECHANICAL SPECIFICATION



# • CARRIER TAPE DIMENSIONS



NOTE: REFER TO EIA-481 FOR DIMENSIONS

#### PACKAGING

178 mm REEL DIAMETER 8 mm TAPE WIDTH, 4 mm PITCH QUANTITY: 3000 PIECES PER REEL

IN ACCORDANCE WITH EIA-481




#### SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 2 of 3

# RH100-12.288-18-2030-EXT-TR

### • **REFLOW PROFILE**



Reflow profile				
Temperature Min Preheat	T <sub>SMIN</sub>	125°C		
Temperature Max Preheat	T <sub>SMAX</sub>	150°C		
Time (T <sub>SMIN</sub> to T <sub>SMAX</sub> )	ts	60-180 sec.		
Temperature	TL	217°C		
Peak Temperature	T <sub>P</sub>	260°C		
Ramp-up rate	R <sub>UP</sub>	3°C/sec max.		
Ramp-down rate	R <sub>DOWN</sub>	6°C/sec max.		
Time within 5°C of Peak Temperature	t <sub>P</sub>	10 sec.		
Time t[25°C] to Peak Temperature	t[25°C] to Peak	480 sec.		
Time	tL	60-150 sec.		

#### ENVIRONMENTAL

PARAMETER	VALUE
MOISTURE SENSITIVITY LEVEL	1
RoHS	Compliant
REACH SVHC	Compliant
HALOGEN-FREE	Compliant
ESD CLASSIFICATION LEVEL	N/A
TERMINATION FINISH	Au





#### SURFACE MOUNT MICROPROCESSOR CRYSTAL

Page 3 of 3

## RH100-12.288-18-2030-EXT-TR

## MARKING

R12.28 xxBDyw

- x Internal Production ID code
- y Year code
- w-Week code

YEAR CODE		
Year	Code	
2011	1	
2012	2	
2013	3	
2014	4	
2015	5	
2016	6	
2017	7	
2018	8	
2019	9	

	ALPHA WEEK CODE TABLE				
Week	Code	Week	Code	Week	Code
1	а	19	8	37	K
2	b	20	t	38	L
3	с	21	u	39	М
4	d	22	v	40	Ν
5	e	23	w	41	0
6	f	24	х	42	Р
7	g	25	у	43	Q
8	h	26	Z	44	R
9	i	27	А	45	S
10	j	28	В	46	Т
11	k	29	С	47	U
12	1	30	D	48	V
13	m	31	E	49	W
14	n	32	F	50	Х
15	0	33	G	51	Y
16	р	34	Н	52	Z
17	q	35	I		
18	r	36	J		

#### APPROVAL

DRAWN BY	KJackson, January 24, 2017
APPROVED BY	Jlvens, January 24, 2017
REVISION	A, Initial Release

Raltron Electronics / RAMI Technology USA, LLC, including its affiliates, employees, agents and other persons acting on its behalf (collectively Raltron/RAMI Tech), disclaim any and all liability for any errors or inaccuracies contained in this data sheet. While Raltron/RAMI Tech has made every reasonable effort ensure the accuracy of all product information, specifications and data contained herein, Raltron/RAMI Tech hoes not guarantee that the information is accurate, reliable or current. The product information is provided only for reference purposes only and is subject to change, correction or revision, at any time withhout notice. Raltron/RAMI Tech hoes not guarantee that the information is accurate, reliable of an application or use of any product described herein and disclaims any warranties expressed or implied. The user of products in such applications shall assume all risks of such use and will agree to hold Raltron/RAMI Tech, hamless against all damages.

Copyright © 2016, Raltron Electronics / RAMI Technology USA, LLC. All rights reserved. No part of this document may be reproduced in any form without the prior written permission of Raltron Electronics / RAMI Technology USA, LLC.