

Features

- Universal Input 100~240VAC 50/60Hz
- IEC/EN/ANSI/AAMI ES 60601-1 (ED 3.1)
- EMC: IEC60601-1-2:2014(ED 4.0)
- Safety Approvals: cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH
- Means of Protection: 2 X MOPP
- Touch Current: <100μA
- Regulated Output with Low Ripple Noise
- Safety Agency Requirements and EMI/EMS Certified
- No Load Power Consumption <0.21W
- Meets DoE Level VI, Energy Star, ErP Stage 2
- IEC C14 Connector



Ideal Power's 44ATM160T-Pxyz 160W AC/DC External Desktop Power Supply (PSU)Series are certified to cULus / UKCA / CB / PSE / FCC / CE / TUV / RoHS / REACH & IEC 60601-1-2:2014(ED 4.0) Standards and comply with (EU) 2019/1782, Level VI Efficiency Regulations. These are primarily used in Medical, ITE, Audio & Video Industries and customised solutions are available upon request.

| Models | | | |
|----------------|------------------------|---------------------|-------------------|
| Model Number | Output Voltage V DC | Output Current A | Output Power W |
| 44ATM160T-P120 | 12 | 12.5 | 150 |
| 44ATM160T-P240 | 24 | 6.6 | 158.4 |
| 44ATM160T-P480 | 48 | 3.3 | 158.4 |

| Switched Mode Power Supply |
|--|
| IEC 320-C14 |
| 4 Pin Kycon |
| 1 |
| VI |
| Desktop |
| 300,000 hours calculated at 25°C, by Telcoria SR-332 |
| LED Indicator for power on |
| 1200mm(±30mm) – 1500mm(±30mm) Depending on Model |
| 16AWG/18AWG/20AWG (Depending on model) |
| Yes |
| |



Mechanical Specifications

| Housing Material | Fully Enclosed Plastic Case |
|--------------------|-----------------------------|
| Overall Dimensions | 183mm x 81mm x 42mm |
| Overall Length | 183mm |
| Overall Height | 42mm |
| Overall Width | 81mm |
| Weight | 820g |

Input Specifications

| Rated Input Voltage | 100~240Vac (±10%) |
|---------------------|--|
| Rated Frequency | 50/60Hz |
| Efficiency Level VI | Level VI / Efficiency (EU) 2019/1782 |
| Input Current | 1.8A-0.9A |
| Inrush Current | 100A Max. / 230Vac (Cold Start At 25°C, Full Load) |
| Touch Current | Less than 100μA |
| Input Protection | Internal Primary Current Fuse |

Output Specifications

| ±5% |
|--|
| 240 mV for 12V Model, 480 mV for 24V Model, 960 mV for 48V Model |
| ±5% |
| ±5% |
| <0.21W |
| 1 |
| 1 |
| Primary to Secondary 4,000Vac for 1 Minutes |
| 10MΩ for 500Vdc |
| Auto-recovery |
| V out * 150% MAX., latch off |
| I out * 150% MAX., auto-recovery |
| |

Protection Category

| Means of Protection |
|---------------------|

Approvals

| Compliance/Certifications | CB / cULus/ FCC / CE / UKCA / T-mark / TUV / PSE |
|--|--|
| Safety Standard IEC/EN/ANSI/AAMI ES 60601-1 | |
| EMC Emission: Directive 93/42/EEC (EN 60601-1-2) | |



