

## Features

- Universal Input 85~264VAC / 120~370 VDC 50/60Hz
- Output Voltages: 5-24V DC
- IEC/UL/EN 60950-1
- Meets the latest Safety Standards and Approvals
- Single Output to 15W
- High Efficiency
- 100% Full load burn-in Test
- Low Ripple & Noise
- Class II
- Protection: Overload/Over voltage/Short circuit
- Dimensions: 58 x 18 x 90mm
- Weight: 78g



Ideal Power's 56YSD15S-xy 15W DIN Rail Mount AC/DC Power Supply Converter Series are certified to cURus, CE, RoHS & IEC/UL/EN62368 Standards and comply with (EU) 2019/1782, Level VI Efficiency Regulations. These are primarily used in ITE, Audio & Video Industries and customised solutions are available upon request.

### Models

Model Number	Output Voltage	Output Current	Output Power
56YSD15S-0502400	5V DC	2.4A	12W
56YSD15S-1201250	12V DC	1.25A	15W
56YSD15S-1501000	15V DC	1A	15W
56YSD15S-2400630	24V DC	0.63A	15W

### General Specification

Type	DIN Rail Power Supply
AC or DC Input Voltage	AC
AC or DC Output Voltage	DC
Number of Outputs	1
Mounting Style	Din Rail Mount
Connection Type	Screw Terminal Type
Overload Protection	>130%-200% rated output power (Hiccup mode, recovers automatically after fault condition is re-moved)
Over Current Protection	110% - 180%
Short Circuit Protection	Protection to Zero Voltage
Over Voltage Protection	110~145% (Protection Type: Clamp by zener diode)

**Mechanical Specifications**

Housing Material	Fully Enclosed Plastic Case
Overall Dimensions	58mm x 18mm x 90mm
Overall Length	90mm
Overall Depth	58mm
Overall Width	18mm
Weight	78g

**Input Specifications**

Input Electrical Phase	Single
Line Frequency	50-60Hz
Inrush Current	25 Amps max. at 115VAC/60Hz,full load & 45Amps max. at 240VAC/50Hz,full load
AC Current	0.5A/115VAC 0.25A/230VAC
Efficiency Type	79~86% Depending on Model
Leakage Current	<0.25mA/240VAC

**Output Specifications**

Output Voltage Adjustment	+/- 10% Depending on Model
Ripple and Noise	80~150 mV Depending on Model
Line Regulation	± 1%
Load Regulation	± 1%
Isolation Resistance	I/P-O/P:100M Ohms / 500VDC / 25 / 70% RH
Setup, Rise, Hold Up time	2S/80mS/15mS(115V/60HZ MAX ROAD), 1S/80mS/30mS(230V/50HZ MAX ROAD)
MTBF	200000 h

**Operational Environment**

Operating Humidity	20% ~ 90% RH non-condensing
Operating Temperature Range	-20°C to 50°C, Full load, Normal operation.
Storage Temperature Range	-40°C to 80°C
Storage Humidity	10% ~ 90% RH
Cooling	Cooling

**Protection Category**



IP Rating	IP20
-----------	------

### Approvals


Safety Standard	UL60950-1, UL508, , BSMI CNS14336-1,TUV EN61558-2-16 IEC60950-1, EAC TPTC 004,TUV EN60950-1
EMC Emissions	EN55032(CISPR32), CNS13438 Class B ,EN61000-3-2 Class A ,EN61000-3-3,EN61000-4-2,3,4,5,6,8,11, EN55024, EN55035, EN61000-6-2, EN61204-3

### Mechanical Drawing

#### ■ Dimensions and Installation:



#### ■ Deduction curve and temperature:



#### ■ Minus output and input voltage curves:

