



SAFETY DATA SHEET
DDP SPECIALTY ELECTRONIC MATERIALS
US 9, LLC

Product name: MOLYKOTE® P-74 Assembly Paste

Issue Date: 11/25/2020

Print Date: 06/23/2023

DDP SPECIALTY ELECTRONIC MATERIALS US 9, LLC encourages and expects you to read and understand the entire (M)SDS, as there is important information throughout the document. We expect you to follow the precautions identified in this document unless your use conditions would necessitate other appropriate methods or actions.

1. IDENTIFICATION

Product name: MOLYKOTE® P-74 Assembly Paste

Recommended use of the chemical and restrictions on use

Identified uses: Lubricants and lubricant additives

COMPANY IDENTIFICATION

DDP SPECIALTY ELECTRONIC MATERIALS
US 9, LLC
974 Centre Road
Wilmington DE 19805
UNITED STATES

Customer Information Number:

833-338-7668
SDSQuestion-NA@dupont.com

EMERGENCY TELEPHONE NUMBER

24-Hour Emergency Contact: 1-800-424-9300

Local Emergency Contact: 800-424-9300

2. HAZARDS IDENTIFICATION

Hazard classification

GHS classification in accordance with 29 CFR 1910.1200
Not a hazardous substance or mixture.

Other hazards

No data available

3. COMPOSITION/INFORMATION ON INGREDIENTS

Chemical nature: Inorganic and organic compounds, Mixture

This product is a mixture.

Component	CASRN	Concentration
------------------	--------------	----------------------

Paraffin oils

8012-95-1

>= 10.0 - <= 20.0 %

4. FIRST AID MEASURES

Description of first aid measures

General advice:

First Aid responders should pay attention to self-protection and use the recommended protective clothing (chemical resistant gloves, splash protection). If potential for exposure exists refer to Section 8 for specific personal protective equipment.

Inhalation: Move person to fresh air; if effects occur, consult a physician.

Skin contact: Wash off with plenty of water. Suitable emergency safety shower facility should be available in work area.

Eye contact: Wash immediately and continuously with flowing water for at least 30 minutes. Remove contact lenses after the first 5 minutes and continue washing. Obtain prompt medical consultation, preferably from an ophthalmologist. Suitable emergency eye wash facility should be immediately available.

Ingestion: No emergency medical treatment necessary.

Most important symptoms and effects, both acute and delayed:

Aside from the information found under Description of first aid measures (above) and Indication of immediate medical attention and special treatment needed (below), any additional important symptoms and effects are described in Section 11: Toxicology Information.

Indication of any immediate medical attention and special treatment needed

Notes to physician: Chemical eye burns may require extended irrigation. Obtain prompt consultation, preferably from an ophthalmologist. No specific antidote. Treatment of exposure should be directed at the control of symptoms and the clinical condition of the patient.

5. FIREFIGHTING MEASURES

Suitable extinguishing media: Water spray Alcohol-resistant foam Carbon dioxide (CO₂) Dry chemical

Unsuitable extinguishing media: None known.

Special hazards arising from the substance or mixture

Hazardous combustion products: Carbon oxides Metal oxides Oxides of phosphorus Nitrogen oxides (NO_x)

Unusual Fire and Explosion Hazards: Exposure to combustion products may be a hazard to health.

Advice for firefighters

Fire Fighting Procedures: Fire residues and contaminated fire extinguishing water must be disposed of in accordance with local regulations.

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment. Use water spray to cool unopened containers. Collect contaminated fire extinguishing water separately. This must not be discharged into drains. Remove undamaged containers from fire area if it is safe to do so. Evacuate area.

Special protective equipment for firefighters: In the event of fire, wear self-contained breathing apparatus. Use personal protective equipment.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures: Use personal protective equipment. Follow safe handling advice and personal protective equipment recommendations.

Environmental precautions: Discharge into the environment must be avoided. Prevent further leakage or spillage if safe to do so. Retain and dispose of contaminated wash water. Local authorities should be advised if significant spillages cannot be contained.

Methods and materials for containment and cleaning up: Wipe up or scrape up and contain for salvage or disposal. Local or national regulations may apply to releases and disposal of this material, as well as those materials and items employed in the cleanup of releases. You will need to determine which regulations are applicable. For large spills, provide dyking or other appropriate containment to keep material from spreading. If dyked material can be pumped, Sections 13 and 15 of this SDS provide information regarding certain local or national requirements. See sections: 7, 8, 11, 12 and 13.

7. HANDLING AND STORAGE

Precautions for safe handling: Do not get on skin or clothing. Do not swallow. Do not get in eyes. Keep container tightly closed. Take care to prevent spills, waste and minimize release to the environment. Handle in accordance with good industrial hygiene and safety practice. Use only with adequate ventilation. See Engineering measures under EXPOSURE CONTROLS/PERSONAL PROTECTION section.

Conditions for safe storage: Keep in properly labelled containers. Keep tightly closed. Store in accordance with the particular national regulations.

Do not store with the following product types: Strong oxidizing agents.
Unsuitable materials for containers: None known.

8. EXPOSURE CONTROLS/PERSONAL PROTECTION

Control parameters

If exposure limits exist, they are listed below. If no exposure limits are displayed, then no values are applicable.

Component	Regulation	Type of listing	Value
Paraffin oils	OSHA P0	TWA	5 mg/m ³
	OSHA Z-1	TWA	5 mg/m ³
	ACGIH		See Further information
Further information: URT irr: Upper Respiratory Tract irritation; *: 2019 Adoption; L: Exposure by all routes should be carefully controlled to levels as low as possible.; A2:			

	Suspected human carcinogen		
	OSHA Z-1	TWA Mist	5 mg/m3
	ACGIH	TWA Inhalable particulate matter	5 mg/m3
	Further information: URT irr: Upper Respiratory Tract irritation; A4: Not classifiable as a human carcinogen		
	CAL PEL	PEL particulate	5 mg/m3
	Further information: (I): As sampled by method that does not collect vapor.		
	OSHA P0	TWA Mist	5 mg/m3
	NIOSH REL	TWA Mist	5 mg/m3
	NIOSH REL	ST Mist	10 mg/m3

Although some of the components of this product may have exposure guidelines, no exposure would be expected under normal handling conditions due to the physical state of the material.

Exposure controls

Engineering controls: Use local exhaust ventilation, or other engineering controls to maintain airborne levels below exposure limit requirements or guidelines. If there are no applicable exposure limit requirements or guidelines, general ventilation should be sufficient for most operations. Local exhaust ventilation may be necessary for some operations.

Individual protection measures

Eye/face protection: Use chemical goggles.

Skin protection

Hand protection: Use gloves chemically resistant to this material. Examples of preferred glove barrier materials include: Chlorinated polyethylene. Neoprene. Nitrile/butadiene rubber ("nitrile" or "NBR"). Polyethylene. Ethyl vinyl alcohol laminate ("EVAL"). Polyvinyl alcohol ("PVA"). Viton. Examples of acceptable glove barrier materials include: Butyl rubber. Natural rubber ("latex"). Polyvinyl chloride ("PVC" or "vinyl"). **NOTICE:** The selection of a specific glove for a particular application and duration of use in a workplace should also take into account all relevant workplace factors such as, but not limited to: Other chemicals which may be handled, physical requirements (cut/puncture protection, dexterity, thermal protection), potential body reactions to glove materials, as well as the instructions/specifications provided by the glove supplier.

Other protection: Use protective clothing chemically resistant to this material. Selection of specific items such as face shield, boots, apron, or full body suit will depend on the task.

Respiratory protection: Respiratory protection should be worn when there is a potential to exceed the exposure limit requirements or guidelines. If there are no applicable exposure limit requirements or guidelines, wear respiratory protection when adverse effects, such as respiratory irritation or discomfort have been experienced, or where indicated by your risk assessment process. In dusty or misty atmospheres, use an approved particulate respirator.

The following should be effective types of air-purifying respirators: Organic vapor cartridge with a particulate pre-filter.

9. PHYSICAL AND CHEMICAL PROPERTIES

Appearance

Physical state	paste
Color	dark grey
Odor	slight
Odor Threshold	No data available

pH	Not applicable
Melting point/range	No data available
Freezing point	No data available
Boiling point (760 mmHg)	Not applicable
Flash point	Not applicable
Evaporation Rate (Butyl Acetate = 1)	Not applicable
Flammability (solid, gas)	Not classified as a flammability hazard
Lower explosion limit	No data available
Upper explosion limit	No data available
Vapor Pressure	Not applicable
Relative Vapor Density (air = 1)	No data available
Relative Density (water = 1)	1.3
Water solubility	No data available
Partition coefficient: n-octanol/water	No data available
Auto-ignition temperature	No data available
Decomposition temperature	No data available
Dynamic Viscosity	Not applicable
Kinematic Viscosity	Not applicable
Explosive properties	Not explosive
Oxidizing properties	The substance or mixture is not classified as oxidizing.
Molecular weight	No data available
Particle size	No data available

NOTE: The physical data presented above are typical values and should not be construed as a specification.

10. STABILITY AND REACTIVITY

Reactivity: Not classified as a reactivity hazard.

Chemical stability: Stable under normal conditions.

Possibility of hazardous reactions: Can react with strong oxidizing agents.

Conditions to avoid: None known.

Incompatible materials: Oxidizing agents

Hazardous decomposition products: 1-Butene.

11. TOXICOLOGICAL INFORMATION

Toxicological information appears in this section when such data is available.

Acute toxicity

Acute oral toxicity

Product test data not available. Refer to component data.

Acute dermal toxicity

Product test data not available. Refer to component data.

Acute inhalation toxicity

Product test data not available. Refer to component data.

Skin corrosion/irritation

Product test data not available. Refer to component data.

Serious eye damage/eye irritation

Product test data not available. Refer to component data.

Sensitization

Product test data not available. Refer to component data.

Specific Target Organ Systemic Toxicity (Single Exposure)

Product test data not available. Refer to component data.

Specific Target Organ Systemic Toxicity (Repeated Exposure)

Product test data not available. Refer to component data.

Carcinogenicity

Product test data not available. Refer to component data.

Teratogenicity

Product test data not available. Refer to component data.

Reproductive toxicity

Product test data not available. Refer to component data.

Mutagenicity

Product test data not available. Refer to component data.

Aspiration Hazard

Product test data not available. Refer to component data.

COMPONENTS INFLUENCING TOXICOLOGY:

Paraffin oils

Acute oral toxicity

May cause abdominal discomfort or diarrhea.

For similar material(s): LD50, Rat, > 5,000 mg/kg OECD Test Guideline 401

Acute dermal toxicity

For similar material(s): LD50, Rabbit, > 5,000 mg/kg OECD Test Guideline 402

Acute inhalation toxicity

Vapors are unlikely due to physical properties. Excessive exposure to mineral oil mist may cause lung injury (lipoid pneumonia).

Prolonged excessive exposure to mist may cause adverse effects. Excessive exposure may cause irritation to upper respiratory tract (nose and throat).

For similar material(s): LC50, Rat, 4 Hour, dust/mist, > 5 mg/l OECD Test Guideline 403

Skin corrosion/irritation

Brief contact is essentially nonirritating to skin.
Prolonged contact may cause skin irritation with local redness.
Repeated contact may cause skin irritation with local redness.

Serious eye damage/eye irritation

May cause slight eye irritation.
May cause slight temporary corneal injury.

Sensitization

One type of mineral oil (CAS 8042-47-5) has caused skin sensitization in guinea pigs.

Did not cause allergic skin reactions when tested in guinea pigs.

Specific Target Organ Systemic Toxicity (Single Exposure)

Evaluation of available data suggests that this material is not an STOT-SE toxicant.

Specific Target Organ Systemic Toxicity (Repeated Exposure)

In animals, effects have been reported on the following organs after ingestion:

Kidney.

Liver.

Spleen.

Excessive repeated exposure to mineral oil mist may produce lung injury.

Carcinogenicity

Did not cause cancer in laboratory animals.

Available data are inadequate to evaluate carcinogenicity. IARC has classified untreated and mildly-treated mineral oils as Group 1 (sufficient evidence for carcinogenicity in humans) and highly refined oils as Group 3 (not classifiable as to its carcinogenicity).

Teratogenicity

Relevant data not available.

Reproductive toxicity

Relevant data not available.

Mutagenicity

For similar material(s): In vitro genetic toxicity studies were negative.

Aspiration Hazard

May be fatal if swallowed and enters airways.

Carcinogenicity Component	List	Classification
Paraffin oils	ACGIH	A2: Suspected human carcinogen

12. ECOLOGICAL INFORMATION

Ecotoxicological information appears in this section when such data is available.

Toxicity

Paraffin oils

Acute toxicity to fish

Material is practically non-toxic to aquatic organisms on an acute basis (LC50/EC50/EL50/LL50 >100 mg/L in the most sensitive species tested).

LC50, Pimephales promelas (fathead minnow), > 100 mg/l

LC50, Lepomis macrochirus (Bluegill sunfish), 96 Hour, > 10,000 mg/l

Acute toxicity to aquatic invertebrates

For similar material(s):

EL50, Daphnia magna (Water flea), 48 Hour, 1,000 - 10,000 mg/l

Acute toxicity to algae/aquatic plants

For similar material(s):

EL50, Pseudokirchneriella subcapitata (green algae), 72 Hour, > 100 mg/l

Persistence and degradability

Paraffin oils

Biodegradability: Material is expected to be readily biodegradable.

10-day Window: Pass

Biodegradation: 82 %

Exposure time: 24 d

Method: OECD Test Guideline 301F

Chemical Oxygen Demand: 1.45 - 3.01 mg/mg

Bioaccumulative potential

Paraffin oils

Bioaccumulation: Bioconcentration potential is moderate (BCF between 100 and 3000 or Log Pow between 3 and 5).

Partition coefficient: n-octanol/water(log Pow): > 3.5 Estimated.

Mobility in soil

Paraffin oils

Expected to be relatively immobile in soil (Koc > 5000).

Partition coefficient (Koc): > 5000 Estimated.

13. DISPOSAL CONSIDERATIONS

Disposal methods: DO NOT DUMP INTO ANY SEWERS, ON THE GROUND, OR INTO ANY BODY OF WATER. All disposal practices must be in compliance with all Federal, State/Provincial and local laws and regulations. Regulations may vary in different locations. Waste characterizations and compliance with applicable laws are the responsibility solely of the waste generator. AS YOUR SUPPLIER, WE HAVE NO CONTROL OVER THE MANAGEMENT PRACTICES OR MANUFACTURING PROCESSES OF PARTIES HANDLING OR USING THIS MATERIAL. THE INFORMATION PRESENTED HERE PERTAINS ONLY TO THE PRODUCT AS SHIPPED IN ITS INTENDED CONDITION AS DESCRIBED IN MSDS SECTION: Composition Information. FOR UNUSED & UNCONTAMINATED PRODUCT, the preferred options include sending to a licensed, permitted: Incinerator or other thermal destruction device. For additional information, refer to: Handling & Storage Information, MSDS Section 7 Stability & Reactivity Information, MSDS Section 10 Regulatory Information, MSDS Section 15

Treatment and disposal methods of used packaging: Empty containers should be recycled or otherwise disposed of by an approved waste management facility. Waste characterizations and compliance with applicable laws are the responsibility solely of the waste generator. Do not re-use containers for any purpose.

14. TRANSPORT INFORMATION

DOT

Not regulated for transport

Classification for SEA transport (IMO-IMDG):

	Not regulated for transport
Transport in bulk according to Annex I or II of MARPOL 73/78 and the IBC or IGC Code	Consult IMO regulations before transporting ocean bulk

Classification for AIR transport (IATA/ICAO):

Not regulated for transport

This information is not intended to convey all specific regulatory or operational requirements/information relating to this product. Transportation classifications may vary by container volume and may be influenced by regional or country variations in regulations. Additional transportation system information can be obtained through an authorized sales or customer service representative. It is the responsibility of the transporting organization to follow all applicable laws, regulations and rules relating to the transportation of the material.

15. REGULATORY INFORMATION

Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Sections 311 and 312

No SARA Hazards

Superfund Amendments and Reauthorization Act of 1986 Title III (Emergency Planning and Community Right-to-Know Act of 1986) Section 313

This material does not contain any chemical components with known CAS numbers that exceed the threshold (De Minimis) reporting levels established by SARA Title III, Section 313.

Comprehensive Environmental Response, Compensation, and Liability Act of 1980 (CERCLA) Section 103

This material does not contain any components with a CERCLA RQ.

Pennsylvania Right To Know

The following chemicals are listed because of the additional requirements of Pennsylvania law:

Components	CASRN
1-Decene, homopolymer, hydrogenated	68037-01-4
Graphite	7782-42-5
Paraffin oils	8012-95-1
Calcium hydroxide	1305-62-0
Hydroxylapatite	1306-06-5
Alkyl Quaternary Ammonium Montmorillonite	68953-58-2
Alkyl Acid Ether	Not available
Polybutene No aspiration hazard	9003-29-6
Distillates (petroleum), hydrotreated heavy naphthenic	64742-52-5
Distillates, petroleum, hydrotreated heavy paraffinic	64742-54-7
Distillates, petroleum, hydrotreated light paraffinic	64742-55-8
Solvent dewaxed heavy paraffinic distillates	64742-65-0

California Prop. 65

This product contains a chemical that is at or below California Propositions 65's "safe harbor level" as determined via a risk assessment. Therefore, the chemical is not required to be listed as a Prop 65 chemical on the SDS or label.

United States TSCA Inventory (TSCA)

All components of this product are in compliance with the inventory listing requirements of the U.S. Toxic Substances Control Act (TSCA) Chemical Substance Inventory.

16. OTHER INFORMATION

Hazard Rating System

NFPA

Health	Flammability	Instability
3	1	0

HMIS

Health	Flammability	Physical Hazard
0/	1	0

Revision

Identification Number: 4045295 / A776 / Issue Date: 11/25/2020 / Version: 8.0

Most recent revision(s) are noted by the bold, double bars in left-hand margin throughout this document.

Legend

ACGIH	USA. ACGIH Threshold Limit Values (TLV)
CAL PEL	California permissible exposure limits for chemical contaminants (Title 8, Article 107)
NIOSH REL	USA. NIOSH Recommended Exposure Limits
OSHA P0	USA. OSHA - TABLE Z-1 Limits for Air Contaminants - 1910.1000
OSHA Z-1	USA. Occupational Exposure Limits (OSHA) - Table Z-1 Limits for Air Contaminants
PEL	Permissible exposure limit
ST	STEL - 15-minute TWA exposure that should not be exceeded at any time during a workday
TWA	8-hour time weighted average

Full text of other abbreviations

AICS - Australian Inventory of Chemical Substances; AIIC - Australian Inventory of Industrial Chemicals; ASTM - American Society for the Testing of Materials; bw - Body weight; CERCLA - Comprehensive Environmental Response, Compensation, and Liability Act; CMR - Carcinogen, Mutagen or Reproductive Toxicant; DIN - Standard of the German Institute for Standardisation; DOT - Department of Transportation; DSL - Domestic Substances List (Canada); ECx - Concentration associated with x% response; EHS - Extremely Hazardous Substance; ELx - Loading rate associated with x% response; EmS - Emergency Schedule; ENCS - Existing and New Chemical Substances (Japan); ErCx - Concentration associated with x% growth rate response; ERG - Emergency Response Guide; GHS - Globally Harmonized System; GLP - Good Laboratory Practice; HMIS - Hazardous Materials Identification System; IARC - International Agency for Research on Cancer; IATA - International Air Transport Association; IBC - International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk; IC50 - Half maximal inhibitory concentration; ICAO - International Civil Aviation Organization; IECSC - Inventory of Existing Chemical Substances in China; IMDG - International Maritime Dangerous Goods; IMO - International Maritime Organization; ISHL - Industrial Safety and Health Law (Japan); ISO - International Organisation for Standardization; KECI - Korea Existing Chemicals Inventory; LC50 - Lethal Concentration to 50 % of a test population; LD50 - Lethal Dose to 50% of a test population (Median Lethal Dose); MARPOL - International Convention for the Prevention of Pollution from Ships; MSHA - Mine Safety and Health Administration; n.o.s. - Not Otherwise Specified; NFPA - National Fire Protection Association; NO(A)EC - No Observed (Adverse) Effect Concentration; NO(A)EL - No Observed (Adverse) Effect Level; NOELR - No Observable Effect Loading Rate; NTP - National Toxicology Program; NZIoC - New Zealand Inventory of Chemicals; OECD - Organization for Economic Co-operation and Development; OPPTS - Office of Chemical Safety and Pollution Prevention; PBT - Persistent, Bioaccumulative and Toxic substance; PICCS - Philippines Inventory of Chemicals and Chemical Substances; (Q)SAR - (Quantitative) Structure Activity Relationship; RCRA - Resource Conservation and Recovery Act; REACH - Regulation (EC) No 1907/2006 of the European Parliament and of the Council concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals; RQ - Reportable Quantity; SADT - Self-Accelerating Decomposition Temperature; SARA - Superfund Amendments and Reauthorization Act; SDS - Safety Data Sheet; TCSI - Taiwan Chemical Substance Inventory; TSCA - Toxic Substances Control Act (United States); UN - United Nations; UNRTDG - United Nations Recommendations on the Transport of Dangerous Goods; vPvB - Very Persistent and Very Bioaccumulative

Information Source and References

This SDS is prepared by Product Regulatory Services and Hazard Communications Groups from information supplied by internal references within our company.

DDP SPECIALTY ELECTRONIC MATERIALS US 9, LLC urges each customer or recipient of this (M)SDS to study it carefully and consult appropriate expertise, as necessary or appropriate, to become aware of and understand the data contained in this (M)SDS and any hazards associated with the product. The information herein is provided in good faith and believed to be accurate as of the effective date shown above. However, no warranty, express or implied, is given. Regulatory requirements are subject to change and may differ between various locations. It is the buyer's/user's responsibility to ensure that his activities comply with all federal, state, provincial or local laws. The information presented here pertains only to the product as shipped. Since conditions for use of the product are not under the control of the manufacturer, it is the buyer's/user's duty to determine the conditions necessary for the safe use of this product. Due to the proliferation of sources for information such as manufacturer-specific (M)SDSs, we are not and cannot be responsible for (M)SDSs obtained from any source other than ourselves. If you have obtained an (M)SDS from another source or if you are not sure that the (M)SDS you have is current, please contact us for the most current version.

US