

16 1614 05

Power supply connectors





Power supply chassis socket acc. to JEITA RC-5320A JSBJ5, straight version, with break contact and solder eyes, for front side mounting

1 of 3 03/2023
















*a port in mounting plate

Environmental conditions

Temperature range -20 °C/+70 °C

Materials

Insulating body

Contact

Cu alloy, silver-plated/tin-plated
Insulation

PBT (may be PF in a transitional phase)

Hexagonal nut PA

Mechanical data

Diameter opening7,0 mmDiameter insulation4,0 mmDiameter central hole1,45 mmMating cycles≥ 5000Insertion force≤ 30 NWithdrawal force3-30 N

Electrical data (at Tamb 20 °C)

 $\begin{array}{lll} \mbox{Contact resistance} & \leq 30 \ \mbox{m}\Omega \\ \mbox{Rated current} & 2 \ \mbox{A} \\ \mbox{Rated voltage} & 18 \ \mbox{V DC} \\ \mbox{Rated impulse voltage} & 500 \ \mbox{V/60 s} \\ \mbox{Insulation resistance} & \geq 100 \ \mbox{M}\Omega \\ \end{array}$

Associated products

Counterparts

☐ 1636 05



16 1614 05

Designation	Pole Number	PU (Pieces)	MDQ (Pieces)
1614 05	2	250	500

Packaging:

in bulk, in a cardboard box or a plastic bag

3 of 3 03/2023