
# Onsemi

## **MOSFET** – N-Channel, **Shielded Gate, POWERTRENCH<sup>®</sup> 150 V, 62 A, 12.4 m**Ω



# **FDMS86255**

#### Description


This N-Channel MOSFET is produced using onsemi advanced POWERTRENCH process that incorporates Shielded Gate technology. This process has been optimized for the on-state resistance and yet maintain superior switching performance.

#### Features

- Shielded Gate MOSFET Technology
- Max  $R_{DS(on)} = 12.4 \text{ m}\Omega$  at  $V_{GS} = 10 \text{ V}$ ,  $I_D = 10 \text{ A}$
- Max  $R_{DS(on)} = 15.5 \text{ m}\Omega$  at  $V_{GS} = 6 \text{ V}$ ,  $I_D = 8 \text{ A}$
- Advanced Package and Silicon Combination for Low R<sub>DS(on)</sub> and High Efficiency
- Next Generation Enhanced Body Diode Technology, Engineered for Soft Recovery
- MSL1 Robust Package Design
- 100% UIL Tested
- RoHS Compliant
- These Device is Halogen Free

#### Applications

- OringFET / Load Switching
- Synchronous Rectification
- DC-DC Conversion



#### **MARKING DIAGRAM**



= Logo

\$Y

&K

- &Z = Assembly Location &З
  - = Date Code (Year and Week)
  - = Specific Device Code

#### **ORDERING INFORMATION**

See detailed ordering and shipping information on page 6 of this data sheet.

#### MOSFET MAXIMUM RATINGS $T_{A}$ = 25 $^{\circ}\mathrm{C}$ unless otherwise noted

Symbol	Parameter	Rating	Unit
V <sub>DS</sub>	Drain to Source Voltage	150	V
$V_{GS}$	Gate to Source Voltage	±20	V
I <sub>D</sub>	Drain Current Continuous, $T_C = 25^{\circ}C$	62	А
	Continuous, T <sub>A</sub> = 25°C (Note 1a)	10	
	Pulsed (Note 4)	271	
E <sub>AS</sub>	Single Pulse Avalanche Energy (Note 3)	541	mJ
PD	Power Dissipation, $T_C = 25^{\circ}C$		W
	Power Dissipation, $T_A = 25^{\circ}C$ (Note 1a)	2.7	
T <sub>J,</sub> T <sub>STG</sub>	Operating and Storage Junction Temperature Range	-55 to +150	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

#### THERMAL CHARACTERISTICS

Symbol	Parameter	Rating	Unit
$R_{\theta JC}$	Thermal Resistance, Junction to Case	1.1	°C/W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient (Note 1a)	45	

### **ELECTRICAL CHARACTERISTICS** $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
OFF CHAR	ACTERISTICS	·				
BV <sub>DSS</sub>	Drain to Source Breakdown Voltage	$I_D = 250 \ \mu A, \ V_{GS} = 0 \ V$	150	-	-	V
$\frac{\Delta BV_{DSS}}{\Delta T_{J}}$	Breakdown Voltage Temperature Coefficient	$I_D$ = 250 µA, referenced to 25°C	-	109	-	mV/°C
I <sub>DSS</sub>	Zero Gate Voltage Drain Current	V <sub>DS</sub> = 120 V, V <sub>GS</sub> = 0 V	-	-	1	μA
I <sub>GSS</sub>	Gate to Source Leakage Current	$V_{GS} = \pm 20$ V, $V_{DS} = 0$ V	-	-	±100	nA
ON CHARA	CTERISTICS	·				
VGS(th)	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}, I_D = 250 \ \mu A$	2.0	3.0	4.0	V
$\Delta VGS(th) \Delta T_J$	Gate to Source Threshold Voltage Temperature Coefficient	$I_D = 250 \ \mu\text{A}$ , referenced to $25^{\circ}\text{C}$	-	-11	-	mV/°C
R <sub>DS(ON)</sub>	Static Drain to Source On Resistance	V <sub>GS</sub> = 10 V, I <sub>D</sub> = 10 A	-	9.5	12.4	mΩ
		V <sub>GS</sub> = 6 V, I <sub>D</sub> = 8 A	-	11.5	15.5	7
		V <sub>GS</sub> = 10 V, I <sub>D</sub> = 10 A, T <sub>J</sub> = 125°C	-	19	25	
<b>9</b> FS	Forward Transconductance	V <sub>DS</sub> = 5 V, I <sub>D</sub> = 10 A	-	35	-	S
DYNAMIC (	CHARACTERISTICS					
C <sub>ISS</sub>	Input Capacitance	$V_{DS} = 75 \text{ V}, \text{ V}_{GS} = 0 \text{ V},$	-	3200	4480	pF
C <sub>OOS</sub>	Output Capacitance	f = 1 MHz	-	291	410	pF
Crss	Reverse Transfer Capacitance	1	-	11	20	pF
R <sub>g</sub>	Gate Resistance		0.1	0.7	2.1	Ω
SWITCHING		·	•	-	-	-
	<b>T O D I T</b>		-	1	1	T

t <sub>d(on)</sub>	Turn-On Delay Time		$V_{DD}$ = 75 V, I_D = 10 A, $V_{GS}$ = 10 V, $R_{GEN}$ = 6 $\Omega$		21	34	ns
tr	Rise Time	$V_{GS} = 10 V, R_{GEN} = 0$			4.5	10	ns
t <sub>d(off)</sub>	Turn-Off Delay Time				28	45	ns
t <sub>f</sub>	Fall Time				6.2	12	ns
Qg	Total Gate Charge	$V_{GS}$ = 0 V to 10 V	V <sub>DD</sub> = 75 V,	-	45	63	nC
Qg	Total Gate Charge	$V_{GS} = 0 V \text{ to } 6 V$	$V_{GS} = 0 V \text{ to } 6 V$ $I_D = 10 \text{ A}$		29	41	nC


#### **ELECTRICAL CHARACTERISTICS** (continued) $T_A = 25^{\circ}C$ unless otherwise noted

Symbol	Parameter	Test Conditions	Min.	Тур.	Max.	Unit
SWITCHING CHARACTERISTICS						
Qgs	Gate to Source Charge		-	14	-	nC
Qgd	Gate to Drain "Miller" Charge		_	8.8	_	nC
DRAIN-SOURCE DIODE CHARACTERISTICS						
Ven	Source to Drain Diode Forward	Voo = 0 V Io = 1 9 A (Note 2)	_	0.7	12	V

$V_{SD}$	Source to Drain Diode Forward	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 1.9 A (Note 2)	-	0.7	1.2	V
	Voltage	V <sub>GS</sub> = 0 V, I <sub>S</sub> = 10 A (Note 2)	-	0.8	1.3	
t <sub>rr</sub>	Reverse Recovery Time	$I_F = 10 \text{ A}, \text{ di/dt} = 100 \text{ A/}\mu\text{s}$	-	87	139	ns
Q <sub>rr</sub>	Reverse Recovery Charge		-	165	264	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

1. R<sub>0JA</sub> is determined with the device mounted on a 1 in<sup>2</sup> pad 2 oz copper pad on a 1.5 x 1.5 in. board of FR-4 material. R<sub>0JC</sub> is guaranteed by design while  $R_{\theta CA}$  is determined by the user's board design.



a. 45°C/W when mounted on a 1 in<sup>2</sup>



pad of 2 oz copper.







b. 115°C/W when mounted on a minimum pad of 2 oz copper.

- 2. Pulse Test: Pulse Width <  $300 \ \mu$ s, Duty cycle < 2.0%. 3. E<sub>AS</sub> of 541 mJ is based on starting T<sub>J</sub> = 25 °C, L = 3 mH, I<sub>AS</sub> = 19 A, V<sub>DD</sub> = 150 V, V<sub>GS</sub> = 10 V. 100% tested at L = 0.1 mH, I<sub>AS</sub> = 60 A. 4. Pulse Id refers to Figure.11 Forward Bias Safe Operation Area.

#### TYPICAL CHARACTERISTICS T<sub>J</sub> = 25°C unless otherwise noted







#### **TYPICAL CHARACTERISTICS** (continued) $T_J = 25^{\circ}C$ unless otherwise noted





Figure 13. Transient Thermal Response Curve

#### **ORDERING INFORMATION**

Device Marking	Device	Package	Reel Size	Tape Width	Shipping <sup>†</sup>
FDMS86255	FDMS86255	PQFN8 (Halogen Free)	13"	12 mm	3000 / Tape and Reel

†For information on tape and reel specifications, including part orientation and tape sizes, please refer to our Tape and Reel Packaging Specification Brochure, BRD8011/D.





DOCUMENT NUMBER: 98AON13657G Electronic versions are uncontrolled except when accessed directly from the Document R Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.							
DESCRIPTION:	PQFN8 5X6, 1.27P		PAGE 1 OF 1				
ON Semiconductor and ()) are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability. Including without limitation special consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the							

© Semiconductor Components Industries, LLC, 2019

rights of others.

onsemi, ONSEMI, and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does **onsemi** assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using **onsemi** products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by **onsemi**. "Typical" parameters which may be provided in **onsemi** data sheets and/or specifications can and do vary in different applications and calcular performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. **onsemi** does not convey any license under any of its intellectual property rights nor the rights of others. **onsemi** products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use **onsemi** products for any such unintended or unauthorized application, Buyer shall indemnify and hold **onsemi** and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that **onsemi** was negligent regarding the design or manufacture of the part. **onsemi** is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

#### PUBLICATION ORDERING INFORMATION

#### LITERATURE FULFILLMENT:

#### TECHNICAL SUPPORT

onsemi Website: www.onsemi.com

Email Requests to: orderlit@onsemi.com

North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support: Phone: 00421 33 790 2910 For additional information, please contact your local Sales Representative