



# Si photodiodes

S1336 series

# UV to near IR for precision photometry

These Si photodiodes have sensitivity in the UV to near IR range. They are suitable for low-light-level detection in analysis and the like.

#### Features

- Applications

- High sensitivity in UV range
- Low capacitance
- High reliability

# Analytical instruments Optical measurement equipment

### Structure / Absolute maximum ratings

				Absolute maximum ratings					
Type no.	Dimensional outline/ Window material*1	Package	Photosensitive area size	Reverse voltage Vr max	Operating temperature* <sup>2</sup> Topr	Storage temperature <sup>*2</sup> Tstg			
			(mm)	(V)	(°C)	(°C)			
S1336-18BQ*3	(1)/Q	TO-18	$1.1 \times 1.1$		-20 to +60	-55 to +80			
S1336-18BK	(2)/K	10-16	1.1 × 1.1		-40 to +100	-55 to +125			
S1336-5BQ*3	(3)/Q		2.4 × 2.4		-20 to +60	-55 to +80			
S1336-5BK	(4)/K	TO-5	2.4 × 2.4	5	-40 to +100	-55 to +125			
S1336-44BQ*3	(5)/Q	10-5	3.6 × 3.6	5	-20 to +60	-55 to +80			
S1336-44BK	(6)/K		3.0 × 3.0		-40 to +100	-55 to +125			
S1336-8BQ*3	(7)/Q	TO-8	5.8 × 5.8		-20 to +60	-55 to +80			
S1336-8BK	(8)/K	10-8	5.0 × 5.8		-40 to +100	-55 to +125			

\*1: Window material K=borosilicate glass, Q=quartz glass

\*2: No dew condensation


When there is a temperature difference between a product and the surrounding area in high humidity environments, dew condensation may occur on the product surface. Dew condensation may cause deterioration in characteristics and reliability. \*3: Refer to "Precautions against UV light exposure."

Note: Exceeding the absolute maximum ratings even momentarily may cause a drop in product quality. Always be sure to use the product within the absolute maximum ratings.


# Electrical and optical characteristics (Typ. Ta=25 °C, unless otherwise noted)

Type no.	Spectral response range $\lambda$	Peak sensitivity wavelength λp	Photosensitivity S (A/W)			Short circuit current Isc		Dark current ID VR=10 mV	coefficient of ID	UR=0 V	Terminal capacitance Ct VR=0 V	Rsh		Noise equivalent power	
				200	nm	He-Ne 100 lx laser		max.	TCID	RL=1 kΩ	f=10 kHz	VR=10 mV		NEP	
	(nm)	(nm)	λр	Min.	Тур.	633 nm	Min. (µA)	Тур. (µА)	(pA)	(times/°C)	(µs)	(pF)	Min. (GΩ)	Typ. (GΩ)	(W/Hz <sup>1/2</sup> )
S1336-18BQ	190 to 1100	960	0.5	0.10	0.12	0.33	1	1.2	20	1.15	0.1	20	0.5	2	5.7 × 10 <sup>-15</sup>
S1336-18BK	320 to 1100			-	-		0.9	1.0	20					2	5.7 ~ 10
S1336-5BQ	190 to 1100			0.10	0.12		4	5	30		0.2	65	0.3	1	$8.1 \times 10^{-15}$
S1336-5BK	320 to 1100			-	-										
S1336-44BQ	190 to 1100			0.10	0.12		8	10	50		0.5	150	0.2	0.6	$1.0 \times 10^{-14}$
S1336-44BK	320 to 1100			-	-										1.0 × 10
S1336-8BQ	190 to 1100			0.10	0.12		22	28	100		1	380	0.1	0.4	$1.3 \times 10^{-14}$
S1336-8BK	320 to 1100			-	-										1.5 × 10


# Spectral response




#### Photosensitivity temperature characteristics




# Dark current vs. reverse voltage














### Precautions against UV light exposure

- When UV light irradiation is applied, the product characteristics may degrade. Such examples include degradation of the product's UV sensitivity and increase in dark current. This phenomenon varies depending on the irradiation level, irradiation intensity, usage time, and ambient environment and also varies depending on the product model. Before employing the product, we recommend that you check the tolerance under the ultraviolet light environment that the product will be used in.
- Exposure to UV light may cause the characteristics to degrade due to gas released from the resin bonding the product's component materials. As such, we recommend that you avoid applying UV light directly on the resin and apply it on only the inside of the photosensitive area by using an aperture or the like.



## Related information

www.hamamatsu.com/sp/ssd/doc\_en.html

- Precautions
- Disclaimer
- · Metal, ceramic, plastic package products
- Technical note
- · Si photodiodes

Information described in this material is current as of July 2023.

Product specifications are subject to change without prior notice due to improvements or other reasons. This document has been carefully prepared and the information contained is believed to be accurate. In rare cases, however, there may be inaccuracies such as text errors. Before using these products, always contact us for the delivery specification sheet to check the latest specifications.

The product warranty is valid for one year after delivery and is limited to product repair or replacement for defects discovered and reported to us within that one year period. However, even if within the warranty period we accept absolutely no liability for any loss caused by natural disasters or improper product use. Copying or reprinting the contents described in this material in whole or in part is prohibited without our prior permission.



# www.hamamatsu.com

#### HAMAMATSU PHOTONICS K.K., Solid State Division

1126-1 Ichino-cho, Higashi-ku, Hamamatsu City, 435-8558 Japan, Telephone: (81)53-434-3311, Fax: (81)53-434-5184

1126-1 ICHINO-CHO, HIGdShIFKU, Halmathatsu City, 435-8558 Japah, Telephone: (1)908-231-960, Fax: (81)55-454-5311, FaX: (81)53-434-5184 U.S.A.: HAMAMATSU CORPORATION: 360 Foothill Road, Bridgewater, NJ 08807, U.S.A., Telephone: (1)908-231-960, Fax: (1)908-231-1218 Germany: HAMAMATSU PHOTONICS DEUTSCHLAND GMBH: Arzbergerstr. 10, 82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-265-8 E-mail: info@hamamatsu.de France: HAMAMATSU PHOTONICS PEUTSCHLAND GMBH: Arzbergerstr. 10, 82211 Herrsching am Ammersee, Germany, Telephone: (49)8152-375-0, Fax: (49)8152-265-8 E-mail: info@hamamatsu.de France: HAMAMATSU PHOTONICS FRANCE S.A.R.L: 19 Rue du Saule Trapu, Parc du Moulin de Massy, 91882 Massy Cedex, France, Telephone: (33)1 69 53 71 100, Fax: (33)1 69 53 71 100, Fax: (31) 10 E-mail: info@hamamatsu.fr United Kingdow: HAMAMATSU PHOTONICS NUL LIMITED: 2 Howard Court,10 Towin Road, Welwyn Garden City, Herfordshire, ALT 18W, UK, Telephone: (44)1707-29488K, Fax: (44)1707-325777 E-mail: info@hamamatsu.ce Italy: HAMAMATSU PHOTONICS ITALIA S.R.L: Strada della Moia, 1 int. 6 20044 Arses (Milano), Haly, Telephone: (46)8-509-031-00, Fax: (46)8-509-031-01 E-mail: info@hamamatsu.se Italy: HAMAMATSU PHOTONICS (CHINA IO, LTD: 1201, Tower B, Jaming Certer, 27 Dongsanhuan Bellu, Chaoyang District, 100020 Beijing, PR. China, Telephone: (86)10-6586-6006, Fax: (86)10-6586-2066 E-mail: hpc@hamamatsu.ce Taiwan: HAMAMATSU PHOTONICS TAIWAN CO., LTD: 13F-1, No.101, Section 2, Gongdao 5th Road, East Dist., Hsinchu City, 300046, Taiwan(R.O.C), Telephone: (886)3-659-0081 E-mail: info@hamamatsu.ce