

136 to 174 MHz Omni Antenna 2.5 dBi Gain, NMO Connector, Stainless Steel

LCANOM1083

Features

- · Vertically Polarized
- · 2.5 dBi Gain
- NMO Connector

Applications

- · Offroad/Overland Vehicles
- · Mining/Industrial Heavy Equipment
- Commercial Trucking

- · Stainless Steel
- 1.5:1 VSWR Max
- 50 Watt Max Input Power
- Fleet Management
- · Farm Equipment

Description

The L-com LCANOM1083 is a single band antenna that ships on the same day as ordered. Our vertical polarized antenna with 136 to 174 MHz frequency range has a NMO male connectors. This antenna is made of stainless steel has an overall length of 21.65 in, a width of 2 in, and a weight of 0.33 lbs.

L-com's LCANOM1083 is a single band antenna operating from 136 to 174 MHz with 2.5 dBi gain. The omni directional antenna has a maximum input VSWR of 1.5:1.

L-com has one of the largest in-stock collections of omni directional antennas with our wide selection of superior quality RF parts, that ship same day. Make your online purchase right now to take advantage of our same-day shipping. For further information on similar products, our expert technical support and knowledgeable sales team can help you get the ideal single band antenna as per your requirement.

Configuration

Band Type Radiation Pattern Polarization Connector Type Single Omni Directional Vertical NMO

Electrical Specifications

Description	Minimum	Typical	Maximum	Units
Frequency Range	136		174	MHz
Frequency Range Input VSWR			1.5:1	
Impedance		50		Ohms
Gain		2.5		dBi
Input Power			50	Watts

Mechanical Specifications

Click the following link (or enter part number in "SEARCH" on website) to obtain additional part information including price, inventory and certifications: 136 to 174 MHz Omni Antenna 2.5 dBi Gain, NMO Connector, Stainless Steel LCANOM1083



136 to 174 MHz Omni Antenna 2.5 dBi Gain, NMO Connector, Stainless Steel

LCANOM1083

Radome Material Stainless Steel

Size

 Length
 21.65 in [549.91 mm]

 Width
 2 in [50.8 mm]

 Height
 2 in [50.8 mm]

 Weight
 0.33 lbs [149.69 g]

Environmental Specifications

Temperature

Operating Range -40 to +80 deg C

Compliance Certifications (see product page for current document)

Plotted and Other Data

Notes:

136 to 174 MHz Omni Antenna 2.5 dBi Gain, NMO Connector, Stainless Steel from L-com has same day shipment for domestic and International orders. Our portfolio includes coaxial cable assemblies, connectors, adapters and custom products as well as lightning and surge protectors, NEMA rated enclosures, and an RF product line which includes antennas, amplifiers, passive, and active components.

The information contained within this document is accurate to the best of our knowledge and representative of the part described herein. It may be necessary to make modifications to the part and/or the documentation of the part in order to impliment improvements. L-com reserves the right to make such changes as required. Unless otherwise stated, all specifications are nominal. L-com does not make any representation or warranty regarding the suitability of the part described herein for any particular purpose, and L-com does not assume liability arising out of the use of any part or document.

L-com CAD Drawing

