## 



## 10W

The MCE10 series of PCB mount single output AC-DC medical power supplies delivers a power output of 10W and offers single output voltages ranging from 3.3V to 48VDC. The MCE10 series, which is available in open-frame and encapsulated mechanical formats, is specifically designed for medical applications with 2 x MOPP isolation and is approved for Class II applications.

With world-wide medical safety approvals, class B compliance for conducted and radiated emissions, high efficiency, high reliability, 4kVAC isolation, the MCE series benefits system designers with easy integration into a wide range of BF rated medical applications including imaging, patient treatment, surgical equipment and home healthcare applications.

#### **Features**

- Single outputs 3.3V to 48VDC
- Input range 80 to 264VAC
- Available in open frame and encapsulated formats
- High efficiency, up to 84%
- 4kVAC input to output isolation
- Class B conducted and radiated emissions
- IEC 60601-1 medical safety agency approvals, 2 x MOPP
- IEC class II insulation rating
- -25°C to +70°C operating temperature
- Overvoltage, overload and short circuit protection

## Models & Ratings

#### Model Number(1) **Output Voltage Output Current** Efficiency(2) **Output Power** MCE10US03 3.3VDC 2.40A 76% 8W MCE10US05 5.0VDC 2.00A 79% 10W MCE10US09 9.0VDC 80% 10W 1.11A MCE10US12 12.0VDC 0.83A 81% 10W MCE10US15 15.0VDC 0.67A 81% 10W MCE10US24 24.0VDC 0.42A 84% 10W 10W MCE10US48 48.0VDC 0.21A 84%

#### Notes:

- 1. For Open Frame version add suffix -P to model number, e.g. MCE10US12-P.
- 2. Typical efficiency at 230VAC and full load.

#### AC-DC POWER SUPPLIES



#### **Applications**







Healthcare

Home Healthcare

Medical Diagnostic

#### **Dimensions**

#### MCE10:

2.00 x 1.15 x 0.91" (50.8 x 29.2 x 23.1mm)

#### MCE10-P:

1.90 x 1.05 x 0.71" (48.3 x 26.7 x 18.0mm)

# **○** MCE10 Series

## Summary

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Input Voltage Range	80		264	VAC	Derate from 100% at 90 VAC to 90% at 80 VAC	
No Load Input Power			0.3	W		
Efficiency		81		%	Model dependent, see Models & Ratings	
Operating Temperature	-25		+70	°C	Derate output linearly from 100% at 50°C to 50% at 70°C	
EMC	EN55011 Lev	EN55011 Level B Conducted & Radiated, EN61000-3-2, EN61000-3-3, EN60601-1-2				
Safety Approvals	IEC60601-1, EN60601-1, ES60601-1					

## Input

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	80		264	VAC	Derate from 100% at 90VAC to 90% at 80VAC
Input Frequency	47		63	Hz	
Input Current - Full Load		0.2/0.12		A rms	At 115/230VAC
No Load Input Power			0.3	W	
Inrush Current			40	А	At 230VAC, cold start 25°C
Earth Leakage Current					Class II construction no earth
Input Protection	Internal T1.0 A/300 VAC fuse fitted in line and neutral				

## Output

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	3.3		48	VDC	
Initial Set Accuracy			3/2	%	3% for 3V3 and 5V models, 2% for others at 50% load
Minimum Load	0			А	No minimum load required
Line Regulation			1	%	
Load Regulation			3/5	%0	5% for 3V3 and 5V models, 3% for others
Start Up Delay			2	s	
Start Up Rise Time			35	ms	
Hold Up Time	8	14		ms	At full load and 115VAC
Transient Response			4	%	Deviation, recovery within 1% in less than 500µs for a 25% load change
			120	mV pk-pk - %pk-pk	3.3V model, 20MHz bandwidth
			200		5V and 9V models, 20MHz bandwidth
Ripple & Noise			2.5		12V and 15V models. 20MHz bandwidth
			1.5		24V and 48V models. 20MHz bandwidth
Patient Leakage Current			65	μA	At 264VAC, 60Hz
Overvoltage Protection	115		145	% Vnom	220% typical for 3V3 model, auto recovery
Overload Protection	110		190	%	
Short Circuit Protection					Trip & Restart (hiccup mode)
Temperature Coefficient			0.05	%/°C	

# **─** MCE10 Series

### General


Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		81		%	Model dependent
Isolation: Input to Output	4000			VAC	2 x MOPP, suitable for BF applications
Switching Frequency	10		55	kHz	Varies with load
Power Density			7	W/in³	For '-P' version
Mean Time Between Failure	550	600		khrs	MIL-HDBK-217F, +25°C GB
Weight		0.05 (23)		lb (a)	Open frame versions (-P)
		0.12 (52)		lb (g)	Encapsulated version

### **Environmental**


Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Operating Temperature	-25		+70	°C	Derate output linearly from 100% at 50°C to 50% at 70°C
Storage Temperature	-40		+85	°C	
Cooling	Convection-cooled				
Humidity			95	%RH	Non-condensing
Operating Altitude			5000	m	
Shock	IEC68-2-27, 30g, 11ms half sine, 3 times in each of 6 axes				
Vibration	IEC68-2-6, 2g, 10Hz to 500kHz, 10 mins/cycle, 60 mins each cycle				

## **Efficiency Graphs**

### MCE10US12-P



#### MCE10US24-P



### **EMC: Emissions**

Phenomenon	Standard	Test Level	Notes & Conditions	
Conducted	EN55011	Class B	If output is connected to ground, additional external components will	
Radiated	EN55011	Class B	be required. See application notes	
Harmonic Current	EN61000-3-2	Class A		
Voltage Flicker	EN61000-3-3			

## 

### **EMC: Immunity**

Phenomenon	Standard	Test Level	Criteria	Notes & Conditions
Medical	EN60601-1-2	As below	As below	
ESD Immunity	EN61000-4-2	±8kV contact, ±15kV air discharge	А	
Radiated Immunity	EN61000-4-3	10 V/m	Α	
EFT/Burst	EN61000-4-4	3	Α	
Surge	EN61000-4-5	2	Α	Line to line
Conducted	EN61000-4-6	10Vrms	Α	
Magnetic Fields	EN61000-4-8	30A/m	Α	
		70% U <sub>T</sub> (80.5VAC) for 100ms	Α	
	EN61000-4-11	40% U <sub>T</sub> (46VAC) for 200ms	В	
	(115VAC)	<5% U <sub>T</sub> (0VAC) for 10ms	Α	
Diagram di latamantiana		<5% U <sub>T</sub> (0VAC) for 5000ms	В	
Dips and Interruptions		70% U <sub>T</sub> (161VAC) for 100 ms	Α	
	EN61000-4-11	40% U <sub>T</sub> (92VAC) for 200ms	Α	
	(230VAC)	<5% U <sub>T</sub> (0VAC) for 10ms	Α	
		<5% U <sub>T</sub> (0VAC) for 5000ms	В	


### **Safety Approvals**

Certification	Standard	Notes & Conditions	
СВ	IEC60601-1	Medical, 2 x MOPP	
UL	ES60601-1/CSA-C22.2 No.60601-1:14	Medical, 2 x MOPP	
TUV	EN60601-1	Medical, 2 x MOPP	
CE	Meets all applicable directives		
UKCA	Meets all applicable legislation		

#### **Application Notes**

#### **EMC** with output grounded

EMC with output grounded. This product is designed for class II operation, but if there is a requirement to connect the output to ground then additional components as shown below can be added to improve emissions.




Suggested value - C: X2 cap, 0.22 $\mu$ F/275V, 10% MKP HJC.


- L: CMCK DIP UU-9.8 Φ0.27\*95T 17.6mH (min)

## **─ MCE10 Series**


#### **Mechanical Details**


#### **Encapsulated**





#### **Open Frame (-P)**





Pin Connections		
Pin	Single	
1	ACN	
2	ACL	
3	-Vout	
4	+Vout	

#### Notes:

- 1. Dimensions in inches (mm).
- 2. Weight: Open frame versions (-P): 0.05lbs (23g) Encapsulated: 0.12lbs (52g)
- 3. Tolerances:  $x.xx = \pm 0.02$  ( $x.x = \pm 0.5$ )  $x.xxx = \pm 0.01$  ( $x.xx = \pm 0.25$ )