Datasheet M-Duino 53ARR+ GPRS



💓 Industrial Shields

Technical Features CONECTABLE PLC ARDUINO 24Vcc M-DUINO

| MODEL TYPE | M-Duino |
|---------------------|--|
| Input Voltage | 12 to 24Vdc (Fuse protection (2.5A) Polarity protection) |
| Input rated voltage | 24Vdc |
| Rated Power | 30 W |
| I max. | 15A |
| Size | 101x119.3x119.5 |
| Clock Speed | 16MHz |
| Flash Memory | 256KB of which 8KB used by bootloader |
| SRAM | 8KB |
| EEPROM | 4KB |
| Communications | Ethernet, GPRS/GSM, USB, I2C, Serial TTL, , RS-232, RS-485 (HD-FD), SPI, RTC, μSD Socket |
| USB consideration! | Only for uploading or debugging. NOT connected as a serial Cannot be working in a final application |

General Features

| Power supply voltage | DC power supply | 12 to 24Vdc |
|---------------------------------|---|-----------------|
| Operating voltage range | DC power supply | 11.4 to 25.4Vdc |
| Power consumption | DC power supply | 30 W MAX. |
| External power supply | Power supply voltage | 24Vdc |
| | Power supply voltage | 700Ma |
| Insulation resistance | 20MΩ min.at 500Vdc between the AC terminals and the protective earth terminal. | |
| Dielectric strength | 2.300 VAC at 50/60 Hz for one minute with a leakage current of 10mA max. Between all the external AC terminals and the protective ground terminal. | |
| Shock resistance | 80m/s2 in the X, Y and Z direction 2 times each. | |
| Ambient temperature (operating) | 0° to 60°C | |
| Ambient humidity (operating) | 10% to 90% (no condensation) | |
| Ambient environment (operating) | With no corrosive gas | |
| Ambient temperature (storage) | -20° to 60°C | |
| Power supply holding time | 2ms min. | |
| Veight | 861g max. | |


INPUTS (x28)

| (x14) - An/Dig Input 10bit (0-10Vcc) | 0 to 10Vac Input Impedance: 39K Separated PCB ground Rated Voltage: 10Vac 7 to 24Vdc I mir: 2 to 12 mA Galvanic Isolation Rated Voltage: 24 Vdc |
|--|--|
| (x9) - Digital Isolated Input (24Vcc) | 7 to 24Vdc I min: 2 to 12 mA Galvanic Isolation Rated Voltage: 24 Vdc |
| (x5) - Interrupt isolated Input HS (24Vcc) * - The Interrupt isolated Inputs can also work as Digital isolated Inputs | 7 to 24Vdc I mir: 2 to 12 mA Galvanic Isolation Rated Voltage: 24 Vdc |
| Expandability | |
| | |

I2C - 127 elements - Serial Port RS232/RS485

OUTPUTS (x32)

| • · · · · · · · · · · · · · · · · · · · | | |
|---|---|--|
| (x8) - Analog Output 8bit (0-10Vcc) | 0 to 10Vac I max: 20 mA Separated PCB ground Rated Voltage: 10Vac | |
| (x9) - Digital Isolated Output (24Vcc) | 5 to 24Vdc I max 70 mA Galvanic Isolation Diode Protected for Relay Rated Voltage: 24Vdc | |
| (x8) - PWM Isolated Output 8bit (24Vcc) • The PWM outputs can also work as Digital outputs | 5 to 24Vdc I max: 70 mA Galvanic Isolation Diode Protected for Relay Rated Voltage: 24Vdc | |
| (x15) -Digital Isolated Output Relay | 220V Vac I max: 5A Galvanic Isolation Diode protected for Relayc Imax 24Vdc: 410 mA | |







DataSheet Rev. 20200710

006001001000

Industrial Shields

Performance Specifications

| Arduino Board | Arduino Mega2560 | |
|----------------------|---|--|
| Control method | Stored program method | |
| I/O control method | Combination of the cyclic scan and immediate refresh processing methods. | |
| Programming language | Arduino IDE. Based on wiring (Wiring is an Open Source electronics platform composed of a programming language. "similar to the C") | |
| Microcontroller | ATmega2560 | |

http://arduino.cc/en/Tutorial/HomePage



Do not disconnect equipment when a flammable or combustible

atmosphere is present. Disconnection of equipment when a flammable or combustible atmosphere is present may cause a fire or explosion which could result in death, serious injury and/or property damage.

| Install Arduino IDE and the Industrial Shields boards | Warnings |
|---|---|
| The steps to follow to install our equipment's to Arduino IDE are: | Unused pins should not be connected. Ignoring the directive may damage the controller. |
| • Open the Arduino IDE, versión 1.8.0 or superior. If you don't have it yet , you can download here | Before using this product, it is the responsibility of the user to read the product's User Guide and all accompanying documentation. |
| https://www.arduino.cc/en/Main/Software . Press the "Preferences" option to "File" menu and open the preferences window. | Industrial Shields PLCs must be powered between 12Vdc and 24Vdc. If a higher voltage is supplied to the equipment can suffer irreversible damage. |
| In the text box "Additional boards manager URLs", add the | Maintenance must be performed by qualified personnel familiarized with the construction, operation, and hazards involved with the control. |
| direction: http://apps.industrialshields.com/main/arduino/boards/package_ | Maintenance should be performed with the control out of operation and disconnected from all sources of power. |
| industrialshields_index.jsonClose the preferences window with the "OK" button. | The Industrial Shields Family PLCs are Open Type Controllers. It is required that you install the M-Duino PLC in a housing, cabinet, or electric control room. Entry to the housing, cabinet, or electric control room should be limited to authorized personnel. |
| • Click on "Tools" menu, and open the "Boards" submenu, and click the "Boards Manager" option, to open the Boards Manager window. | Inside the housting, cabinet or electric control room, the Industrial Shields PLC must be at a minimum distance from the rest of the components of a minimum of 25 cm, it can be severely damaged. |
| Search "industrialshields" to the search filter and select to the list and click "Install" | Failure to follow these installation requirements could result in severe personal injury and/or property damage. Always follow these requirements when installing M-Duino family PLCs. |
| • Close the "Boards Manager". Once it is performed that steps, you are available to select each PLC that you wish to work on "Tools" - | In case of installation or maintenance of the M-Duino please follow the instructions marked in the Installation and Maintenance section on the User Guide. |

"Boards" : M-Duino... >

To get more information:

https://www.industrialshields.com/first-steps-with-the-industrialarduino-based-plc-s-and-the-panel-pc-s-raspberry-pi-based#boards

Symbology

| Symb | ology | Technical Support |
|-------------|---|---|
| | Indicates that the equipment is suitable for direct current only; to identify relevant terminals | You can contact with us using the best channel for you: |
| \sim | Indicates that the equipment is suitable for alternating current only; to identify relevant terminals | support@industrialshields.com |
| | To identify the control by which a pulse is started. | www.industrialshields.com |
| | To identify an earth (ground) terminal in cases where neither the symbol 5018 nor 5019 is explicily required. | Visit our Blog, Forum orTicketing system |
| \otimes | To identify the switch by means of which the signal lamp(s) is (are) switched on or off. | S 34 644 927 900 |
| CE | CE marking indicates that a product complies with applicable European Union regulations | Use our chat service |
| \triangle | Indicates a potentially hazardous situation which, if not avoided, could result in death or serious injury | Check the user guides |
| 4 | To indicate hazards arising from dangerous voltages | Visit our Channel |