

## LE-UVWE5D MAGNIFYING UV AND WHITE LED LAMP, ESD SAFE, 2.25X (5 DIOPTERS)

Ideal-tek LE-WUVE5D lamp features unique illumination options, giving operators the ability to use Ultraviolet (UV) LEDs or standard white LEDs. Operating at 365 nm the UV LED lights in this magnifying lamp can be used for examination of conformal coatings, holograms, etc, any type of materials that fluoresces under inspection. This model features 48 adjustable white LEDs as well as 30 UV LEDs operating at 365 nm. Features an ESD safe coating to dissipate static energy designed to protect sensitive components.

## **FEATURES**

- Features 48 adjustable white LEDs as well as 30 UV LEDs operating at 365 nm
- Large 19 x 15,7 mm (7.5 x 6.2 inch), 5-Diopter crystal-clear glass lens for distortion-free viewing
- Fully covered spring-balanced arm with a large working range
- Swivel motion allows the lamp head to rotate
- Covered spring arm prevents pinching hazards
- ESD Safe coating









**Brightness Controls** 

ESD Safe

Dissipates

Electrostatic Discharge **LE-UVWE5D** specifications Magnification 2.25X (5-Diopter) Lens Dimension 19 x 15,7 mm (7.5" x 6.2") Color 48 White LEDs | 6500K Color Temperature | White LEDs 1-10W Adjustable Brightness UV LEDs 30 UV LEDs | 365 nm | 6W Max: 1100Lm Lumen ESD safe Packaging Dimension 1 pc 53x36x14 cm / 2 pcs 55x37x30 cm Packaging Weight 1 pc 4.8 kg / 2 pcs 10 kg Plug Type Type F (Schuko)

This product contains a light source of energy efficiency class F.

ideal-tek.com

30 UV

I FDs

48 White

I FDs

1100

7.5" x 6.2"

5-Diopter Lens

2.25x

Magnification