


Double-deck terminal block; Through/through terminal block; N/N; without marker carrier; for Ex e II and Ex i applications; for DIN-rail  $35 \times 15$  and  $35 \times 7.5$ ;  $2.5 \text{ mm}^2$ ; Push-in CAGE CLAMP®;  $2.50 \text{ mm}^2$ ; blue



https://www.wago.com/2002-2204







Similar to illustration

Electrical data	
Ratings per IEC/EN	
Ratings per	IEC/EN 60947-7-1
Nominal voltage (III/3)	500 V
Rated impulse voltage (III/3)	6 kV
Rated current	24 A
Current at conductor cross-section (max.) mm <sup>2</sup>	28 A
Legend (ratings)	(III / 3) ≙ Overvoltage category III / Pollution degree 3

Ratings per UL 1059	
Approvals per	UL 1059
Rated voltage UL (Use Group B)	300 V
Rated current UL (Use Group B)	20 A
Rated voltage UL (Use Group C)	300 V
Rated current UL (Use Group C)	20 A
Rated voltage UL (Use Group D)	600 V
Rated current UL (Use Group D)	5 A

Ratings per CSA	
Approvals per	CSA 22.2 No 158
Rated voltage CSA (Use Group B)	600 V
Rated current CSA (Use Group B)	20 A
Rated voltage CSA (Use Group C)	600 V
Rated current CSA (Use Group C)	20 A

Ex information	
Reference hazardous areas	See "Downloads – Documentation – Additional Information: Technical Section; Technical Explications"
Ratings per	ATEX: PTB 03 ATEX 1162 U / IECEx: PTB 03.0004U (Ex eb IIC Gb)
Rated voltage EN (Ex e II)	440 V
Rated current (Ex e II)	20 A
Rated current (Ex e II) with jumper	18 A

https://www.wago.com/2002-2204





Depending on the conductor characteristic, a conductor with a smaller cross-section can also be inserted via push-in

 $10\dots12\,\text{mm}\,\text{/}\,0.39\dots0.47$  inches

termination.

Front-entry wiring

Connection data			
Connection points	4	Connection 1	
Total number of potentials	2	Connection technology	Push-in CAGE CLAMP®
Number of levels	2	Number of connection points	2
Number of jumper slots	4	Actuation type	Operating tool
Anzahl Brückeraufnahmen Rang	1	Connectable conductor materials	Copper
		Nominal cross-section	2.5 mm²
		Solid conductor	0.25 4 mm² / 22 12 AWG
		Solid conductor; push-in termination	0.75 4 mm² / 18 12 AWG
		Fine-stranded conductor	0.25 4 mm² / 22 12 AWG
		Fine-stranded conductor; with insulated ferrule	0.25 2.5 mm² / 22 14 AWG
		Fine-stranded conductor; with ferrule;	1 2.5 mm² / 18 14 AWG

push-in termination

Strip length

Wiring direction

Note (conductor cross-section)

Connection 2		
Number of connection points 2	2	

Physical data	
Width	5.2 mm / 0.205 inches
Height	69.7 mm / 2.744 inches
Depth from upper-edge of DIN-rail	51.7 mm / 2.035 inches

Mechanical Data	
Potential marking	N/N
Mounting type	DIN-35 rail
Marking level	Center/side marking

Material Data	
Note (material data)	
	<u>Information on material specifications can be found here</u>
Color	blue
Material group	1
Insulation material	Polyamide (PA66)
Flammability class per UL94	V0
Fire load	0.204 MJ
Weight	10.2 g

https://www.wago.com/2002-2204



#### **Environmental requirements**

Processing temperature -35 ... +85 °C Continuous operating temperature -60 ... +105 °C

Commercial data	
Product Group	22 (TOPJOB S)
eCl@ss 10.0	27-14-11-20
eCl@ss 9.0	27-14-11-20
ETIM 8.0	EC000897
ETIM 7.0	EC000897
PU (SPU)	50 pcs
Packaging type	Box
Country of origin	DE
GTIN	4044918691093
Customs tariff number	85369010000

#### Approvals / Certificates

#### General approvals







	_	
Approval	Standard	Certificate Name
CCA DEKRA Certification B.V.	EN 60947	71-120369
CCA DEKRA Certification B.V.	EN 60947	NTR NL 7892
CSA DEKRA Certification B.V.	C22.2 No. 158	1536069
UL Underwriters Laboratories	UL 1059	E45172

#### Declarations of conformity and manufacturer's declarations



Approval	Standard	Certificate Name
Railway WAGO GmbH & Co. KG	-	Railway Ready

#### Approvals for marine applications





Approval	Standard	Certificate Name
ABS American Bureau of Ship- ping	EN 60947	20-HG1941090-PDA
DNV GL Det Norske Veritas, Ger- manischer Lloyd	-	TAE00001V2

#### Approvals for hazardous areas








Approval	Standard	Certificate Name
AEx Underwriters Laboratories Inc.	UL 60079	E185892 (AEx eb IIC resp. Ex eb IIC)
ATEX Physikalisch Technische Bundesanstalt (PTB)	EN 60079	PTB 03 ATEX 1162 U (II2G Ex eb IIC Gb, IM2 Ex eb IMb)
CCC CNEX	GB/T 3836.3	2020312313000238 (Ex eb IIC Gb, Ex eb I Mb)
EAC Brjansker Zertifizierungs- stelle	TP TC 012/2011	RU C-DE.AM02. B.00127/19 (Ex e IIC Gb U)
IECEx Physikalisch Technische Bundesanstalt	IEC 60079	IECEx PTB 03.0004U (Ex eb IIC Gb or Ex eb I Mb)
INMETRO TÜV Rheinland do Brasil Ltda.	IEC 60079	TÜV 12.1307 U


#### **Downloads**

https://www.wago.com/2002-2204



# Environmental Product Compliance Compliance Search Environmental Product Compliance 2002-2204







#### 1.2 Optional Accessories

#### 1.2.1 DIN-rail

https://www.wago.com/2002-2204



#### 1.2.1.1 Mounting accessories



#### Item No.: 210-196

Aluminum carrier rail; 35 x 8.2 mm; 1.6 mm thick; 2 m long; unslotted; similar to EN 60715; silver-colored



#### Item No.: 210-198

Copper carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to EN 60715; copper-colored



#### Item No.: 210-508

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; galvanized; similar to EN 60715; silver-colored



Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; slotted; similar to EN 60715; silver-colored



#### Item No.: 210-506

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; galvanized; similar to FN 60715; silver-colored

#### .....

Steel carrier rail; 35 x 15 mm; 1.5 mm thick; 2 m long; unslotted; similar to EN 60715: silver-colored

#### Item No.: 210-118

Steel carrier rail; 35 x 15 mm; 2.3 mm thick; 2 m long; unslotted; according to FN 60715; silver-colored

#### Item No.: 210-115

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 18 mm; silver-colored



#### Item No.: 210-112

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; according to EN 60715; "Hole width 25 mm; silver-colored

#### Item No.: 210-504

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; slotted; galvanized; according to EN 60715; silver-colored

#### Item No.: 210-113

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; according to EN 60715; silver-colored

#### Item No.: 210-505

Steel carrier rail; 35 x 7.5 mm; 1 mm thick; 2 m long; unslotted; galvanized; according to EN 60715; silver-colored

#### 1.2.2 End plate

#### 1.2.2.1 End plate



#### Item No.: 209-192

Separator for Ex e/Ex i applications; 3 mm thick; 125.5 mm wide; orange

#### 1.2.3 Ferrule

#### 1.2.3.1 Ferrule

Item No.: 216-241



Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

### Item No.: 216-262

Ferrule; Sleeve for 0.75 mm² / 18 AWG; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; gray

#### Item No.: 216-243

Ferrule; Sleeve for 1 mm<sup>2</sup> / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red



#### Item No.: 216-263

46228, Part 4/09.90; white

Ferrule; Sleeve for 1 mm² / AWG 18; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; red

Ferrule; Sleeve for 0.5 mm<sup>2</sup> / 20 AWG; in-

sulated; electro-tin plated; electrolytic

copper; gastight crimped; acc. to DIN

#### Item No.: 216-244

Ferrule; Sleeve for 1.5 mm² / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

#### Item No.: 216-264

Ferrule; Sleeve for 1.5 mm<sup>2</sup> / AWG 16; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; black

#### Item No.: 216-246

Ferrule; Sleeve for 2.5 mm² / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue

# Item No.: 216-266

Ferrule; Sleeve for 2.5 mm<sup>2</sup> / AWG 14; insulated; electro-tin plated; electrolytic copper; gastight crimped; acc. to DIN 46228, Part 4/09.90; blue

#### 1.2.4 Installation

https://www.wago.com/2002-2204



#### 1.2.4.1 Cover



Item No.: 709-156

Cover; Type 3; suitable for cover carrier, type 3; 1 m long; transparent

#### 1.2.4.2 Cover carrier



Item No.: 709-169

Cover carrier; Type 3; gray

#### 1.2.5 Insulation stop

#### 1.2.5.1 Insulation stop





Item No.: 2002-171

Insulation stop; 0.25 - 0.5 mm2; 5 pieces/ strip; light gray

Item No.: 2002-172

Insulation stop; 0.75 - 1 mm<sup>2</sup>; 5 pieces/ strip; dark gray

#### 1.2.6 Jumper

#### 1.2.6.1 Jumper

Item No.: 2002-400

gray





Item No.: 2002-423/000-006 Continuous jumper; from 1 to 3; insulated; blue



Continuous jumper; from 1 to 3; insulated; light gray

Item No.: 2002-423/000-005

Continuous jumper; from 1 to 3; insulated; red



Continuous jumper; 2-way; insulated; light



Continuous jumper; from 1 to 4; insulated; blue



Item No.: 2002-410

Continuous jumper; from 1 to 4; insulated; light gray

Item No.: 2002-424/000-005

Continuous jumper; from 1 to 4; insulated;



Item No.: 2002-406/020-000



red

Delta jumper; insulated; light gray



Item No.: 2002-410/000-006

Jumper; 10-way; insulated; blue

HILLIAN

Jumper; 10-way; insulated; light gray

Item No.: 2002-410/000-005

Item No.: 2002-402/000-006



Jumper; 2-way; insulated; blue

Item No.: 2002-402 Jumper; 2-way; insulated; light gray Item No.: 2002-402/000-005

Item No.: 2002-403/000-006

Jumper; 10-way; insulated; red



Jumper; 2-way; insulated; red

Jumper; 3-way; insulated; blue

Item No.: 2002-403 Jumper; 3-way; insulated; light gray



Item No.: 2002-403/000-005

Jumper; 3-way; insulated; red

Item No.: 2002-404

Jumper; 4-way; insulated; light gray



Jumper; 4-way; insulated; blue

Item No.: 2002-404/000-006

Jumper; 4-way; insulated; red

Item No.: 2002-405/000-006



Item No.: 2002-405

Jumper; 5-way; insulated; light gray Jumper; 5-way; insulated; red

Item No.: 2002-405/000-005

Item No.: 2002-406/000-006 Jumper; 6-way; insulated; blue



Item No.: 2002-406/000-005 Item No.: 2002-407/000-006



Jumper; 6-way; insulated; light gray

Jumper; 6-way; insulated; red

Jumper; 7-way; insulated; blue

Item No.: 2002-407 Jumper; 7-way; insulated; light gray



Item No.: 2002-407/000-005 Jumper; 7-way; insulated; red

Item No.: 2002-406

Item No.: 2002-408/000-006

Item No.: 2002-408 Jumper; 8-way; insulated; blue Jumper; 8-way; insulated; light gray

HIII

Item No.: 2002-408/000-005

Jumper; 8-way; insulated; red

https://www.wago.com/2002-2204



#### 1.2.6.1 Jumper



Item No.: 2002-409/000-006

Jumper; 9-way; insulated; blue

Item No.: 2002-409

Jumper; 9-way; insulated; light gray



Item No.: 2002-409/000-005

Jumper; 9-way; insulated; red

Item No.: 2002-440

Jumper; from 1 to 10; insulated; light gray



Item No.: 2002-433

Jumper; from 1 to 3; insulated; light gray



Item No.: 2002-434

Jumper; from 1 to 4; insulated; light gray



Item No.: 2002-435

Jumper; from 1 to 5; insulated; light gray



Item No.: 2002-436

Jumper; from 1 to 6; insulated; light gray



Item No.: 2002-437

Jumper; from 1 to 7; insulated; light gray

Item No.: 2002-438

Item No.: 2002-482

light gray

Jumper; from 1 to 8; insulated; light gray



Jumper: from 1 to 9: insulated: light gray



Staggered jumper; 10-way; insulated; light gray



Item No.: 2002-481

Staggered jumper; 11-way; insulated; light gray



Staggered jumper; 12-way; insulated;

Item No.: 2002-473/011-000

Staggered jumper; 2-way; from 1 to 3; insulated; light gray



Item No.: 2002-472



Item No.: 2002-473

Staggered jumper; 3-way; insulated; light gray



Item No.: 2002-475/011-000 Staggered jumper; 3-way; insulated; light gray



Item No.: 2002-474 Staggered jumper; 4-way; insulated; light

Staggered jumper; 2-way; insulated; light gray



Staggered jumper; 7-way; insulated; light gray

gray

Item No.: 2002-475

Staggered jumper; 5-way; insulated; light gray



Item No.: 2002-476

Staggered jumper; 6-way; insulated; light gray



Item No.: 2002-477



Staggered jumper; 8-way; insulated; light gray

Item No.: 2002-479

Staggered jumper; 9-way; insulated; light gray



Item No.: 2002-477/011-000

Staggered jumper; insulated; light gray



Item No.: 2002-479/011-000

Staggered jumper; insulated; light gray



Item No.: 2002-481/011-000

Staggered jumper; insulated; light gray



Item No.: 2002-405/011-000


Star point jumper; 3-way; insulated; light gray





Item No.: 2002-492/000-012

Vertical jumper: insulated: orange



Wire commoning chain; insulated; black

Item No.: 210-123 Wire commoning chain; insulated; blue



Item No.: 2002-492

#### 1.2.7.1 Group marker carrier

Vertical jumper: insulated: light gray





Item No.: 2009-193

Group marker carrier; gray

Item No.: 2009-192

Group marker carrier; gray

Group marker carrier; gray

1.2.7.2 Marker

Item No.: 2009-191

Item No.: 2009-145/000-006

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue

#### Item No.: 2009-145/000-007

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

#### Item No.: 2009-145/000-023

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

Item No.: 2009-145/000-012

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange

Item No.: 2009-145/000-005

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red

#### Item No.: 2009-145/000-024

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; violet

#### Item No.: 2009-145

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

Item No.: 2009-145/000-002

Mini-WSB Inline; for Smart Printer; 1700 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

Continued on next page

https://www.wago.com/2002-2204



#### 1.2.7.2 Marker



#### Item No.: 248-501/000-006

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; blue



#### Item No.: 248-501/000-007

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; gray



#### Item No.: 248-501/000-023

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; green




#### Item No.: 248-501/000-017


Mini-WSB marking card; as card; not stretchable; plain; snap-on type; light green




#### Item No.: 248-501/000-012

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; orange





Mini-WSB marking card; as card; not stretchable; plain; snap-on type; violet



Mini-WSB marking card; as card; not stretchable; plain; snap-on type; white



#### Item No.: 248-501/000-002

Mini-WSB marking card; as card; not stretchable; plain; snap-on type; yellow

#### Item No.: 793-5501/000-006

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; blue

WMB marking card; as card; for terminal

block width 5 - 17.5 mm; stretchable 5 -

5.2 mm; plain; snap-on type; light green



WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; brown

## Item No.: 793-5501/000-007

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; gray



#### Item No.: 793-5501/000-023

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; green



#### Item No.: 793-5501/000-012

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; orange



WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; red



Item No.: 793-5501/000-024 WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; violet



WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; white

#### Item No.: 793-5501/000-002

WMB marking card; as card; for terminal block width 5 - 17.5 mm; stretchable 5 -5.2 mm; plain; snap-on type; yellow

#### Item No.: 2009-115/000-006

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; blue



#### Item No.: 2009-115/000-007

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; gray

#### Item No.: 2009-115/000-023

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; green

#### Item No.: 2009-115/000-017

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; light green

#### Item No.: 2009-115/000-012

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; orange



#### Item No.: 2009-115/000-005

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; red

Item No.: 2009-115/000-024 WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain;

#### Item No.: 2009-115

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; white

#### Item No.: 2009-115/000-002

WMB-Inline; for Smart Printer; 1500 pieces on roll; stretchable 5 - 5.2 mm; plain; snap-on type; yellow

#### 1.2.7.3 Marker carrier



snap-on type; violet

Item No.: 2002-161 Adaptor; gray



#### Item No.: 2009-198

Adaptor; gray

#### 1.2.7.4 Marking strip



#### Item No.: 2009-110

Item No.: 2002-121

Adaptor; gray

Marking strips; for Smart Printer; on reel; not stretchable; plain; snap-on type; white

#### 1.2.8 Protective warning marker

Page 8/10 Version 27.03.2023 Continued on next page

https://www.wago.com/2002-2204



#### 1.2.8.1 Cover



#### Item No.: 2002-115

Protective warning marker; for 5 terminal blocks; with high-voltage symbol, black; yellow

#### 1.2.9 Push-in type wire jumper

#### 1.2.9.1 Jumper



Push-in type wire jumper; 1.5 mm²; insulated; 110 mm long; black

Item No.: 2009-412
Push-in type wire jumper; insulated; 60 mm long; black

#### Item No.: 2009-414/000-005

Push-in type wire jumper; 1.5 mm²; insulated; 110 mm long; black

Item No.: 2009-416

Push-in type wire jumper; 1.5 mm²; insulated; 250 mm long; black

Item No.: 2009-414/000-006

Push-in type wire jumper; insulated; 110 mm long; black

#### 1.2.10 Test and measurement

#### 1.2.10.1 Testing accessories

#### Item No.: 2009-174

Test plug adapter; for 4 mm Ø test plugs; for testing TOPJOB®S rail-mounted terminal blocks; gray

#### Item No.: 2009-182

Testing tap; for max. 2.5 mm²; tool-free connection for individual test wires 0.08 - 2.5 mm; gray

#### Item No.: 2002-649

TOPJOB®S L-type spacer module; modular; e.g., for bridging commoned terminal blocks; gray

#### Item No.: 2002-611

TOPJOB®S L-type test plug module; modular; 1-pole; 2,50 mm²; gray

#### 1.2.11 Tool

#### 1.2.11.1 Operating tool



Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; angled; short; multicoloured

#### Item No.: 210-720

Operating tool; Blade: 3.5 x 0.5 mm; with a partially insulated shaft; multicoloured

#### **Installation Notes**

https://www.wago.com/2002-2204

# N/AGO

#### Conductor termination



All conductor types at a glance



Push-in termination of solid and ferruled conductors



Inserting a conductor via push-in termination:

Solid conductors with cross-sections from either one size above, or up to two sizes below, the rated cross-section can be simply pushed in – no tools needed.



Inserting a conductor via operating tool: Connecting fine-stranded conductors without ferrules, or small cross-sectional conductors that cannot be pushed in, is performed similarly to the original CAGE CLAMP® – just use an operating tool. Advantage:

To open the clamp, the operating tool is inserted vertically. The conductor entry is less than 15 degrees for easier wiring.

#### Commoning



Removing a push-in type jumper bar: Insert the operating tool between the jumper and partition wall of the dual jumper slots, then lift up the jumper. Place the operating tool in the center of jumpers for up to five contacts (see above), or alternately on both sides for jumpers with more than five contacts.



Insert push-in type jumper bar and push down until it hits backstop.

#### Commoning



Commoning two levels via double-deck vertical jumper (2002-492).

#### Marking



Snapping WMB Inline markers into marker slots.





Double-deck terminal blocks A double-deck marker carrier (2002-121) can be retrofitted to double-deck terminal blocks without a marker carrier.

Subject to changes. Please also observe the further product documentation!

Current addresses can be found at::  $\underline{www.wago.com}$ 

Page 10/10 Version 27.03.2023