


COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle PCB jack (female)

85_SMA-50-0-103/111_N

Properties

- Lead free material
- RoHS full compliant without exemption 6C
- Excellent return loss
- Applicable in frequencies up to 18 GHz

**Product configuration**

Interface type	Gender	Standard
SMA	jack	IEC 60169-15_MIL-STD-348A/310_CECC 22110

Material Data

Piece parts	Description / Material	Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer conductor	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Body	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Other body part	Brass	Gold Plating (Nickel underplated)
Insulator	PTFE (Polytetrafluoroethylene)	

Electrical Data

Impedance	50Ω
Operating frequency	18 GHz

Mechanical data

Weight	0.0038 kg
Mating cycles	500
Board mounting type	through holes
Number of printlegs	4
Height above PCB HA	9.6 mm
Height of stand off HS	0 mm

COAXIAL CONNECTOR, SMA, 50 Ohm, Right angle PCB jack (female)

85_SMA-50-0-103/111_N

Environmental data	
Operation temperature	-65 °C ... 165°C

Ordering Information Table	
Item number	Item description
85201239	85_SMA-50-0-103/111_NE

HUBER+SUHNER is certified by ISO 9001, ISO 14001, ISO 45001, IATF 16949, AS/EN 9100 and ISO/TS 22163-IRIS. Waiver: Facts and figures herein are for information only and do not represent any warranty of any kind.
DOCUMENT DOC-0000002694 / Date of publication: 15.06.2023 / uncontrolled copy