US Office: Tel: 800.648.2800 or +1.847.671.6690 UK Office: Tel: (+44) 1543 459 555 www.mobilemark.com





CVL Antenna

Mobile Mark's new CVL-WLF Series Covert Antenna covers all Cellular & LTE networks from the 694 MHz to 2.7 GHz, including 3G/4G, AWS, UMTS and LTE. This antenna is ideal for modems with high data throughput that are designed to operate on multiple networks worldwide.

The antenna is broadbanded enough that it can be stocked for multiple modems. Regardless of where the modem is designed for use, the antenna is designed to provide efficient coverage on the bands that operate in that country.

The antenna has excellent performance characteristics and performs well at all points in the operating frequencies bands. The CVL-WLF antenna offers 2 dBi gain with a VSWR rating of under 2:1 across the bandwidth.

The CVL-WLF has a very slim profile: the depth of the antenna is less than 1/4" (.6 cm). The overall dimensions are also small. The antenna is approximately 5 3/4" long, including the mounting holes, and 1 1/2" wide (14.6 cm x 3.8 cm).

The antenna features an over-molded plastic radome made from UV stable polyamide that allows some flexing of the antenna case. This flexibility, along with the antenna's slim profile, allows it to fit into a

Covert Antenna, LTE Broadband 694-2700 MHz

- Global LTE coverage for worldwide projects
- Extremely slim profile for tight installations
- Built-in mounting holes for easy installation

If mounted inside, the enclosure must be non-metallic: in other words the enclosure must be built out of a material such as plastic or fiberglass that will not block the transmission signal.

This antenna is typically configured with 8 feet (2.5m) of RG-174 cable and an SMA plug connector. Other cable lengths or connector options are available.

The antenna comes with two built-in grommet holes for an easy and secure installation. If the mounting holes are not needed and space is an issue, the mounting holes can be cut off. If the mounting holes are not used the antenna can be mounted with double sided tape.

This CVL-WLF antenna is completely encased in plastic and meets the water & dust ingress rating of IP69. In addition, it passes the following Military and Industrial standards for Shock & Vibration: IEEE-147, EN61373, TIA329.2-C and MIL-810G.

Carble

wide variety of mounting locations. The CVL-WLF can be mounted either outside or inside a stand-alone device, a NEMA box or a vehicle.		Model #	
		CVL-WLF-2C-BLK-96	8' (2.5m), RG-174
		CVL-WLF-2C-BLK-36	3' (91.4cm), RG-174
Specifications			
Frequency:	694-960 MHz	Dimension:	5 ³ /4"L x 1 ¹ /2"W x 1/4" H
	1700-2700 MHz		(14.6cm x 3.8cm x .6cm)
Gain:	2 dBi		(
VSWR:	2:1	Mounting:	Two .19" mounting hole
Radome Material:	UV Stable Polyamide	Ū.	or Double sided tape
Nominal Impedance:	50 Ohm (nominal)	Cables:	8 ft. long RG-174 standard
Max power:	10 watt	Connectors:	SMA Plug (Male)
maxperien	10 1144		0 ()
Operating Temp:	-40 to +85° C	Shock and Vibration:	IEEE1478, EN61373, MIL-810G,
Color:	Black		TIA 329.1-C
	Diack	Water Ingress:	IP69