| MATERIAL THICKNESS & APPLICATION | | BI-METAL HOLE SAWS | | | TUNGSTEN CARBIDE HOLE SAWS | | | DIAMOND GRIT/ TIPPED HOLE SAWS | |
|-------------------------------------|--------------|--------------------|--------------|---|---------------------------------------|--------------------------------|-------------------------------|---|------------------------------------|
| | | Fast Cut | Deep Cut | Cordless Smooth Cutting Hole Saw | Fast Cut Multi Purpose Hole Saw | Stainless Steel Hole Saw | Carbide Tipped Hole Saw | Ceramic & Abrasive Material Hole Saw | Brick & Masonry Dri-Core Dri |
| Hole Saw Depth | | 41mm 1.5/8" | 51mm 2" | 13mm 1/2" | 54mm 2.1/8" | 13mm 1/2" | 41mm 1.5/8" | Diameter Dependant | Diameter Dependant |
| Recommended Cutting Depths | Hole Saw Ref | FCH | DCH | CSC | FCH | | MPH | D | |
| | <3MM | ✓ | | ✓ | \checkmark | √ | ✓ | ✓ | |
| | 3-13MM | | \checkmark | | ✓ | | ✓ | ✓ | |
| | >13MM | | ✓ | | ✓ | | ✓ | ✓ | ✓ |
| Metal/Inox (Stainless) | | ** | ** | ** | | ** | | | |
| Non Ferrous Material | | ** | ** | ** | | ** | | | |
| Cast Iron | | ** | * | | | | * | | |
| Wood | | * | * | * | ** | | * | | |
| Nail Embedded Wood | | | | | | | ** | | |
| Veneer | | * | * | * | ** | | ** | | |
| MDF | | | | | ** | | | | |
| Plastic | | * | * | * | ** | | * | | |
| Acrylic | | * | * | * | ** | | * | | |
| Ceramic | | | | | * | | * | ** | |
| Porcelain/Glass/Stone | | | | | | | | ** | |
| Fibreglass | | * | * | | * | | ** | ** | |
| Formica | | * | * | * | ** | | ** | | |
| Plaster | | * | * | * | ** | | ** | | |
| Suspended Floors | | * | * | | | | ** | | |
| Brick & Masonry | | | | | | | * | ** | ** |
| Cutting Performance | | | | | | | | | |
| Excellent | ** | | | | | | | | |
| Satisfactory | * | | | | | | | | |

Starrett Hole Saws

Bi-Metal Cordless Smooth Cut Hole Saws

Complete hole saw assembly including arbor and pilot drill, specifically for cordless power tools. Heat resistant high speed steel edge, with alloy backing and constant pitch of 8 TPI for stainless and mild steel, sheet steel, plasterboard, wood and thin non-metallics.

Features and Benefits

- Ideal for cutting stainless steel, mild steel sheeting plus plasterboards, wood and thin plastics
- Safety stop at the base of the hole saw prevents drilling beyond the maximum cutting depth
- Complete assembly arbor and pilot drill included
- Constant pitch teeth provide exceptionally smooth cuts 8 teeth per 25mm/inch
- Recommended cutting depth 2mm
- Saw design enables longer battery life of tool between changes



Bi-Metal Cordless Smooth Cut Hole Saws.





CSC Hole Saw application.

CSC Hole Saw Kits also available see pg 54.

| | Saw | Pack |
|-------|------|-------|
| TYPE | Dia | Cont. |
| CSC16 | 16mm | 1 |
| CSC19 | 19mm | 1 |
| CSC20 | 20mm | 1 |
| CSC22 | 22mm | 1 |
| CSC25 | 25mm | 1 |
| CSC27 | 27mm | 1 |
| CSC29 | 29mm | 1 |
| CSC30 | 30mm | 1 |
| CSC32 | 32mm | 1 |
| CSC35 | 35mm | 1 |
| CSC38 | 38mm | 1 |
| CSC40 | 40mm | 1 |
| CSC51 | 51mm | 1 |