

M12 T1 SPE 1x2xAWG22/7 PUR 1,0m




Image is for illustration purposes only. Please refer to product description.

Part number	33 28 141 4002 010
Specification	M12 T1 SPE 1x2xAWG22/7 PUR 1,0m
HARTING eCatalogue	https://b2b.harting.com/33281414002010

Version

Cable length	1 m
Number of cores	2
Core structure	1x 2x AWG 22/7
Termination method	Crimp termination
Gender	Male
Shielding	Fully shielded, 360° shielding contact
Number of contacts	2
further contacts	+ shielding
Coding	Single Pair Ethernet (SPE)
Locking type	Screw locking

Technical characteristics

Rated current	4 A
Rated voltage	60 V DC
Transmission characteristics	600 MHz Bandwidth
Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
	2.5 Gbit/s
	5 Gbit/s
	10 Gbit/s
Contact resistance	≤20 mΩ
Shielding resistance	≤100 mΩ
Limiting temperature	-40 ... +80 °C unmoved
	-25 ... +80 °C moved



Pushing Performance
Since 1945

Technical characteristics

Mating cycles	≥1,000
Degree of protection acc. to IEC 60529	IP65 / IP67 mated condition
Test voltage U _{DC}	1 kV (contact-contact) 2.25 kV (contact-ground)

Material properties

Material (hood/housing)	Zinc die-cast
Material (cable)	PUR (polyurethane)
Colour (cable)	Yellow
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

Specifications and approvals

Specifications	IEC 63171-6 IEEE 802.3bu (remote power supply over PoDL = Power over Data Line) IEEE 802.3cg (10BASE-T1) IEEE 802.3bw (100BASE-T1) IEEE 802.3bp (1000BASE-T1) IEEE 802.3ch (2.5GBASE-T1 / 5GBASE-T1 / 10GBASE-T1) IEC 60332-1-2 Flame retardancy EN 60811-404 Oil resistance
----------------	---

Commercial data

Packaging size	1
Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140247093
eCl@ss	27060390 Ready-made data cable (unspecified)