www.vishay.com

Vishay Siliconix

RoHS

COMPLIANT

HALOGEN FREE



PRODUCT SUMMARY -40 V_{DS} (V) $R_{DS(on)}$ max. (Ω) at V_{GS} = 10 V 0.0022 $R_{DS(on)}$ max. (Ω) at V_{GS} = 7.5 V 0.0029 180 Q_g typ. (nC) I_D (A) ^a -198 Configuration Single


FEATURES

P-Channel 40 V (D-S) MOSFET

- · Leadership R_{DS(on)} minimizes power loss from conduction
- 100 % R_q and UIS tested
- Enhance power dissipation and lower R_{thJC}
- Material categorization: for definitions of please compliance see
- www.vishay.com/doc?99912

APPLICATIONS

- · Adapter and charger switch
- · Load switch
- Motor drive control
- Battery management



P-Channel MOSFET

ORDERING INFORMATION

Package	PowerPAK SO-8S	
Lead (Pb)-free and halogen-free	SiRS4401DP-T1-GE3	

PARAMETER		SYMBOL	LIMIT	UNIT	
Drain-source voltage		V _{DS}	-40	V	
Gate-source voltage		V _{GS}	± 20		
Continuous drain current (T _J = 150 °C)	T _C = 25 °C		-198		
	T _C = 70 °C		-158		
	T _A = 25 °C	I _D	-46.8 ^{b, c}		
	T _A = 70 °C		-37.4 ^{b, c}		
Pulsed drain current (t = 100 μs)		I _{DM}	-350	— A	
Continuous source-drain diode current	T _C = 25 °C		-110		
	T _A = 25 °C	I _S	-6.1 ^{b, c}		
Single pulse avalanche current		I _{AS}	-50		
Single pulse avalanche energy $L = 0.1 \text{ mH}$		E _{AS}	125	mJ	
Maximum power dissipation	T _C = 25 °C		132		
	T _C = 70 °C		84	w	
	T _A = 25 °C	P _D	7.4 ^{b, c}	VV	
	T _A = 70 °C		4.7 ^{b, c}		
Operating junction and storage temperature	e range	T _J , T _{stg}	-55 to +150	*0	
Soldering recommendations (peak temperature) ^c			260	°C	

THERMAL RESISTANCE RATINGS						
PARAMETER		SYMBOL	TYPICAL	MAXIMUM	UNIT	
Maximum junction-to-ambient b	t ≤ 10 s	R _{thJA}	13	17	°C/W	
Maximum junction-to-case (drain)	Steady state	R _{thJC}	0.73	0.95	0/10	

Notes

a. T_C = 25 °C b. Surface mounted on 1" x 1" FR4 board

t = 10 s c.

See solder profile (<u>www.vishay.com/doc?73257</u>). The PowerPAK SO-8S is a leadless package. The end of the lead terminal is exposed copper (not plated) as a result of the singulation process in manufacturing. A solder fillet at the exposed copper tip cannot be guaranteed and is not required to ensure adequate bottom side solder interconnection Rework conditions: manual soldering with a soldering iron is not recommended for leadless components Maximum under steady state conditions is 45 °C/W d.

e.

f.

S22-1039-Rev. A, 19-Dec-2022

1

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT www.vishav.com/doc?91000



Vishay Siliconix

PARAMETER	SYMBOL	TEST CONDITIONS	MIN.	TYP.	MAX.	UNIT	
Static			•			•	
Drain-source breakdown voltage	V _{DS}	V _{GS} = 0 V, I _D = -250 μA	-40	-	-	V	
V _{DS} temperature coefficient	$\Delta V_{DS}/T_{J}$	I _D = -10 mA	-	-30	-		
V _{GS(th)} temperature coefficient	$\Delta V_{GS(th)}/T_J$	I _D = -250 μA	-	5.6	-	mV/°C	
Gate-source threshold voltage	V _{GS(th)}	$V_{DS} = V_{GS}, I_{D} = -250 \ \mu A$	-1	-	-2.3	V	
Gate-source leakage	I _{GSS}	$V_{DS} = 0 V, V_{GS} = \pm 20 V$	-	-	± 100	nA	
u u u u u u u u u u u u u u u u u u u	I _{DSS} -	$V_{DS} = -40 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	-	-	-1		
Zero gate voltage drain current		V _{DS} = -40 V, V _{GS} = 0 V, T _J = 55 °C	-	-	-10	μA	
	_	V _{GS} = -10 V, I _D = -20 A	-	0.0018	0.0022	Ω	
Drain-source on-state resistance ^a	R _{DS(on)}	$V_{GS} = -4.5 \text{ V}, \text{ I}_{D} = -20 \text{ A}$	-	0.0023	0.0029		
Forward transconductance ^a	g _{fs}	V _{DS} = -15 V, I _D = -20 A	-	125	-	S	
Dynamic ^b	0.0						
Input capacitance	Ciss		-	21 850	-	pF	
Output capacitance	C _{oss}		-	1500	-		
Reverse transfer capacitance	C _{rss}		-	1320	-		
		V _{DS} = -20 V, V _{GS} = -10 V, I _D = -20 A	_	392	588	nC	
Total gate charge			-	180	270		
Gate-source charge	Q _{gs}	$V_{DS} = -20 \text{ V}, \text{ V}_{GS} = -4.5 \text{ V}, \text{ I}_{D} = -20 \text{ A}$	-	65	-		
Gate-drain charge	Q _{qd}		-	59	-		
Output charge	Q _{oss}	$V_{DS} = -20 \text{ V}, \text{ V}_{GS} = 0 \text{ V}$	-	45	-		
Gate resistance	R _q	f = 1 MHz	0.5	2.5	5	Ω	
Turn-on delay time	t _{d(on)}		-	20	40	-	
Rise time	t _r	V_{DD} = -20 V, R_L = 2 Ω , $I_D \cong$ -10 A, V_{GEN} = -10 V, R_g = 1 Ω	-	25	50		
Turn-off delay time	t _{d(off)}		-	220	440		
Fall time	t _f		-	80	160	1	
Turn-on delay time	t _{d(on)}		-	75	150	ns	
Rise time	t _r	V_{DD} = -20 V, R_L = 2 Ω , $I_D \cong$ -10 A, V_{GEN} = -4.5 V, R_g = 1 Ω	-	150	300	-	
Turn-off delay time	t _{d(off)}		-	220	440		
Fall time	t _f	-	-	120	240		
Drain-Source Body Diode Characteristi	· · · ·			1			
Continuous source-drain diode current	Is	T _C = 25 °C	-	-	-110		
Pulse diode forward current	I _{SM}	~ • •	-	-	-350	A	
Body diode voltage	V _{SD}	I _S = -10 A, V _{GS} = 0 V	-	-0.75	-1.2	V	
Body diode reverse recovery time	t _{rr}	0 0 00 0	-	48	96	ns	
Body diode reverse recovery charge	Q _{rr}	I _F = -10 A, di/dt = 100 A/μs,	-	50	100	nC	
Reverse recovery fall time	t _a	$T_{\rm J} = 25 ^{\circ}{\rm C}$	-	21	-	- ns	
Reverse recovery rise time	t _a	-	-	27	-		

Notes

a. Pulse test; pulse width \leq 300 µs, duty cycle \leq 2 %

b. Guaranteed by design, not subject to production testing


Stresses beyond those listed under "Absolute Maximum Ratings" may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated in the operational sections of the specifications is not implied. Exposure to absolute maximum rating conditions for extended periods may affect device reliability.

2





Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)





On-Resistance vs. Drain Current and Gate Voltage





Transfer Characteristics






On-Resistance vs. Junction Temperature

3




Vishay Siliconix


TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)




Source-Drain Diode Forward Voltage




On-Resistance vs. Gate-to-Source Voltage



Threshold Voltage



Single Pulse Power, Junction-to-Ambient



Safe Operating Area, Junction-to-Ambient

Note


a. V_{GS} > minimum V_{GS} at which $R_{DS(on)}$ is specified

For technical questions, contact: <u>pmostechsupport@vishay.com</u> THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT ARE SUBJECT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishay.com/doc?91000</u>



Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)






a. The power dissipation P_D is based on T_J max. = 150 °C, using junction-to-case thermal resistance, and is more useful in settling the upper dissipation limit for cases where additional heatsinking is used. It is used to determine the current rating, when this rating falls below the package limit




Vishay Siliconix

TYPICAL CHARACTERISTICS (25 °C, unless otherwise noted)



Normalized Thermal Transient Impedance, Junction-to-Ambient



Normalized Thermal Transient Impedance, Junction-to-Case

Vishay Siliconix maintains worldwide manufacturing capability. Products may be manufactured at one of several qualified locations. Reliability data for Silicon Technology and Package Reliability represent a composite of all qualified locations. For related documents such as package / tape drawings, part marking, and reliability data, see <u>www.vishay.com/ppg?62471</u>.

S22-1039-Rev. A, 19-Dec-2022	6	Document Number: 62471		
For technical questions, contact: pmostechsupport@vishay.com				
THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. THE PRODUCTS DESCRIBED HEREIN AND THIS DOCUMENT				
ARE SUBJE	CT TO SPECIFIC DISCLAIMERS, SET FORTH AT <u>www.vishav.c</u>	:om/doc?91000		



Vishay

Disclaimer

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Hyperlinks included in this datasheet may direct users to third-party websites. These links are provided as a convenience and for informational purposes only. Inclusion of these hyperlinks does not constitute an endorsement or an approval by Vishay of any of the products, services or opinions of the corporation, organization or individual associated with the third-party website. Vishay disclaims any and all liability and bears no responsibility for the accuracy, legality or content of the third-party website or for that of subsequent links.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.