

100G QSFP28 Active Optical Cable

FEATURES

- Four-channel full duplex active optical cable
- Multi-rate capability: 10 Gbps to 25.78125 Gbps per channel
- Low power consumption: < 2.5 W per cable end
- Single 3.3 V power supply
- Maximum link length of 70m on OM3 or 100m on OM4
- Built-in digital diagnostic functions, compliant with SFF-8636
- Hot pluggable
- Commercial operating case temperature range: 0 to 70°C
- RoHS compliant



APPLICATION

• 10/25/40/100G Ethernet

PRODUCT SELECTION

| Parameter | Length (m) | | |
|------------------------------------------------------------------------|------------|--|--|
| 2368650-1 | 1 | | |
| 2368650-2 | 2 | | |
| 2368650-3 | 3 | | |
| 2368650-4 | 5 | | |
| 2368650-5 | 10 | | |
| 2368650-6 | 15 | | |
| 2368650-7 | 20 | | |
| 2368650-8 | 30 | | |
| Note: For availability of additional cable lengths, please contact TE. | | | |



1. ABSOLUTE MAXIMUM RATINGS

| Parameter | Symbol | Min | Max | Unit |
|------------------------------------|--------|------|-----|------|
| Power Supply Voltage | Vcc | -0.5 | 3.6 | V |
| Storage Temperature | Tst | -40 | 85 | °C |
| Case Operating Temperature | Тор | 0 | 70 | °C |
| Relative Humidity (non-condensing) | RH | 0 | 85 | % |

2. RECOMMENDED OPERATING CONDITIONS

| Parameter | Symbol | Min | Тур | Max | Unit | Note |
|----------------------|--------|-------|----------|-------|------|---------------|
| Power Supply Voltage | VCC | 3.135 | 3.3 | 3.465 | V | |
| Power Supply Current | ICC | - | - | 750 | mA | per cable end |
| Power Dissipation | Р | - | - | 2.5 | W | per cable end |
| Bit Rate | BR | - | 25.78125 | - | Gbps | each channel |

3. GENERAL PRODUCT CHARACTERISTICS

| Parameter | Value | Notes | | |
|-----------------------------------------|---------------------------------------------------------------------------|---------------------------------------------------------------------------------------------------|--|--|
| Module Form Factor | QSFP28 | | | |
| Number of Lanes | 4 Tx and 4 Rx | | | |
| Maximum Aggregate Data Rate | 103.125 Gbps | | | |
| Maximum Data Rate per Lane | 25.781 Gbps | Data rates other than 25.781 Gbps is available through request and customization | | |
| Bit Error Ratio, Pre-FEC | 5x10 ⁻⁵ | Tested with PRBS31. Pre-FEC BER of 10 ⁻¹² supported through request and customization | | |
| Standard Cable Lengths | 1, 2, 3, 5, 10, 15, 20, 30 | Other lengths may be available upon request | | |
| Electrical Interface and Pin-out | 38-pin edge connector | Pin-out as defined by QSFP28 MSA SFF-8679 | | |
| Standard Optical Cable Type | Multimode round fiber cable, OFNR and Low Smoke Zero Halogen (LSZH) | OFNP rated cable may be available upon request | | |
| Maximum Power Consumption per Cable End | 2.5 W | | | |
| Management Interface | Serial, I2C-based, 400kHz maximum frequency | As defined by the QSFP28 MSA SFF- 8636 | | |

Rev B 2 of 4



4. ELECTRICAL CHARACTERISTICS

Low speed electrical specifications are compliant with SFF-8679 clause 5.

High speed electrical specifications are compliant with SFF-8679 clause 5, OIF CEI-VSR-28G/IEEE CAUI-4 over operating case temperature 0 to 70° C and VCC 3.3 ± 5% Volts.

| Parameter | Min | Max | Unit | Note |
|--------------------------------------------------------------------------------------------------------|------------------------------------|--------------------|----------|------|
| | Module Electrica | ıl Input | | |
| Overload Differential Voltage pk-pk | 900 | - | mV | |
| Common Mode Voltage (Vcm) | -350 | 2850 | mV | 1 |
| Differential Termination Resistance Mismatch | - | 10 | % | |
| Differential Return Loss (SDD11) | CEI-VSR-28G Equation 13-19 | | dB | |
| Common Mode to Differential conversion and Differential to Common Mode conversion (SDC11, SCD11) | CEI-VSR-28G Equation 13-20 | | dB | |
| Stressed Input Test | CEI-VSR-28G Section 13.3.11.2.1 | | | |
| | Module Electric | al Output | | |
| | | | | |
| Differential Voltage, pk-pk | - | 900 | mV | |
| Common Mode Voltage (Vcm) | -350 | 2850 | mV | 1 |
| Common Mode Noise, RMS | - | 17.5 | mV | |
| Differential Termination Resistance Mismatch (at 1 MHz) | - | 10 | % | |
| Differential Return Loss (SDD22) | CEI-VSR-28G Equation 13-19 | | dB | |
| Common Mode to Differential conversion and Differential to Common Mode Conversion (SDC22, SCD22) | CEI-VSR-28G Equation 13-21 | | dB | |
| Common Mode Return Loss (SCC22) – from 250 MHz to 30 GHz | - | -2 | dB | |
| Transition Time, 20 to 80% | 9.5 | - | ps | |
| Vertical Eye Closure (VEC) | - | 5.5 | dB | |
| Eye Width at 10-15 probability (EW15) | 0.57 | - | UI | |
| Eye Height at 10-15 probability (EH15) | 228 | - | mV | |
| Notes: 1. Vcm is generated by the host. Specificat | tion includes effect | s of ground offset | voltage. | |

Rev B 3 of 4



5. PIN ASSIGNMENT


Pin assignment is compliant with SFF-8679.

6. MEMORY MAP

The memory map is compatible with SFF-8636, and customization can be supported.

7. MECHANICAL SPECIFICATIONS

Unit: mm



Rev B 4 of 4