

MATE-N-LOK | Universal MATE-N-LOK

TE Internal #: 926893-3

Power Contacts, Contact, 600 VAC, Tin, 20 – 14 AWG Wire Size, .5 – 2.1 mm² Wire Size, Wire & Cable, Crimp, Power, Socket, Universal

MATE-N-LOK

View on TE.com >



Connectors > Power Connectors > Power Contacts











Power Contact Type: Contact
Operating Voltage: 600 VAC

Contact Mating Area Plating Material: Tin

Wire Size: .5 – 2.1 mm²

Features

Product Type Features

Compatible With Discrete Wire Type	Stranded
Power Contact Type	Contact
Connector & Contact Terminates To	Wire & Cable
Electrical Characteristics	
Operating Voltage	600 VAC
Contact Features	
Contact Shape & Form	Split
Contact Mating Area Plating Material	Tin
Contact Current Rating (Max)	19 A
Contact Type	Socket
Contact Retention Within Housing	With
Mating Pin Diameter	2.06 mm[.081 in]
Contact Base Material	Phosphor Bronze
Wire Contact Termination Area Plating Material	Tin
Wire Contact Termination Area Plating Material Finish	Matte



Contact Orientation	Straight
Termination Features	
Termination Method to Wire & Cable	Crimp
Mechanical Attachment	
Contact Retention Type Within Housing	Locking Lance
Wire Insulation Support	Without
Dimensions	
Wire Size	.5 – 2.1 mm ²
Accepts Insulation Diameter Range	3.3 mm[.13 in]
Usage Conditions	
Operating Temperature Range	-55 – 105 °C[-67 – 221 °F]
Operation/Application	
Circuit Application	Power
Industry Standards	
CSA Rating	Certified, LR 7189
UL Rating	Recognized
Agency/Standard	CSA, UL, VDE
Packaging Features	
Packaging Quantity	1000
Packaging Method	Box

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233) Candidate List Declared Against: JUNE 2022 (224) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free



Solder Process Capability

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach

Compatible Parts





INSERTION TOOL







































Also in the Series | Universal MATE-N-LOK







Connector Contacts(7)



Insertion & Extraction Tools(4)



Power Contacts(201)



Rectangular Boots & Strain Relief(34)



Rectangular Connector Adapters(7)




Rectangular Connector Hardware(1)



Rectangular Connector Housings(1)



Rectangular Connector Keying Plugs(3)



Rectangular Connector Seals(26)



Rectangular Power Connectors(662)

Customers Also Bought





















Documents

Product Drawings

UNIV.M-N-L.SOCKET

English

CAD Files

Customer View Model

ENG_CVM_CVM_926893-3_K.2d_dxf.zip

English

3D PDF

3D

Customer View Model

ENG_CVM_CVM_926893-3_K.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_926893-3_K.3d_stp.zip

English

By downloading the CAD file I accept and agree to the **Terms and Conditions** of use.

Product Environmental Compliance



MD_926893-3_04022018031_dmtec

English

MD_926893-3_04022018031_dmtec

English

Agency Approvals

VDE Certificate

English