

402E



Electronic SUPER DUSTER™

402E is a portable, hand-held, eco-friendly electronic blower that's an alternative to using compressed air for removing dust in hard-to-reach areas. This duster has multiple settings, balancing performance with battery life and unlike compressed air products, does not get cold during extended use.

402E is ideal for use around the home and office for cleaning dust, lint and debris on keyboards, audio visual, PCBs, telecommunication devices and lab equipment. It is also an excellent choice for repair and maintenance technicians and service providers.

Features & Benefits

- ESD-safe
- Eco-friendly and cost-effective
- Cordless and rechargeable
- USB charging cable included—fast recharge
- Strong dust blowing
- Digital display
- 5 h of use (low) and 40 min of use (high)
- RoHS compliant

Available Packaging

Cat. No.	Packaging	Size	Net Wt.
402E	Electronic duster	7.5 x 8.0 x 15.8 cm	400 g

Contact Information

MG Chemicals, 1210 Corporate Drive
Burlington, Ontario, Canada L7L 5R6

Email: support@mgchemicals.com

Phone: North America: +(1)800-340-0772

International: +(1) 905-331-1396

Europe: +(44)1663 362888



Usage Parameters

Working Time (low setting)	5 h
(high setting)	40 min
Speed	40 000 rpm
Working Temperature	<55 °C
Sound Level	<85 dB

Battery Properties

Battery Type	Lithium-ion
Voltage	11.1 V
Watt-Hour Rating	22.2 Wh
Battery Capacity	2 000 mAh

Instructions

1. Check battery power by pressing the battery indicator button on the display.
2. Let device cool 5 to 10 min before charging.
3. Recharge when battery is at 30% to extend life.
4. Insert the blowpipe attachment into the blowpipe hole.
5. Slide the power switch to H1 for low speed or H2 for high speed.

Disclaimer

This information is believed to be accurate. It is intended for professional end-users who have the skills required to evaluate and use the data properly. M.G. Chemicals Ltd. does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.