



Part Number : [1205050106](#)
Product Description : Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female Mini-Change (Straight) to Male M12 L-Coded (Straight), 16 AWG, Black TPU WSOR Cable, 5.0m (16.4') Length
Series Number : 120505
Status : Active
Product Category : Circular Industrial Cordsets
Engineering Number : 1LP5030B66M050



Documents & Resources

Drawings
[Drawing 1205050106_sd.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Compliant with Exemption 3; 10(a) per 2000/53/EC
Low-Halogen Status	Not Relevant
REACH SVHC	Contains Lead per D(2022)9120-DC (17 Jan 2023)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration

- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Circular Industrial Cordsets
Series	120505
Description	Micro-Change (M12) Double-Ended Cordset, 5 Poles, Female Mini-Change (Straight) to Male M12 L-Coded (Straight), 16 AWG, Black TPU WSOR Cable, 5.0m (16.4') Length
IP Rating	IP67
Product Family	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Region	Asia, Europe
Type	Double Ended
UPC	195842918238

Agency

UL	E152210
----	---------

Electrical

Current - Maximum per Contact	12.0A
Voltage - Maximum	63V

Physical

Cable Diameter	8.60mm (.338")
Cable Length	5.0m (16.40')
Color - Cable Jacket	Black
Connector End A	Mini-Change
Connector End B	Micro-Change (M12)
Coupling Style	Threaded

Gender	Female-Male
Keyway	L-Coded
LED Indicator	No
Material - Cable Jacket	WSOR TPU
Material - Connector Body	TPE
Material - Contact	Brass
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold
Net Weight	656.500/g
Orientation	Straight to Straight
Poles	5
Temperature Range - Operating	-25° to +85°C
Wire/Cable Type	UL 21215
Wire Size (AWG)	16