
NI-9425

Specifications

2023-08-02



Contents

NI-9425 Specifications..... 3

NI-9425 Specifications

Introduction

In this document, the NI-9425 with spring terminal and NI-9425 with DSUB are referred to inclusively as the NI-9425. The information in this document applies to all versions of the NI-9425 unless otherwise specified.

Related information:

- [Software Support for CompactRIO, CompactDAQ, Single-Board RIO, R Series, and EtherCAT](#)

Definitions

Warranted specifications describe the performance of a model under stated operating conditions and are covered by the model warranty.

Characteristics describe values that are relevant to the use of the model under stated operating conditions but are not covered by the model warranty.

- **Typical** specifications describe the performance met by a majority of models.
- **Nominal** specifications describe an attribute that is based on design, conformance testing, or supplemental testing.

Specifications are **Typical** unless otherwise noted.

Conditions

Specifications are valid for the range -40 °C to 70 °C unless otherwise noted.

Input Characteristics

| | |
|-------------------------------|---------------------------|
| Number of channels | 32 digital input channels |
| Input type | Sinking |
| Digital logic levels | |
| OFF state | |
| Input voltage | ≤ 5 V |
| Input current | ≤ 150 μ A |
| ON state | |
| Input voltage | ≥ 10 V |
| Input current | ≥ 330 μ A |
| Hysteresis | |
| Input voltage | 2 V minimum |
| Input current | 60 μ A minimum |
| Input impedance | 30 k Ω \pm 5% |
| I/O protection | |
| Input voltage | |
| 8 channels | 60 V DC maximum |
| 32 channels | 30 V DC maximum |
| Reverse-biased voltage | |
| 8 channels | -60 V DC maximum |

| | |
|--------------------------------------|--|
| 32 channels | -30 V DC maximum |
| Hold time | 0 μ s minimum |
| Setup time | 1 μ s minimum |
| Update/transfer time | |
| cRIO-9151 R Series Expansion chassis | 8 μ s maximum |
| All other chassis | 7 μ s maximum |
| MTBF | 1,256,699 hours at 25 °C; Bellcore Issue 2, Method 1, Case 3, Limited Part Stress Method |

Power Requirements

| | |
|---------------------------------------|----------------|
| Power consumption from chassis | |
| Active mode | 410 mW maximum |
| Sleep mode | 0.5 mW maximum |
| Thermal dissipation (at 70 °C) | |
| Active mode | 1.45 W maximum |
| Sleep mode | 1 W maximum |

Physical Characteristics

| | |
|-------------------------------|--|
| Spring-terminal wiring | |
| Gauge | 0.14 mm to 1.5 mm (26 AWG to 16 AWG) copper conductor wire |

| | |
|------------------------------|--|
| Wire strip length | 10 mm (0.394 in.) of insulation stripped from the end |
| Temperature rating | 90 °C, minimum |
| Wires per spring terminal | One wire per spring terminal; two wires per spring terminal using a 2-wire ferrule |
| Ferrules | 0.14 mm to 1.5 mm |
| Connector securement | |
| Securement type | Screw flanges provided |
| Torque for screw flanges | 0.2 N · m (1.80 lb · in.) |
| Weight | |
| NI-9425 with spring terminal | 163 g (5.7 oz) |
| NI-9425 with DSUB | 147 g (5.2 oz) |

NI-9425 with Spring Terminal Safety Voltages

Connect only voltages that are within the following limits:

| | |
|--------------------------------|------------------------------------|
| Channel-to-COM | 60 V DC |
| Isolation | |
| Channel-to-channel | None |
| Channel-to-earth ground | |
| Continuous | 250 V RMS, Measurement Category II |

| | |
|-------------------------|--|
| Withstand Up to 5,000 m | 3,000 V RMS, verified by a 5 s dielectric withstand test |
|-------------------------|--|

NI-9425 with DSUB Safety Voltages

Connect only voltages that are within the following limits:

| | |
|--------------------------------|---|
| Channel-to-COM | 60 V DC |
| Isolation | |
| Channel-to-channel | None |
| Channel-to-earth ground | |
| Continuous | 60 V DC, Measurement Category I |
| Withstand up to 2,000 m | 1,000 V RMS verified by a 5 s dielectric withstand test |
| Withstand Up to 5,000 m | 500 V RMS , verified by a 5 s dielectric withstand test |

Environmental Characteristics

| | |
|--------------------|---------------------------------|
| Temperature | |
| Operating | -40 °C to 70 °C |
| Storage | -40 °C to 85 °C |
| Humidity | |
| Operating | 10% RH to 90% RH, noncondensing |
| Storage | 5% RH to 95% RH, noncondensing |

| | |
|----------------------------|---|
| Ingress protection | IP40 |
| Pollution Degree | 2 |
| Maximum altitude | 2,000 m |
| Shock and Vibration | |
| Operating vibration | |
| Random | 5 g RMS, 10 Hz to 500 Hz |
| Sinusoidal | 5 g, 10 Hz to 500 Hz |
| Operating shock | 30 g, 11 ms half sine; 50 g, 3 ms half sine; 18 shocks at 6 orientations |

To meet these shock and vibration specifications, you must panel mount the system.

Calibration

You can obtain the calibration certificate and information about calibration services for the NI-9425 at ni.com/calibration.

| | |
|----------------------|--------|
| Calibration interval | 1 year |
|----------------------|--------|