TECHNICAL DATA







Lubricants



High Temperature Resistant

AMBERGREASE SIL

PURE SILICONE GREASE

Ambergrease SIL is a high quality, pure silicone grease which is water repellent and non-melting, prevents moisture ingress. As an anti-tracking, anti-arcing coating, it will protect electrical systems. It can also be used as a multipurpose lubricating agent. It has many uses in electrical and chemical industries.

It is insoluble in water, alcohol, diluted acids and alkalis, taste free, odourless and non-toxic. Withstands marine environments.

PRODUCT CODES / FILL SIZES



31888 / 100g

APPLICATIONS

Electrical servicing:

- Anti-tracking, anti-corona discharge coating
- Waterproofing all types of electric systems
- Protection of switch gear, distributors
- · Easing cables into conduits

Lubrication of:

- Instruments subjected to high or low temperatures
- Centrifuge and autoclave lid seals
- · Cold room trolley castors
- Conditioning devices
- Conveyor chains
- · Glass and ceramic stop-cocks and glands

O-ring and rubber seal assembly:

- Pneumatic, automotive and compressed air systems
- Plastic plumbing systems

Moulding:

- Shell moulding for the pre-treatment of pattern plates
- Ingot moulding for brass, aluminium and silver

Typical Industries:

- Automotive
- Mechanical engineering
- Workshops
- Civil engineering
- Mining

- Iron and steel
- Dock yards
- Agricultural machinery
- Heavy engineering
- Offshore

DIRECTIONS

- Apply straight from container and spread to cover required area
- Can be applied by brush if desired.

TECHNICAL DATA



TECHNICAL DATA (WITHOUT PROPELLANT)

| Physical appearance | Smooth, translucent grease |
|---|--|
| Colour | Colourless |
| Odour | Odourless |
| Grade (NLGI) | 2 |
| Penetration (unworked) | 200 - 260 mm/10 |
| Penetration (worked) | 280 maximum |
| Dielectric strength (IEC 243-1) | 15.4 kV/mm |
| Volume resistivity (IEC3) | 1.4 x 10 ¹⁵ ohm.mm |
| Dielectric loss | 0.0018 at 1 kHz |
| TEC250 | 0.0022 at 1 MHz |
| Resistance to corrosion - EMCOR (IP220) | 0:0 |
| Water washout @38°C - (ASTM D 1264) | 2% maximum |
| Operating temperature range | -40°C to +200°C (220°C intermittently) |
| Flash point | >300°C |

MATERIALS COMPATIBILITY

OK No effects on rubber, plastic and metals

CAUTION -NOT OK -

STORAGE & SHELF LIFE

The product may be stored at normal ambient temperatures and has a shelf life of not less than 3 years with correct storage.

HEALTH AND SAFETY

A separate Safety Data Sheet (SDS) according to EC Regulation 73/404/EEC and 648/2004/EC is available from Ambersil.com or via info.uk@crcind.com

MISREPRESENTATION ACT 1967

TRADE DESCRIPTIONS ACT 1968

The information given in this publication is based on our experience and reports from customers. There are many factors outside our control and knowledge which affect the use and performance of our products and for which reason no warranty is given, express or implied. Users should make their own tests to determine the applicability of such information or the suitability of any products for their own particular purposes. Statements concerning the use of the products described herein are not to be construed as recommending the infringement of any patent and no liability for infringement arising out of any such use is to be assumed.

Version 3.3 Created: July 2019 Updated: May 2022

CRC Industries UK Ltd. Wylds Road,Bridgwater Somerset, TA6 4DD United Kingdom

Company Registered No. 04910479

t +44 (0)1278 727200

f +44 (0)1278 425644

e sales.uk@crcind.com

w www.ambersil.com

VAT No. GB 821 5195 42



