

AEC-Q200 (-40 to 85°C) qualified component family

Multilayer Antenna

For 2400-2484MHz

ANT162442ST-1000AM1

1.6x0.8mm [EIA 0603]*

* Dimensions Code JIS[EIA]




Multilayer Antenna


For 2400-2484MHz

Conformity to RoHS Directive

ANT162442ST-1000AM1

SHAPES AND DIMENSIONS






Те	Terminal functions					
1	Radiator electrode					
2	Dummy pad					
3	Dummy pad					
4	Feed point					
5	Dummy pad					
6	Dummy pad					


Dimensions in mm

■ RECOMMENDED LAND PATTERN



Dimensions in mm

■SOLDER RESIST PATTERN




Dimensions in mm

OROHS Directive Compliant Product: See the following for more details.https://product.tdk.com/info/en/environment/rohs/index.html


[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.

EVALUATION BOARD




PCB size : 50mm x 20mm x 1mm Antenna area : 5 x 3 mm



	Component P/N
Ft-1	6.2pF
Mt	0.8pF

☐ Measurement condition for Radiation Pattern



- All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.



ELECTRICAL CHARACTERISTICS

Item	Frequency Range (MHz)	Min.	Тур.	Max.
VSWR	2400 to 2484	_	1.60	3.0
Polarization			Linear	
PCB size (mm)			50×20	
Antenna keep-out area (mm)			5×3	
Characteristic Impedance (Ω)			50 (Nominal)	


 $[\]boldsymbol{\cdot}$ This is typical antenna performance with the standard PCB.

TEMPERATURE RANGE

Operating temperature	Storage temperature		
(°C)	(°C)		
-40 to +85	-40 to +85		

FREQUENCY CHARACTERISTICS

EFFICIENCY AND VSWR



• Tested antenna has been soldered. Evaluation board size is 50x20x1 mm.


[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



RADIATION PATTERNS

□2.4GHz BAND




Tested antenna has been soldered. Evaluation board size is 50x20x1 mm.

- All specifications are subject to change without notice.
- Before using these products, be sure to request the delivery specifications.



■ RECOMMENDED REFLOW PROFILE



Preheating			Soldering Critical zone (T3 to T4) Peak					
Temp.		Time	Temp.	Time	Temp.	Time		
T1	T2	t1	T3	t2	T4	t3*		
150°C	200°C	60 to 120sec	217°C	60 to 120sec	240 to 260°C	30sec max.		


^{*}t3: Time within 5°C of actual peak temperature


The maximum number of reflow is 3.

All specifications are subject to change without notice.Before using these products, be sure to request the delivery specifications.

■ PACKAGING STYLE


☐REEL DIMENSIONS





Dimensions in mm

TAPE DIMENSIONS



Dimensions in mr								sions in mm		
Α	В	С	D	Е	F	G	Н	J	K	t
0.97±0.05	1.8±0.05	8.0±0.2	3.5±0.05	1.75±0.1	4.0±0.1	2.0±0.05	4.0±0.1	1.5+0.1/-0	0.55max.	0.25±0.05

■ PACKAGE QUANTITY

Standardpackage quantity
(pieces/reel)
4,000

[•] All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.



REMINDERS FOR USING THESE PRODUCTS

Before using these products, be sure to request the delivery specifications.

SAFETY REMINDERS

Please pay sufficient attention to the warnings for safe designing when using these products.

⚠ REMINDERS

The products listed on this catalog are intended for use in general electronic equipment (AV equipment, telecommunications equipment, home appliances, amusement equipment, computer equipment, personal equipment, office equipment, measurement equipment, industrial robots) under a normal operation and use condition.

The products are not designed or warranted to meet the requirements of the applications listed below, whose performance and/or quality require a more stringent level of safety or reliability, or whose failure, malfunction or trouble could cause serious damage to society, person or property.

Please understand that we are not responsible for any damage or liability caused by use of the products in any of the applications below or for any other use exceeding the range or conditions set forth in this catalog.

- (1) Aerospace/Aviation equipment
- (2) Transportation equipment (cars, electric trains, ships, etc.)
- (3) Medical equipment
- (4) Power-generation control equipment
- (5) Atomic energy-related equipment
- (6) Seabed equipment
- (7) Transportation control equipment

- (8) Public information-processing equipment
- (9) Military equipment
- (10) Electric heating apparatus, burning equipment
- (11) Disaster prevention/crime prevention equipment
- (12) Safety equipment
- (13) Other applications that are not considered general-purpose applications

When using this product in general-purpose applications, you are kindly requested to take into consideration securing protection circuit/equipment or providing backup circuits, etc., to ensure higher safety.

All specifications are subject to change without notice.

[•] Before using these products, be sure to request the delivery specifications.