





REV	ECN	DESCRIPTION	APP'D
G	2478	UPDATE FORMAT; REVISE MARKING	DS 7/27/93
H	7350	REDRAW; UPDATE SUBASSEMBLY P/N	AT 11/18/14



DETAIL
SCALE: 5X
ROTATED 90°

2X FIXED STUD
STUD RETENTION FORCES:
AXIAL - 100 LB MIN.
TORQUE - 24 IN.-LB MIN APPLIED TO 10-32

SUBASSEMBLY P/N	RELAY SOCKET P/N		SUPPLIED CONTACTS				MARKING
	MILITARY	APCD	SIZE	MIL P/N	APCD P/N	QTY	
700116697-IN	M12883/41-17	RSE116696	CONTACTS NOT SUPPLIED				M12883/41-17 J 58982 XXXX RSE116697
		RSE116697	16/16	M39029/92-533	CNS126900	8	

DIMENSIONS ANSI Y14.5M UNITS: INCHES Pro/E FILE	TOLERANCES .XX ±0.01 .XXX ±0.005 ANGLES ±2.0°	PROJECTION 	Amphenol Pcd		RELAY SOCKET 2-POLE, 10 AMP, FIXED STUDS REF. M12883/41-17			
			ENGR J.PHAN Sept-24-14	TITLE RELAY SOCKET 2-POLE, 10 AMP, FIXED STUDS REF. M12883/41-17			SIZE B	DWG NO. RSE116696
ORIGINAL NOT FOR CUSTOMER DISTRIBUTION	THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF AMPHENOL PCD, BEVERLY, MA			CHKD <i>William Luma</i> 11/18/14 APPD <i>John</i> 11/18/14	CODE: 58982	SCALE: 5:3	SHEET 1 OF 1	

RSE116696

RSE116696