

PRODUCT DATA DRAWING





MATERIAL:

BODY: STAINLESS STEEL

CONTACT: BERYLLIUM COPPER

INSULATOR: TORLON

FINISH:

BODY & CONTACT: GOLD OVER NICKEL


PERFORMANCE:

IMPEDANCE: 50 OHMS

FREQ. RANGE: DC TO 40.0 GHz.

NOTES:

- DIMENSIONS APPLY PRIOR TO PRE-TINNING Sn63 SOLDER REQUIRED IN HATCHED AREA.
- SOLDER PERMISSBLE ON OUTER AND ADJACENT SURFACES OF BODY IN THIS AREA.
- FOR A FOOTPRINT RECOMMENDATION SPECIFIC TO YOUR PCB, PLEASE CONTACT US AT applications@svmicro.com



MATERIAL:	SEE NOTES
FINISH:	SEE NOTES

SURFACE AREA: N/A

PROPRIETARY

THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF SV MICROWAVE, INC. ANY REPRODUCTION IN PART OR AS A WHOLE WITHOUT THE WRITTEN PERMISSION OF SV MICROWAVE, INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15'

.X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE F	PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING,
3) BREAK CORNERS & EDGES 005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63.4 MIL-STD-10.
6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN. 005 T.I.R.
7) REMOVE ALL BURRS

N	DRAWN:	KRR 02/16/23
	CHECKED:	SEE PDM
	APPROVED:	SEE PDM

MICROWAVE


THREADED MALE SMPM **SMOOTH BORE PCB MOUNT**

SIZE B	DWG. NO.	3212-60037	

SCALE: 15:1 SHEET 1 OF 2

	REVISION HISTORY		
REV DESCRIPTION		DATE	APPROVED
SEE SHEET 1			
			SEE PDM

RECOMMENDED PCB MECHANICAL FOOTPRINT



MATERIAL:	SEE NOTES
FINISH:	SEE NOTES
SURFACE ARE	^{A:} N/A
F	PROPRIETARY
IS THE SOLE PR ANY REPRODUC WITHOUT THE W	ON CONTAINED IN THIS DRAWING OPERTY OF SV MICROWAVE, INC. ITION IN PART OR AS A WHOLE /RITTEN PERMISSION OF , INC IS PROHIBITED.

DIMENSIONS ARE IN INCHES TOLERANCES: FRACTIONAL: ±1/64 ANGULAR: X° ±1°0' X°X' ±15' DECIMAL: .X ±.030 .XX ±.010 .XXX ±.005

INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M - 1994

THIRD ANGLE PROJECTION

UNLESS OTHERWISE SPECIFIED

1) ALL DIMENSIONS ARE IN INCHES [MILLIMETERS]
2) ALL DIMENSIONS ARE AFTER PLATING.
3) BREAK CORNERS & EDGES. 005 R. MAX.
4) CHAM. 1ST & LAST THREADS.
5) SURFACE ROUGHNESS 63. MIL-STD-10.
6) DIA.'S ON COMMON CENTERS TO BE CONCENTRIC WITHIN T.I.R.
7) REMOVE ALL BURRS

APPROVED:

DRAWN: SEE SHEET 1 CHECKED: SEE PDM

SEE PDM



THREADED MALE SMPM SMOOTH BORE PCB MOUNT

SIZE DWG. NO. 3212-60037