
880310-1 🗸 ACTIVE

FASTIN-FASTON | FASTIN-FASTON 250

TE Internal #: 880310-1 Crimp Terminal Housings, Tab, Tab Housing, 2 Position, Straight, Natural, Nylon, Contact Mating Retention, Mating Alignment, FASTIN-FASTON 250

View on TE.com >

Terminals & Splices > Terminal Housings, Insulation Sleeves & Blocks > Crimp Terminal Housings



Terminal Type: Tab

Connector & Housing Type: Tab Housing

Number of Positions: 2

Terminal Orientation: Straight

Primary Product Color: Natural

Features



Product Type Features

Sealable	No								
Connector & Housing Type	Tab Housing								
Configuration Features									
Number of Positions	2								
Body Features									
Primary Product Color	Natural								
Contact Features									
Terminal Type	Tab								
Terminal Orientation	Straight								
Contact Mating Retention	With								
Mechanical Attachment									
Mating Retention Type	Latch								
Mating Alignment	With								

C For support call+1 800 522 6752

880310-1

Crimp Terminal Housings, Tab, Tab Housing, 2 Position, Straight, Natural, Nylon, Contact Mating Retention, Mating Alignment, FASTIN-FASTON 250



Connector Mounting Type	Cable Mount (Free-Hanging)								
Housing Features									
Housing Material	Nylon								
Centerline (Pitch)	7.4 mm[.291 in]								
Dimensions									
Product Length	31.1 mm[1.22 in]								
Usage Conditions									
Operating Temperature Range	-40 - 105 °C[-40 - 221 °F]								
Packaging Features									
Packaging Method	Carton								
Product Compliance For compliance documentation, visit the product page on TE.com>									
EU RoHS Directive 2011/65/EU	Compliant								
EU ELV Directive 2000/53/EC	Compliant								
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold								
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2023 (233)								

Halogen Content

Solder Process Capability

(233)Candidate List Declared Against: JAN 2023(233)Does not contain REACH SVHC

Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free

Not applicable for solder process capability

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: https://echa.europa.eu/guidance-documents/guidance-on-reach


Compatible Parts

L For support call+1 800 522 6752


880310-1

Crimp Terminal Housings, Tab, Tab Housing, 2 Position, Straight, Natural, Nylon, Contact Mating Retention, Mating Alignment, FASTIN-FASTON 250






Also in the Series | FASTIN-FASTON 250



Crimp Terminal Housings(212)	Insertion & Extraction Tools(2)	PCB Terminals(2)	Quick Disconnects(254)

Customers Also Bought



880310-1

Crimp Terminal Housings, Tab, Tab Housing, 2 Position, Straight, Natural, Nylon, Contact Mating Retention, Mating Alignment, FASTIN-FASTON 250





Documents

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_880310-1_R_c-880310-1-r.2d_dxf.zip

English

Customer View Model ENG_CVM_CVM_880310-1_R_c-880310-1-r.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_880310-1_R_c-880310-1-r.3d_stp.zip

English

By downloading the CAD file I accept and agree to the Terms and Conditions of use

Datasheets & Catalog Pages White Paper: Nylon Discoloration

English

Product Specifications Application Specification

English

Product Environmental Compliance MD_880310-1_061020182355_dmtec

English

MD_880310-1_061020182355_dmtec

English